



# Power Bank - XT-27000DC-PA

- Reliable energy for your application
- High quality cells
- Customized settings possible (Voltage)
- Long-life series
- DC output up to 24V



RoHS compliant



Pb free



REACH compliant



Conflict mineral free

## TECHNICAL DATA

Part number	249745
Battery type	Lithium Ion
Capacity	26800mAh (3.7V) / 99Wh
Connections	1x USB-C (OUTPUT/INPUT) 2x USB Q3 Output 1x DC Socket (OUTPUT/INPUT)
Input	1 x USB-C 5V 15W /20V max.30W 1 x DC Socket 14V-20V max.45W
Output	1 x USB-C 5V 2.4A 9-20V PD 60W max 2 x USB QC3 3.8V-12V/max.18W DC Socket 5/6/9/12/14/15/16/19/20/24V 80 Watt continuous / max.100W
Dimensions	142 x 80 x 41 mm
Weigth	550g

## DELIVERY CONTENT

- Powerbank XTPower XT-27000DC
- USB-C cable
- DC cable 2m
- Car charging adapter for DC socket
- 8 Notebook and Netbook Adapter  
C = IBM, Acer, Toshiba, Dell, Asus - 5.5x2.5mm  
D = Asus, HP, NEC, Toshiba, Acer - 5.5x2.1mm  
E = Acer, Lenovo, Sony - 5.5x1.7mm  
G = HP, Acer,Asus,Sony,Samsung - 4.0x1.7mm  
HP = HP - 4.5x3.0mm  
Dell = Dell - 4.5x3.0mm  
M = Lenovo - 7.9x5.4x0.9mm  
I = Dell, HP, Compaq - 7.4x5.0mm
- Power supply unit

## OUTSTANDING FEATURES

- Simultaneously charging and discharging
- Power bank for industrial and professional applications
- Automatic switch off at DC port below 4W
- Also available without automatic switch off at DC output
- Boarding with all airlines (<100Wh)

## ADDITIONAL DATA

Life expectancy	approx. 500 charging cycles
Dimensions DC round socket	5.5mm x 2.1mm
Charging time	approx. 2 hours from 0% to 100%
Charging temperature	0 °C - 45 °C
Operating temperature	-20 °C - +60 °C
Safety	Overcharge protection Discharge protection Short circuit protection
EAN/GTIN	4250637213229



## SCOPE OF DELIVERY

