


CONJUNTO

The image displays a technical drawing of a rectangular assembly, labeled "CONJUNTO". On the left is a top-down view with the following dimensions: overall width 64,10; overall height 29,10; a top-left corner with a 12,05 wide and 2,80 high rectangular cutout; a central horizontal slot with a width of 23,50; a bottom-right corner with a 12,05 wide and 5,50 high rectangular protrusion; and a circular hole with a diameter of 2,80 located 2,80 from the bottom edge and 12,05 from the right edge. On the right is an exploded perspective view showing three components: a top cover with a rectangular notch, a middle plate with two circular holes, and a base with a matching rectangular protrusion.



CUERPO

Technical drawing of the PH008 body, showing three views: top, side, and cross-section A-A.

Top View Dimensions:

- Overall width: 58,50
- Overall height: 29,20
- Inner width: 64,20
- Inner height: 23,50
- Section line A-A is indicated.

Side View Dimensions:

- Overall height: 31,20
- Base width: 6,50
- Top edge radius: R2

Cross-section A-A Dimensions:

- Overall length: 66,20
- Top flange height: 9,5
- Internal cavity width: 6,70
- Internal cavity height: 2,50
- Bottom flange height: 3

Isometric View:

- Shows the 3D perspective of the rectangular body with rounded corners and a central cavity.

Al copiar esta información no se actualizará. Copy for information will not be updated

SUPERTRONIC REF.	PH008	Revision Version 00
www.supertronic.com	supertronic@supertronic.com	+34 932 980 257
Firmado Signed		

