

# GP Batteries

## DATA SHEET



### NO MERCURY ADDED

<b>Description</b>	Mercury & Cadmium Free Alkaline Manganese Battery, AAA Size
<b>Chemical System</b>	Alkaline Manganese
<b>Nominal Voltage</b>	1.5 Volts
<b>Nominal Dimensions</b>	Refer to drawing
<b>Terminals</b>	Protruded positive (+) and flat negative (-) contacts
<b>Jacket</b>	Foil jacket
<b>Applications</b>	All electronic devices, e.g. toys, photographic equipment, data banks, calculators, audio appliances, remote controls, paging machines.
<b>Ambient Temperature Range</b>	Operation: -18°C ~ 50°C Recommended: 10°C ~ 25°C Storage: Not exceed 30°C
<b>Shelf Life</b>	10 years
<b>Approx. Weight</b>	11.5g

### Cross References:

GP	JIS	IEC	Energizer	Duracell	Varta
24AU	LR03	LR03	E92	MN2400	4003

### Discharge curve:




### Remarks


- 1) Store period before test shall be under 20±2°C, RH 55±20% within 30 days of manufacture.
- 2) Batteries shall not leak during the service life test before the end voltage reached.

[www.gpbatteries.com](http://www.gpbatteries.com)

Manufacturer reserves the right to alter or amend the design, model and specification without prior notice.  
Copyright© GPI International Ltd. - All rights reserved



Model No.: **GP24AU**



/	min	max
Ø	9.8	10.5
A	43.5	44.5
C	4.3	—
F	—	3.8
G	0.8	—

Dimension : mm

The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors.

Member  
Gold Peak Technology Group