



brennenstuhl®

SICHERHEITSINFORMATIONEN

SAFETY INFORMATION

DE	Sicherheitsinformationen	HU	Biztonsági információk	LT	Saugos informacija
EN	Safety information	RU	Информация о безопасности	LV	Drošības informācija
FR	Informations sur la sécurité	TR	Güvenlik bilgileri	HR	Sigurnosne informacije
NL	Veiligheidsinformatie	FI	Turvallisuustiedot	RO	Informații privind siguranța
IT	Informazioni sulla sicurezza	GR	Πληροφορίες για την ασφάλεια	BG	Информация за безопасност
SE	Säkerhetsinformation	PT	Informações de segurança	DK	Oplysninger om sikkerhed
ES	Información de seguridad	EE	Ohutusalane teave	NO	Sikkerhetsinformasjon
PL	Informacje dotyczące bezpieczeństwa	SK	Bezpečnostné informácie	UA	Інформація з техніки безпеки
CZ	Bezpečnostní informace	SI	Varnostne informacije	AR	معلومات السلامة

WWW.BRENNENSTUHL.COM

04/11/2024


120mm

brennenstuhl®

EDL BLUPD30 0919 DE 3676
2 m H05VV-F 3G1,5
3680W MAX / 16A / 220-250V~
U_c=255 V~ 50Hz

L-N: $\boxed{T3}$ U_{oc}=6,0 kV/U_p=2,0 kV
L/N-PE: $\boxed{T3}$ U_{oc}=6,0 kV/U_p=2,0 kV

3676 XX23



4 007123 682171

USB input: 200-250V~ 50/60Hz 1A Max

USB output:

USB A port: 5.0V $\equiv$ 3.0A MAX.15.0W,

9.0V $\equiv$ 2.0A MAX.18.0W, 12.0V $\equiv$ 1.5A MAX.18.0W

USB C port: 5.0V $\equiv$ 3.0A MAX.15.0W,

9.0V $\equiv$ 3.0A MAX.27.0W, 12.0V $\equiv$ 2.5A MAX.30.0W,

15.0V $\equiv$ 2.0A MAX.30.0W, 20.0V $\equiv$ 1.5A MAX.30.0W

USB A+C port: 5.0V $\equiv$ 4.8A MAX.24.0W total

5.0V $\equiv$ 2.4A MAX.12.0W for each

η _ø=85,7% / η _{10%}=82,1% / P_{0%}=0,21W

Hugo Brennenstuhl GmbH & Co.KG, Seestr.1-3, D-72074 Tübingen
lectra technik ag, Blegistrasse 13, CH-6340 Baar
service@brennenstuhl.com

Made in China

45mm



Art. 1153580210
0484638/4323

