



thermaltake

TOUGHPOWER SERIES
POWER SUPPLY

Germanium Pro RGB Series



Germanium Pro **RGB**

750W DATASHEET



thermaltake

TOUGHPower SERIES POWER SUPPLY

Germanium Pro RGB Series



Support
PCIe 12V-2X6



ATX 3.1 Compatible

Fully Modular
Etched Cables

DC to DC and LLC
Design

Smart Zero Fan

Features

- Compatible with Intel ATX 3.1 specification and designed with native PCIe Gen 5.1 12+4pin connector.
- 80 PLUS Gold Certified up to 90% efficiency.
- 750W continuous output at 40°C/104°F operating environment.
- Smart Zero Fan: minimizes undesired noise.
- Fully modular low-profile etched black cables.
- 10 LED Lights including 256 colors RGB cycle.
- Ultra Quiet 120mm hydraulic bearing fan delivers excellent airflow.
- High amperage single +12V rail design.
- DC-DC and LLC design for more precise electrical output.
- Intel C6/C7 states & ErP ready.
- Built-in industry grade protections: OCP, OVP, UVP, OPP, OTP, SCP
- Dimension: 150mm(W)x86mm(H)x140mm(D).
- 5 years warranty.

5 YEAR
Warranty



thermatake

TOUGHPower SERIES
POWER SUPPLY

Germanium Pro RGB Series

Highlighted Features

Fully Compatible With ATX 3.1 Specifications

Meets all the needs of a computer system, providing powerful and stable power.



- Supports 200% power excursion
- Reaches 60% low load efficiency
- Complies with required power supply timing standards
- Designed with native 12+4pin 12V-2X6, and bundled with a PCIe Gen 5 cable

ATX 3.1 Compatible



RGB options available at your fingertips for easy use.

Germanium Pro RGB comes with multiple lighting effects with 7 color options: Red, Green, Blue, Yellow, Purple, Light Blue, White, and 256 colors RGB cycle. (LED off mode available)





thermatake

TOUGHPower SERIES
POWER SUPPLY

Germanium Pro RGB Series

Highlighted Features




Ultra Quiet Smart Zero Fan

Adjusts the fan speed and minimizes undesired noise.

Fully Modular, Low-Profile Etched Black Cables

Makes cable management easier, reduces clutter and increases airflow inside the chassis.



High Amperage Single +12V Rail Design

Powerful single +12V rail and DC to DC design for the best compatibility.

High-Class DC to DC and LLC Circuit Design

Provides stable operation and enhanced voltage regulation.






thermaltake

TOUGHPOWER SERIES POWER SUPPLY

Germanium Pro RGB Series

Eco Design



80 PLUS® Gold Certified Efficiency

Delivers top end efficiency under real world load conditions.

Supports Energy Star 5.0* energy standard

Germanium Pro RGB series is suitable for use in Energy Star-compatible computers.

Supports Intel Deep Power Down C6 Status

Helps your PC system operate more power efficiently.





Corresponds to the EU directives on WEEE and RoHS

Thermaltake considers its full impact on the environment during manufacturing and maintains green facilities to ensure Germanium Pro RGB series meets WEEE & RoHS requirements.





Connector and Cable Specification

Connector Type	Connector Quantity		Cable Quantity	Cable Length
Main Power (20+4Pin)	X 1		X 1	550mm
ATX 12V (4+4Pin)	X 2		X 2	700mm
PCIe (6+2Pin)	X 4		X 2	600mm+150mm
PCIe (12+4Pin) 600W	X 1		X 1	600mm
SATA (5Pin)	X 6		X 2	450mm+150mm +150mm
Peripheral (4Pin)	X 4		X 1	450mm+150mm +150mm+150mm



thermaltake

TOUGHPower Series

Power Supply

Germanium Pro RGB Series

Specification

AC Input	Input Voltage: 100-240V ~				
	Input Current: 10A Max.				
	Frequency: 50Hz-60Hz				
DC Output	+3.3V	+5V	+12V	-12V	+5VSB
Max Output Current	20A	20A	62.5A	0.3A	3A
Max Output Power	100W		750W	3.6W	15W
Total Power	750W				

GENERAL INFO	
P/N	WG0750RE
Model	TPD-750AH2FXG-3
Dimension	150mm(W)x86mm(H)x140mm(D)
PFC	Active PFC
Power Good Signal	100-250 msec
Hold-Up Time	> 17msec at 80% load
Cooling System	12cm Hydraulic bearing fan
Protection	OVP/UVP/OCPP/OPP/OTP/SCP
ENVIRONMENT	
Operating Temperature	0°C to + 40°C
Operating Humidity	5% to 85%,non-condensing
Storage Temperature	-40°C to + 70°C
Storage Humidity	5% to 95%, non-condensing
MISCELLANEOUS	
Efficiency	Meet 80 PLUS® Gold at 115Vac input.
MTBF	100,000 hrs minimum
Safety Approval	CE/UKCA/ICES/TUV/LVD/RCM/CB/FCC/cTUVus/BSMI/CCC/BIS/S-MARK
PCIe CONNECTOR	
PCIe 6+2pin	4
PCIe 12+4pin (600W)	1

Total Protection

Protections	Voltage Source		
	+3.3V	+5V	+12V
Over Voltage Protection	3.76~4.3V	5.74~7.0V	13.4~15.6V
Under Voltage Protection	2.0~2.83V	3.15~4.47V	8.1~10.5V
Over Current Protection	24~55A	24~55A	70~112A
Over Power Protection	Protection at 110%~170% over peak load.		
Over Temperature Protection	Protection temperature is 50°C~65°C		
Short Circuit Protection	Short circuit placed on +5V,+12V,+3.3V,-12Vwill latch off. +5VSB will auto-recovery.		