

Datenblatt Art. 349.014

Data sheet | Fiche technique | Scheda tecnica | Fișa tehnică

CEE Adapter

Elektrische Kenngrößen		Electrical parameters	
Nennstrom / Bemessungsspannung Frequenz	32A / 400V~ 50 Hz	Rated current / rated voltage Frequency	32A / 400V~ 50 Hz
Netzanschluss		Power supply	
Zuleitung Stecker	CEE 3L+N+PE, 6h (400V/ 32A)	Supply cable Plug	CEE 3L+N+PE, 6h (400V/ 32A)
Ableitung Kupplung CEE 16A/400V~ 5-polig mit Schutzkontakt Rot 16A / 400V~, IP44		Through cable Coupling CEE 16A/400V~ 5-pole with earthing contact Red 16A / 400V~, IP44	
Weitere Produkteigenschaften		Further product attributes	
Abmessungen	320x98,5x90,5mm	Dimensions	320x98,5x90,5mm
Material Gehäuse aus Spezialkunststoff		Material Housing made of special plastic	
Lieferumfang 1x CEE Adapter		Scope of delivery 1x CEE Adapter	
Im Polybeutel		Packed in polybag	
Umgebungsbedingungen		Environmental conditions	
Umgebungstemperatur bei Montage und Nutzung Vor direkter Sonneneinstrahlung schützen.	-5°C – 35°C	Surrounding temperature during mounting and use Protect from direct sunlight.	-5°C – 35°C
Umgebungstemperatur bei Transport und Lagerung	-25°C - 60°C	Surrounding temperature during transport and storage	-25°C - 60°C
Relative Luftfeuchtigkeit (nicht kondensierend)	5 – 95%	Relative humidity (non-condensing)	5 – 95%
Schutzart	IP44	Protection type	IP44
Konformität / Approbation		Conformity / Approval	
Bauart geprüft	DIN EN 61439, IEC 60309	Type approved	DIN EN 61439, IEC 60309

