

|                           |                               |                                                                                    |
|---------------------------|-------------------------------|------------------------------------------------------------------------------------|
| 15331000                  | <b>DATA SHEET</b>             |  |
| Valid from:<br>2024-06-28 | <b>ÖLFLEX® TRAIN 331 600V</b> |                                                                                    |


## Application

ÖLFLEX® TRAIN 331 are halogen-free, highly flame retardant cables for use in railway vehicles and buses. They are designed for fixed installation and for applications, where limited movement may occur. They are particularly used in areas, where human and animal life as well as valuable property are exposed to high risk of fire hazards. ÖLFLEX® TRAIN 331 are oil-, fuel-, acid- and alkali resistant acc. to EN 50264-3-1.

Application range:

railway vehicles and buses: connecting lamps, heating equipment, switchgear, terminal boxes and power supply

## Design



|                     |                                                                                                                                                                                                                                                                                                                                                                    |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Design              | acc. to EN 50264-3-1, 600 V, M for cables $\geq 1 \text{ mm}^2$                                                                                                                                                                                                                                                                                                    |
| Norm references     | EN 50264-3-1. Code designation M<br>M = extra low temperature, extra oil and fuel resistant                                                                                                                                                                                                                                                                        |
| Classification      | EN 45545-2: Hazard Level HL1, HL2, HL3 (only for cables $0.5 \text{ mm}^2 - 240 \text{ mm}^2$ )<br>NF F 16-101: only for black cables ( $1 \text{ mm}^2 - 300 \text{ mm}^2$ ) and<br>GNYE cables ( $1 \text{ mm}^2 - 95 \text{ mm}^2$ )<br>Internal Category A1, A2, B<br>External Category A1, A2, B<br>Category C for flame propagation<br>Category F0 for smoke |
| Conductor           | fine wire strands of tinned copper acc. to IEC 60228 resp. EN 60228, Class 5                                                                                                                                                                                                                                                                                       |
| Core isolation      | electron beam cross-linked polymer compound EI 109 acc. to EN 50264-1                                                                                                                                                                                                                                                                                              |
| Core identification | black, GN/YE, red, blue, grey, brown, green, yellow, orange, white, violet                                                                                                                                                                                                                                                                                         |

## Electrical properties at 20 °C

|                                     |                                        |
|-------------------------------------|----------------------------------------|
| Nominal voltage                     | $U_0 / U$ : 0.6/1 kV AC                |
| Max. permissible operating voltage: | $U_m$ : 1.2 kV AC<br>$V_0$ : 0.9 kV DC |
| Test voltage                        | 3.5 kV AC; 8.4 kV DC                   |

|                                         |                                       |             |
|-----------------------------------------|---------------------------------------|-------------|
| Creator: HESC/PDC<br>Released: ALTE/PDC | Document: DB15331000EN<br>Version: 09 | Page 1 of 3 |
|-----------------------------------------|---------------------------------------|-------------|

We reserve all rights according to DIN ISO 16016.

PD 0019/05\_04.23EN

|                           |                               |                                                                                    |
|---------------------------|-------------------------------|------------------------------------------------------------------------------------|
| 15331000                  | <b>DATA SHEET</b>             |  |
| Valid from:<br>2024-06-28 | <b>ÖLFLEX® TRAIN 331 600V</b> |                                                                                    |

## Mechanical and thermal properties

|                           |                                                                                                                                                           |
|---------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------|
| Min. bending radius       | Cable diameter $\leq$ 12.0 mm                                                                                                                             |
|                           | for cautions bending: 3 x outer diameter<br>(one bend at end of core)<br>fixed installation: 4 x outer diameter<br>occasional flexing: 5 x outer diameter |
|                           | Cable diameter $>$ 12.0 mm                                                                                                                                |
|                           | for cautions bending: 4 x outer diameter<br>(one bend at end of core)<br>fixed installation: 5 x outer diameter<br>occasional flexing: 6 x outer diameter |
| Temperature range         | fixed installation: -45 °C up to +120°C max. conductor temp. (20.000h)<br>up to +145°C max. conductor temp. (3.000h)                                      |
|                           | occasional flexing: -35 °C up to +120°C max. conductor temp. (20.000h)                                                                                    |
|                           | - 50°C acc. to GOST 33326-2015 and<br>GOST 20.57.406-81 (method 203-1 und 205-1)                                                                          |
| Short circuit temperature | max. +200°C (5s)                                                                                                                                          |

## Fire protection acc. to EN 50264-1 / EN 45545-2 (only for cables 0.5 mm<sup>2</sup> – 240 mm<sup>2</sup>):

|                |                                                                                                                                                                         |
|----------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Classification | EN 45545-2: Hazard Level HL1, HL2, HL3                                                                                                                                  |
| Flammability   | Flame retardant acc. to IEC 60332-1-2 resp. EN 60332-1-2                                                                                                                |
|                | No flame propagation acc. to:<br>$\geq$ 12 mm: IEC 60332-3-24 resp. EN 60332-3-24<br>$>$ 6 mm and $<$ 12mm: IEC 60332-3-25 resp. EN 60332-3-25<br>$\leq$ 6 mm: EN 50305 |
| Smoke density  | acc. to EN 50264-1, light transmission: min. 70%<br>acc. to IEC 61034-2 resp. EN 61034-2                                                                                |
| Halogen-free   | acc. to IEC 60754-1 resp. EN 60754-1 (chlorine and bromine)<br>acc. to EN 60684-2 (fluorine)                                                                            |
| Corrosivity    | acc. to EN 50264-1, pH $\geq$ 4.3 and conductivity $\leq$ 10 $\mu$ S/mm<br>acc. to IEC 60754-2 resp. EN 60754-2                                                         |
| Toxicity       | acc. to EN 50264-1 ( $\leq$ 3)                                                                                                                                          |
|                | acc. to EN 50305                                                                                                                                                        |
|                | acc. to EN 45545-2 ( $\leq$ 6)                                                                                                                                          |

## Fire protection acc. to NF (only for black cables 1mm<sup>2</sup> - 300 mm<sup>2</sup> and GNYE cores 1 mm<sup>2</sup>– 95 mm<sup>2</sup>):

|                |                                                                                                                                      |
|----------------|--------------------------------------------------------------------------------------------------------------------------------------|
| Classification | NF F 16-101: Internal Category A1, A2, B<br>External Category A1, A2, B<br>Category C for flame propagation<br>Category F0 for smoke |
| Flammability   | acc. to NF C 32-070, Category C1 and C2                                                                                              |
| Smoke density  | acc. to NF X 10-702                                                                                                                  |
| Toxicity       | acc. to NF X 70-100                                                                                                                  |

|                    |                        |             |
|--------------------|------------------------|-------------|
| Creator: HESC/PDC  | Document: DB15331000EN | Page 2 of 3 |
| Released: ALTE/PDC | Version: 09            |             |

We reserve all rights according to DIN ISO 16016.

PD 0019/05\_04.23EN

|                           |                               |                                                                                    |
|---------------------------|-------------------------------|------------------------------------------------------------------------------------|
| 15331000                  | <b>DATA SHEET</b>             |  |
| Valid from:<br>2024-06-28 | <b>ÖLFLEX® TRAIN 331 600V</b> |                                                                                    |

### Fire protection acc. to NFPA 130:

Flammability FT4/IEEE1202 acc. to UL1685 (only for 1.5 mm<sup>2</sup> – 70 mm<sup>2</sup>)  
Vertical-Tray Fire-Propagation

Smoke release acc. to UL 1685

### Material properties

Ozone resistance acc. to EN 50264-3-1, method B  
acc. to EN 50305

Mineral oil resistance acc. to EN 50264-3-1

Fuel resistance acc. to EN 50264-3-1

Acid and alkali resistance acc. to EN 50264-3-1

UV resistance Acc. to EN 50525-1 are cables with black sheath suitable for a permanent outdoor use.

Tests acc. to EN 50264-3-1

EU Directives These cables are conform to the EU-Directives 2014/35/EC (Low Voltage Directive)

Environmental information These cables meet the substance-specific requirements of the EU Directive 2011/65/EU (RoHS).

| Conductor cross section<br>[mm <sup>2</sup> ] | Max. wire ø<br>[mm] | Max. conductor resistance (20°C)<br>[Ohm/km] | Conductor ø reference value<br>[mm] | Core ø<br>[mm] | Fire load reference value<br>[kJ/m] | Weight<br>[kg/km] |
|-----------------------------------------------|---------------------|----------------------------------------------|-------------------------------------|----------------|-------------------------------------|-------------------|
| 0.5                                           | 0.21                | 40.1                                         | 0.95                                | 2.15 ±0.2      | 68                                  | 9                 |
| 0.75                                          | 0.21                | 26.7                                         | 1.15                                | 2.35 ±0.2      | 78                                  | 12                |
| 1                                             | 0.21                | 20.0                                         | 1.3                                 | 2.6 ±0.2       | 84                                  | 15                |
| 1.5                                           | 0.26                | 13.7                                         | 1.6                                 | 3.0 ±0.2       | 118                                 | 22                |
| 2.5                                           | 0.26                | 8.21                                         | 2.0                                 | 3.4 ±0.2       | 143                                 | 33                |
| 4                                             | 0.31                | 5.09                                         | 2.7                                 | 4.0 ±0.2       | 170                                 | 49                |
| 6                                             | 0.31                | 3.39                                         | 3.2                                 | 4.5 ±0.2       | 199                                 | 70                |
| 10                                            | 0.41                | 1.95                                         | 4.2                                 | 5.5 ±0.2       | 253                                 | 112               |
| 16                                            | 0.41                | 1.24                                         | 5.2                                 | 6.7 ±0.2       | 330                                 | 174               |
| 25                                            | 0.41                | 0.795                                        | 6.5                                 | 8.4 ±0.2       | 528                                 | 273               |
| 35                                            | 0.41                | 0.565                                        | 7.7                                 | 9.6 ±0.2       | 617                                 | 374               |
| 50                                            | 0.41                | 0.393                                        | 9.7                                 | 11.5 ±0.3      | 833                                 | 531               |
| 70                                            | 0.51                | 0.277                                        | 11.4                                | 13.4 ±0.3      | 1077                                | 739               |
| 95                                            | 0.51                | 0.210                                        | 13.4                                | 15.3 ±0.3      | 1233                                | 988               |
| 120                                           | 0.51                | 0.164                                        | 15.0                                | 17.0 ±0.3      | 1473                                | 1243              |
| 150                                           | 0.51                | 0.132                                        | 17.0                                | 19.2 ±0.4      | 1915                                | 1558              |
| 185                                           | 0.51                | 0.108                                        | 18.5                                | 21.2 ±0.4      | 2445                                | 1927              |
| 240                                           | 0.51                | 0.0817                                       | 22.0                                | 24.2 ±0.4      | 2968                                | 2487              |
| 300                                           | 0.51                | 0.0654                                       | 23.2                                | 26.6 ±0.4      | 3321                                | 3085              |

|                                         |                                       |             |
|-----------------------------------------|---------------------------------------|-------------|
| Creator: HESC/PDC<br>Released: ALTE/PDC | Document: DB15331000EN<br>Version: 09 | Page 3 of 3 |
|-----------------------------------------|---------------------------------------|-------------|

We reserve all rights according to DIN ISO 16016.

PD 0019/05\_04.23EN