



| LOC | DIST | REVISIONS |     |               |           |      |
|-----|------|-----------|-----|---------------|-----------|------|
| CE  | 16   | P         | LTR | DESCRIPTION   | DATE      | DWN  |
|     |      |           | C   | ECR-14-011637 | 14AUG2014 | HZ   |
|     |      |           |     |               |           | APVD |
|     |      |           |     |               |           | RZ   |

- 1

MAXIMUM CONNECTOR INSERTION LOSS IS 0.5dB PLUS CABLE ATTENUATION OF 3.5dB/km AT 850nm. MEASURE AGAINST A REFERENCE LEAD
2. TEST DATA PROVIDED WITH EACH ASSEMBLY.
3. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TEC-138-702.



|                                                                                       |  |                                        |     |                  |             |                                                                                                       |                                                                                                                     |  |  |
|---------------------------------------------------------------------------------------|--|----------------------------------------|-----|------------------|-------------|-------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------|--|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  |                                        | DWN | LG EBY           | 23MAR09     |  TE Connectivity |                                                                                                                     |  |  |
|                                                                                       |  |                                        | CHK | J.DUNCAN         | 23MAR09     |                                                                                                       |                                                                                                                     |  |  |
| DIMENSIONS:                                                                           |  | TOLERANCES UNLESS OTHERWISE SPECIFIED: |     | APVD             | D. BAECHTLE | 23MAR09                                                                                               | NAME                                                                                                                |  |  |
| METERS [INCHES]                                                                       |  |                                        |     | PRODUCT SPEC     |             |                                                                                                       |                                                                                                                     |  |  |
|  |  | 0 PLC ± -                              |     | APPLICATION SPEC |             |                                                                                                       | CABLE ASSEMBLY, FIBER OPTIC,<br>50/125, OM3, 2 FIBER BREAKOUT CABLE,<br>SEALED CIRCULAR LC DUPLEX (ODVA), BOTH ENDS |  |  |
|                                                                                       |  | 1 PLC ± -                              |     |                  |             |                                                                                                       |                                                                                                                     |  |  |
|                                                                                       |  | 2 PLC ± -                              |     |                  |             |                                                                                                       |                                                                                                                     |  |  |
|                                                                                       |  | 3 PLC ± -                              |     |                  |             |                                                                                                       |                                                                                                                     |  |  |
|                                                                                       |  | 4 PLC ± -                              |     |                  |             |                                                                                                       | SIZE                                                                                                                |  |  |
|                                                                                       |  | ANGLES ± -                             |     |                  |             |                                                                                                       |                                                                                                                     |  |  |
| MATERIAL                                                                              |  | FINISH                                 |     | WEIGHT           |             |                                                                                                       | CAGE CODE                                                                                                           |  |  |
| -                                                                                     |  | -                                      |     | -                |             |                                                                                                       | DRAWING NO                                                                                                          |  |  |
|                                                                                       |  |                                        |     |                  |             |                                                                                                       | RESTRICTED TO                                                                                                       |  |  |
|                                                                                       |  |                                        |     | A2               |             |                                                                                                       | 00779                                                                                                               |  |  |
|                                                                                       |  |                                        |     | CUSTOMER DRAWING |             |                                                                                                       | C-2064915                                                                                                           |  |  |
|                                                                                       |  |                                        |     |                  |             |                                                                                                       | SCALE                                                                                                               |  |  |
|                                                                                       |  |                                        |     |                  |             |                                                                                                       | NTS                                                                                                                 |  |  |
|                                                                                       |  |                                        |     |                  |             |                                                                                                       | SHEET                                                                                                               |  |  |
|                                                                                       |  |                                        |     |                  |             |                                                                                                       | 1 of 2                                                                                                              |  |  |
|                                                                                       |  |                                        |     |                  |             |                                                                                                       | REV                                                                                                                 |  |  |
|                                                                                       |  |                                        |     |                  |             |                                                                                                       | C                                                                                                                   |  |  |

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOCCE

DIST16

REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|-------------|------|-----|------|
|   | -   | SEE SHEET 1 | -    | -   | -    |

|             |                   |                 |             |
|-------------|-------------------|-----------------|-------------|
| 1.38        | 250.0±2.50        | [9842.5±98.4]   | 8-2064915-2 |
| 0.85        | 100.0±1.00        | [3937.0±39.4]   | 8-2064915-1 |
| 1.03        | 152.40±1.50       | [6000.0±60.0]   | 8-2064915-0 |
| 0.77        | 76.00±0.76        | [2992.1±29.9]   | 7-2064915-6 |
| 0.76        | 75.00±0.75        | [2953.0±30.0]   | 7-2064915-5 |
| 0.71        | 61.00±0.61        | [2400.0±24.0]   | 6-2064915-1 |
| 0.68        | 50.00±0.50        | [1969.0±20.0]   | 5-2064915-0 |
| 0.64        | 40.00±0.40        | [1574.80±15.75] | 4-2064915-0 |
| 0.64        | 39.00±0.35        | [1535.43±13.78] | 3-2064915-9 |
| 0.63        | 38.00±0.35        | [1496.06±13.78] | 3-2064915-8 |
| 0.63        | 37.00±0.35        | [1456.69±13.78] | 3-2064915-7 |
| 0.63        | 36.00±0.35        | [1417.32±13.78] | 3-2064915-6 |
| 0.62        | 35.00±0.35        | [1377.95±13.78] | 3-2064915-5 |
| 0.62        | 34.00±0.30        | [1338.58±11.81] | 3-2064915-4 |
| 0.62        | 33.00±0.30        | [1299.21±11.81] | 3-2064915-3 |
| 0.61        | 32.00±0.30        | [1259.84±11.81] | 3-2064915-2 |
| 0.61        | 31.00±0.30        | [1220.47±11.81] | 3-2064915-1 |
| 0.61        | 30.00±0.30        | [1181.10±11.81] | 3-2064915-0 |
| 0.60        | 29.00±0.30        | [1141.73±11.81] | 2-2064915-9 |
| 0.60        | 28.00±0.30        | [1102.36±11.81] | 2-2064915-8 |
| 0.59        | 27.00±0.30        | [1062.99±11.81] | 2-2064915-7 |
| 0.59        | 26.00±0.30        | [1023.62±11.81] | 2-2064915-6 |
| 0.59        | 25.00±0.30        | [984.25±11.81]  | 2-2064915-5 |
| 0.58        | 24.00±0.30        | [944.88±11.81]  | 2-2064915-4 |
| 0.58        | 23.00±0.30        | [905.51±11.81]  | 2-2064915-3 |
| 0.58        | 22.00±0.30        | [866.14±11.81]  | 2-2064915-2 |
| 0.57        | 21.00±0.30        | [826.77±11.81]  | 2-2064915-1 |
| 0.57        | 20.00±0.30        | [787.40±11.81]  | 2-2064915-0 |
| 0.57        | 19.00±0.30        | [748.03±11.81]  | 1-2064915-9 |
| 0.56        | 18.00±0.30        | [708.66±11.81]  | 1-2064915-8 |
| 0.56        | 17.00±0.30        | [669.29±11.81]  | 1-2064915-7 |
| 0.56        | 16.00±0.30        | [629.92±11.81]  | 1-2064915-6 |
| 0.55        | 15.00±0.15        | [590.55±5.91]   | 1-2064915-5 |
| 0.55        | 14.00±0.15        | [551.18±5.91]   | 1-2064915-4 |
| 0.55        | 13.00±0.15        | [511.81±5.91]   | 1-2064915-3 |
| 0.54        | 12.00±0.15        | [472.44±5.91]   | 1-2064915-2 |
| 0.54        | 11.00±0.15        | [433.07±5.91]   | 1-2064915-1 |
| 0.54        | 10.00±0.15        | [393.70±5.91]   | 1-2064915-0 |
| 0.53        | 9.00±0.15         | [354.33±5.91]   | 2064915-9   |
| 0.53        | 8.00±0.15         | [314.96±5.91]   | 2064915-8   |
| 0.52        | 7.00±0.08         | [275.59±3.15]   | 2064915-7   |
| 0.52        | 6.00±0.08         | [236.22±3.15]   | 2064915-6   |
| 0.52        | 5.00±0.08         | [196.85±3.15]   | 2064915-5   |
| 0.51        | 4.00±0.08         | [157.48±3.15]   | 2064915-4   |
| 0.51        | 3.00±0.05         | [118.11±1.97]   | 2064915-3   |
| 0.51        | 2.00±0.05         | [78.74±1.97]    | 2064915-2   |
| 0.50        | 1.00±0.05         | [39.37±1.97]    | 2064915-1   |
| MAX IL (dB) | L METERS [INCHES] |                 | PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: METERS [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

MATERIAL -

FINISH -

DWN LG EBY 23MAR09

CHK J.DUNCAN 23MAR09

APVD D. BAECHTLE 23MAR09

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME CABLE ASSEMBLY, FIBER OPTIC, 50/125, OM3, 2 FIBER BREAKOUT CABLE, SEALED CIRCULAR LC DUPLEX (ODVA), BOTH ENDS

SIZE A2

CAGE CODE 00779

DRAWING NO C=2064915

RESTRICTED TO -

SCALE NTS

SHEET 2 of 2

REV C

D

C

B

A

2064915

B

A

1471-9 (3/11)