




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CE	-		B1	ADD 9-1 FOR 0.3M LENGTH	14AUG15	SW	RZ

1 MAXIMUM CONNECTOR INSERTION LOSS IS 0.5dB PLUS CABLE ATTENUATION OF 3.5dB/km AT 850nm. (SEE TABLE)

2. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TEC-138-702.

0.85	100.00±1.00	[3937.0±39.0]	9-2064862-9
0.50	0.30±0.03	[11.8±1.2]	9-2064862-1
0.68	50.00±0.50	[1969.0±20.0]	5-2064862-0
0.64	40.00±0.40	[1575.0±16.0]	4-2064862-0
0.64	39.00±0.39	[1535.4±15.0]	3-2064862-9
0.63	38.00±0.38	[1496.1±15.0]	3-2064862-8
0.63	37.00±0.37	[1456.7±15.0]	3-2064862-7
0.63	36.00±0.36	[1417.3±14.0]	3-2064862-6
0.62	35.00±0.35	[1377.9±14.0]	3-2064862-5
0.62	34.00±0.34	[1338.6±13.0]	3-2064862-4
0.62	33.00±0.33	[1299.2±13.0]	3-2064862-3
0.61	32.00±0.30	[1259.8±12.0]	3-2064862-2
0.61	31.00±0.30	[1220.5±12.0]	3-2064862-1
0.61	30.00±0.30	[1181.0±12.0]	3-2064862-0
0.60	29.00±0.30	[1141.7±12.0]	2-2064862-9
0.60	28.00±0.30	[1102.4±12.0]	2-2064862-8
0.59	27.00±0.30	[1063.0±12.0]	2-2064862-7
0.59	24.00±0.30	[944.9±12.0]	2-2064862-6
0.59	25.00±0.30	[984.2±12.0]	2-2064862-5
0.58	24.00±0.30	[944.9±12.0]	2-2064862-4
0.58	23.00±0.30	[905.5±12.0]	2-2064862-3
0.58	22.00±0.30	[866.1±12.0]	2-2064862-2
0.57	21.00±0.30	[826.8±12.0]	2-2064862-1
0.57	20.00±0.30	[787.0±12.0]	2-2064862-0
0.57	19.00±0.30	[748.0±12.0]	1-2064862-9
0.56	18.00±0.30	[708.7±12.0]	1-2064862-8
0.56	17.00±0.17	[669.3±7.0]	1-2064862-7
0.56	16.00±0.16	[629.9±7.0]	1-2064862-6
0.55	15.00±0.15	[590.6±6.0]	1-2064862-5
0.55	14.00±0.15	[551.2±6.0]	1-2064862-4
0.55	13.00±0.15	[511.8±6.0]	1-2064862-3
0.54	12.00±0.15	[472.4±6.0]	1-2064862-2
0.54	11.00±0.15	[433.1±6.0]	1-2064862-1
0.54	10.00±0.15	[394±6.0]	1-2064862-0
0.53	9.00±0.15	[354.6±6.0]	2064862-9
0.53	8.00±0.15	[315.0±6.0]	2064862-8
0.52	7.00±0.08	[275.6±3.0]	2064862-7
0.52	6.00±0.08	[236.2±3.0]	2064862-6
0.52	5.00±0.08	[196.9±3.0]	2064862-5
0.51	4.00±0.08	[157.5±3.0]	2064862-4
0.51	3.00±0.05	[118.1±2.0]	2064862-3
0.51	2.00±0.05	[78.7±2.0]	2064862-2
0.50	1.00±0.05	[39.4±2.0]	2064862-1

INSERTION LOSS (dB)1	L METERS [INCHES]	PART NUMBER
----------------------	-------------------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.BRIGGS 12MAY2010	TE Connectivity	
DIMENSIONS: METERS [INCHES]		CHK J.DUNCAN 08JUN2010		
	TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD J.DUNCAN 08JUN2010	NAME	
		PRODUCT SPEC	CABLE ASSEMBLY, FIBER OPTIC, 2.0mm OFNR, OM3, LC DUPLEX TO LC DUPLEX	
		APPLICATION SPEC	-	
MATERIAL	FINISH	WEIGHT	SIZE A2	CAGE CODE 00779
-	-	-	DRAWING NO C-2064862	RESTRICTED TO -
CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1
			REV B1	