
© – TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D6	REVISED PER ECR-25-255998	12SEP2025	SA	DSC



1 MUST BE CRIMPED WITH A 22–18 OR 22–16 P.I.D.G. (RED) TOOL.

2 WIRE INSULATION DIA: 1.3–2.7 [.050–.105]

3 TONGUE MATERIAL THK: 0.68±0.051 [.027±.002]

4 BODY & SLEEVE: TIN PLATE PER ASTM B545.

5 MATERIAL: BODY & SLEEVE– CU PER ASTM B152
INSULATION – NYLON, COLOR – YELLOW

6 APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.

7 NOTE DELETED

8 MEETS MS25036–144, CLASS 1

9 NOTE DELETED

1 KIT = 50 PIECES	LOOSE PIECE	6–52189–0
1000	LOOSE PIECE	8 52189
QTY	PACKAGE TYPE	PART NO.

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1–800–522–6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1–800–722–1111
FOR ORDER ENTRY	1–800–526–5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

MAX RECOMMENDED OPERATING TEMPERATURE: 105°C MAX

VOLTAGE RATING: N/A

CIRCULAR MIL AREA: 0.10–0.26mm² [202–509] STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± –
1 PLC	± –
2 PLC	± 0.20[.008]
3 PLC	± –
4 PLC	± –
ANGLES	± –

MATERIAL – 4

FINISH – 5

DWN	JR RUTH	07FEB08
CHK	T MICHIELUTTI	29MAY07
APVD	T MICHIELUTTI	29MAY07
PRODUCT SPEC	—	
APPLICATION SPEC	—	
WEIGHT	—	

TE Connectivity

NAME: TERMINAL, RECTANGULAR TONGUE, PIDG, WIRE SIZE: 26–24 AWG

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-52189	—

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV D6