

© – TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	J	REVISED PER ECR-23-181664	08AUG2023	AP	DSC





AMP WIRE RANGE	E13288 Listed
16–14 AWG SOLID OR STRANDED	16–14 AWG SOLID OR STRANDED

LR7189 Certified	MILITARY P/N AND CLASS
16–14 AWG SOLID OR STRANDED	NOT APPLICABLE

1. STAMP AMP 16–14* APPROX AS SHOWN
2. TIN PLATE 0.00254[.000100] MIN EXT THK PER ASTM B545
3. CLEANED, UNPLATED
4. MATERIAL: COPPER PER ASTM B152, ANNEALED
5. BODY MATERIAL THK: 0.787±0.051[.031±.002]
6. DIMPLE STAMP MARK OPTIONAL

FINISH	QUANTITY	PACKAGING TYPE	PART NO
3	1000	LOOSE PIECE	34123-2
2	100	LOOSE PIECE, BOX	8-34123-1
	5000	ON TAPE	2-34123-1
	1000	LOOSE PIECE	34123

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX RECOMMENDED OPERATING TEMPERATURE: 170° C [338°F]
		VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 1.04–2.62mm² [2,050–5,180] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± 0.127[.005]
4 PLC ± –
ANGLES ± –

MATERIAL 4

FINISH: SEE TABLE

DWN	TA BRINKMAN	3-17-93
CHK	DA PATTERSON	3-17-93
APVD	DE MILLER	3-17-93
PRODUCT SPEC	UL 486A-B	
APPLICATION SPEC	–	
WEIGHT	–	

TE Connectivity

NAME: TERMINAL, RING TONGUE, SOLISTRAND WIRE SIZE: 16–14 AWG

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-34123	–

CUSTOMER DRAWING | SCALE 8:1 | SHEET 1 OF 1 | REV J

34123