


# LED SL-RGBW 560 S-PUd-M8-65

Art. Nr. 1-000000-06918

Ktl. Nr. 15070975

EAN Nr. 4260654163308



## Normen / Norms

DIN EN 60598-1 :2021/A11:2022

DIN EN 60529 :1991/A2:2013/AC:2019-02

DIN EN 55015:2019+A11:2020

DIN EN IEC 63000:2018

DIN EN 61547:2009

DIN EN 62471:2009




## Elektrische Rahmenbedingungen / Electrical characteristic

|                             |                               |
|-----------------------------|-------------------------------|
| Netzanschluss / Main Supply | 24 VDC                        |
| Leistung / Power (W/R/G/B)  | 17,2W / 8W / 7,9W / 7,7W      |
| Dimmbar / Dimmable          | extern PWM                    |
| Anschluss / Connection Type | Flansch, M8, 5-Pol, B-Codiert |
| Kaskadierbar / Cascadable   | Nein                          |
| Polbild                     |                               |


## Licht / Light

|                                      |                              |
|--------------------------------------|------------------------------|
| Bestückt / Fitted With               | LED                          |
| Lichtfarbe / Light Colour            | 6500 K                       |
| Lichtstrom / Luminous Flux (W/R/G/B) | 895lm / 131lm / 339lm / 77lm |
| Effizienz / Efficiency               | 35 lm/W                      |
| Abstrahlwinkel / Beam Angle          | 100°                         |
| Farbtreue / Colour Rendering         | RA / CRI 80                  |
| Photobiological Safety               | RG-1                         |



## Mechanik / Mechanics

|                                      |               |
|--------------------------------------|---------------|
| Gehäuse / Housing                    | Aluminium     |
| Abdeckung / Cover                    | PU, Diffus    |
| Befestigung / Fastening              | Starr         |
| Gewicht(Netto) / Weight(Net)         | 0,53 kg       |
| Betriebstemperatur / Operating Temp. | -20°C / +50°C |
| Lebensdauer / Lifetime               | min. 60000 h  |
| Zubehör / Equipment                  | -             |



a= 623mm b= 635mm