





POS.	A -0.76	B -0.25	C	Part NO.
9	31.19	16.46	25.00 $+0.12$ -0.13	164A16569X
15	39.52	24.79	33.30 $+0.15$ -0.1	164A16579X
25	53.42	38.50	47.04 ± 0.13	164A16589X
37	69.70	54.96	63.50 ± 0.13	164A16599X



(b) NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80pin NICKEL
- INSULATORS: PBT GF UL 94 V-0, BLACK
- CONTACTS: COPPER ALLOY
PLATING: 8pin HARD GOLD over min. 50pin NICKEL
- THREADED SPACER CLIP: COPPER ALLOY; min. 200µin TIN over 80pin NICKEL
PCB-HOLE: $\varnothing 3.1 \pm 0.1$; PCB THICKNESS 1.6mm
- COLLAR: COPPER ALLOY; min. 200µin TIN over 80pin NICKEL
- P.C.B. HOLE DRILLINGS ON DRAWING NO.: 16K11IUA
- MAXIMUM TORQUE VALUE FOR THREAD: 6in.LB
- CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

Directive 2002/95/EC
„RoHS“
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY, WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

3 x b	Ä3304	03.03.09	Petker
a	Origin		
rev.	description	date	name

tolerance	dim. in mm
2000	date
drawn	20.11.
appd.	20.11.
norm	DIN 41652
d-old	

scale:	2:1 (5:1)
material:	SEE NOTES
title:	D-SUB FEMALE 9-37pos. PIN VERSION with threaded spacer clip
dwg no:	AutoCAD 2000
part no:	SEE TABLE

CONEC

DIN-A
3
sh: 1/1