

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


ALL RIGHTS RESERVED.

© COPYRIGHT - By -

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		P	REVISED PER ECO-11-004835	11MAR11	RK	HMR

D

OPENING FOR CABLE
(SEE DASH NO. FOR DIA.)



C


SIZE IDENTIFICATION LETTER
MOLDED IN APPROXIMATE AREA
SHOWN, SEE TABLE

#4-40 HEX NUT
(QTY. 2)
MATL: CARBON STEEL
FINISH: 2

#4-40 FIL HD SCREW
(QTY. 2)
MATL: STEEL
FINISH: 2

1.920
±.015


AMP LOGO



TEXTURED
FINISH

B

1. PARTS PACKAGED UNASSEMBLED, AS A UNIT KIT.
2. ZINC PLATED .000200-.000400 THICK, CLEAR CHROMATE COATING.



D

C

5745173

B

D	.280	5745173-5
G	.350	5745173-4
K	.430	5745173-3
M	.480	5745173-2
P	.530	5745173-1
NECK SIZE IDENT	MAX CABLE DIA	PART NUMBER

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MCMASTER	12AUG05	 TE Connectivity						
		CHK C. ROHDE	12AUG05							
DIMENSIONS: INCHES	TOLERANCES, UNLESS OTHERWISE SPECIFIED:	APVD M. WALMSLEY	12AUG05	NAME	CABLE CLAMP KIT, SIZE 3, 180 DEGREE, AMPLIMITE					
	0 PLC ± -	PRODUCT SPEC								
	1 PLC ± -	—								
	2 PLC ± -	APPLICATION SPEC								
	3 PLC ± -.005	—								
	4 PLC ± -			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
MATERIAL	FINISH	WEIGHT	—	A2	00779	C=5745173	—			
SEE CALLOUTS	SEE CALLOUTS	CUSTOMER DRAWING			SCALE	1:1	SHEET	1 of 1	REV	P