CERTIFICATE

FOR EUROPEAN PRODUCT SAFETY

Reference No. SE-S-2100505

Installation coupler for fixed installation

Type designation:	2379237-*, 1-2379237-*, 2379238-*, 1-2379238-*, 2379239-* 1-2379239-*, 2379240-*, 1-2379240-*, 2359422-*, 1-2359422-* 2359518-*, 1-2359518-*, 2359420-*, 2359421-*
Certificate holder:	Tyco Electronics Austria GmbH Schrackstrasse 1, 3830 Waidhofen / Thaya Austria
The product complies with the standard(s):	EN IEC 61535:2019
Date of expiry:	13 April, 2026
EU Directive information:	According to the principle of presumption of conformity, this certificate constitutes support for an EC Declaration of Conformity and CE marking according to the Low Voltage Directive 2014/35/EU.

Additional information in Appendix

Certification Body: Intertek Semko AB, Product Certification **Place:** Kista - Stockholm

Signed: **Date:** 13 April, 2021

Leif Mattsson

This Certificate is for the exclusive use of Intertek's client and is provided pursuant to the agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this Certificate. Only the Client is authorized to permit copying or distribution of this Certificate and then only in its entirety. Any use of the Intertek name or one of its marks for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek.

APPENDIX:

Reference No. SE-S-2100505

Technical Data:

Type designation	2379237-*, 1-2379237-*, 2379238-*, 1-2379238-*, 2379239-* 1-2379239-*, 2379240-*, 1-2379240-*, 2359422-*, 1-2359422-* 2359518-*, 1-2359518-*, 2359420-*, 2359421-*
Rated voltage (V)	500 VAC
Rated current (A)	Max 25A
IP-Class	IP68
Number of terminals	3
Rated connecting cap	1,5-4 mm^2
Trademark	TE
Order number	2102877
Product information	Rated currents for connectors: 16A with 1,5 mm^2 / 20A with 2,5 mm^2 / 25A with 4 mm^2

Product type references (not marked)
2379237-*: in-line female connector 2359418-1, screw terminals, cable gland 2363547-1 (11.0-15.0 mm)
1-2379237-*: in-line female connector 2359418-1, screw terminals, cable gland 2363547-2 (7.0-10.0 mm)
2379238-*: in-line male connector 2359419-1, screw terminals, cable gland 2363547-1 (11.0-15.0 mm)
1-2379238-*: in-line male connector 2359419-1, screw terminals, cable gland 2363547-2 (7.0-10.0 mm)
2379239-*: in-line female connector 2365125-1, crimp terminals, cable gland 2363547-1 (11.0-15.0 mm)
1-2379239-*: in-line female connector 2365125-1, crimp terminals, cable gland 2363547-2 (7.0-10.0 mm)
2379240-*: in-line male connector 2365129-1, crimp terminals, cable gland 2363547-1 (11.0-15.0 mm)
1-2379240-*: in-line male connector 2365129-1, crimp terminals, cable gland 2363547-2 (7.0-10.0 mm)

2359422-*: panel mounted female connector 2359422-1, screw terminals
1-2359422-*: panel mounted female connector 2359422-1, crimp terminals
2359518-*: panel mounted male connector 2359518-1, screw terminals
1-2359518-*: panel mounted male connector 2359518-1, crimp terminals

2359420-*: 3-way junction (1 male + 2 female), rated current max 25A
2359421-*: 4-way junction (1 male + 3 female), rated current max 25A

"*" denotes polarization key (1 or 2)

This Certificate is for the exclusive use of Intertek's client and is provided pursuant to the agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this Certificate. Only the Client is authorized to permit copying or distribution of this Certificate and then only in its entirety. Any use of the Intertek name or one of its marks for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek.

APPENDIX:

Reference No. SE-S-2100505

Manufacturing Sites:

According to the principle of presumption of conformity, this certificate, which includes production control, constitutes support for an EC Declaration of Conformity and CE marking according to the Low Voltage Directive 2014/35/EU.

This presumption can expire before end of validity of this certificate due to new issued Standard or Amendment and changes within the EU legislation.

Certification Body: Intertek Semko AB, Product Certification **Place:** Kista - Stockholm

Signed: **Date:** 13 April, 2021

Leif Mattsson

This Certificate is for the exclusive use of Intertek's client and is provided pursuant to the agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this Certificate. Only the Client is authorized to permit copying or distribution of this Certificate and then only in its entirety. Any use of the Intertek name or one of its marks for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek.