

**Cabtite (cable entry system)
CABTITE CGS M20 BK**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



For metric M20 to M63 through-holes, the Cabtite cable entry system offers separable cable glands for cables with and without plugs. In case of maintenance or changes in the system, pre-assembled cables with diameters of 2 to 35 mm can be inserted quickly and safely in panels or enclosures. Reliable sealing of IP66 in accordance with DIN EN 60529 and an absolutely secure fitting (strain relief based on DIN EN 62444) is ensured by placing slotted sealing elements with a wave cut around the cable before being inserted into one of the two halves of the cable gland. The separable system ensures easy and fast installation. After inserting the sealing element, the two halves of the cable gland are simply snapped together. A locknut, which is also separable, on the inside of the panel ensures a reliable and secure hold.

Általános rendelési adatok

Típus	CABTITE CGS M20 BK
Rendelési szám	2584200000
Verzió	leválasztható tömszelence, Cabtite (cable entry system), Poliamid, üvegszál-erősítésű, mélyfekete, Magasság: 23.7 mm, M 20, IP54, IP65, IP66
GTIN (EAN)	4050118616576
Menny.	10 Stück

Cabtite (cable entry system)
CABTITE CGS M20 BK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Műszaki adatok
Méretetek és tömegek

Hossz	38,7 mm	Hossz, inch	1,524 inch
Szélesség	40 mm	Szélesség (coll)	1,575 inch
Magasság	23,7 mm	Magasság (coll)	0,933 inch
Mélység	38,7 mm	Mélység (coll)	1,524 inch
Nettó tömeg	11,05 g		

General information

Meghúzási nyomaték, min.	3,8 Nm	Meghúzási nyomaték, max.	4 Nm
UL 94 éghetőségi osztály	V-0	Sealing element	1 small sealing element
Opening diameter	20 mm	Külső menet	M 20
Menet hossza	15 mm	Menetemelkedés	1,5 mm
AF 1. méret	38 mm	AF 2. méret	28 mm
Halogén	Nem	Szilikon	Nem
Tömítés	TPE	Anyag	Poliamid, üvegszál-erősítésű

Besorolások

ETIM 6.0	EC000441	eClass 6.2	27-14-92-01
eClass 9.0	27-14-44-32	eClass 9.1	27-14-44-32

Jóváhagyások

ROHS	Megfelel
------	----------

Letöltések

Engineering Data	STEP
User Documentation	Installation Instructions