

## Kabelconnectoren - ST-08S1N8A8K03S - 1613371

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Kabelconnectoren, recht, SPEEDCON-vergrendeling, M17, aantal polen: 8, soort contact: bus, crimpaansluiting, afgeschermd: ja, kabeldiameter: 5 mm...9 mm

### Key commercial data

package_quantity	1
GTIN	4046356708654

### Technical data

#### Algemeen

Opmerking	bestelinformatie crimpcontacten Ø 1 mm separaat bestellen
type vergrendeling	SPEEDCON-vergrendeling
draairichting contactkamernummering	standaard
polarisatie	N
type contactaansluiting	crimpaansluiting
soort contacten	bus
aantal polen	8
contactdiameter vermogenscontacten	1 mm
nominale stroom per vermogenscontact bij 25 °C	3,6 A
kabelinvoer	5 mm ... 9 mm

#### Omgevingsomstandigheden

beschermklasse	IP67
----------------	------

#### Opgave volgens DIN EN 61984:2001

max. opstelhoogte	3000 m
nom./bedrijfsspanning vermogenscontacten	60 V
teststootspanning vermogenscontacten	1,5 kV
overspanningscategorie vermogenscontacten	II
vervuilingsgraad vermogenscontacten	3

### classifications

#### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701

# Kabelconnectoren - ST-08S1N8A8K03S - 1613371

## classifications

### eCl@ss

eCl@ss 5.0	27260701
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27440102

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002635
ETIM 5.0	EC002635

### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

## approvals

cUL Recognized /

### Approval details

cUL Recognized	
nomiale spanning UN	60 V
nomiale stroom IN	1 A
mm <sup>2</sup> /AWG/kcmil	

## accessories

### Crimpcontact

ST-10KS010 - 1618239



## Kabelconnectoren - ST-08S1N8A8K03S - 1613371

accessories

ST-10KS020 - 1618251



ST-10KS030 - 1618254



SF-10KS320 - 1607031



SF-10KS350 - 1607032



SF-10KS330 - 1607358



SF-10KS360 - 1607361



## Kabelconnectoren - ST-08S1N8A8K03S - 1613371

accessories

---

### Beschermkappen

ST-Z0007 - 1607777



---

### Montagemateriaal

ST-Z0016 - 1617993



---

ST-Z0017 - 1618049



---

ST-Z0018 - 1618050




---

Drawings

## Kabelconnectoren - ST-08S1N8A8K03S - 1613371

Maatschets



# Kabelconnectoren - ST-08S1N8A8K03S - 1613371

schematekening

