BUSINESS & PRODUCTIVITY PCS

Cubi 5 1M

CUBI 5 1MA-661AT


PATH TO THE FUTURE



Picture and logos

SELLING POINTS

- Windows 11 HomeMSI empfiehlt Windows 11 Pro für Unternehmen
- 0,83 Liter mit VESA-montierbarem Design
- Bis zu Intel® Core™ 7 Prozessor 150U
- Dual-Channel-DDR5-SO-DIMM-Speicher
- Thunderbolt™ 4 und Dual-LAN (2,5G und 1G)
- Unterstützung für drei Displays und einfach zu aktualisierendes Design
- MSI Power Link: Der Cubi 5 1M kann über die MSI Power Link-Technik über einen Monitor mit Strom versorgt werden.
- MSI AI Engine: Optimieren Sie die Benutzererfahrung ohne manuelle Konfiguration.
- Der Power Meter ermöglicht mit einem Klick Energiesparen, die Berechnung der CO2-Emissionen und die Schätzung der Stromkosten.
- Ausgestattet mit FSC™-zertifiziertem Karton; Abfallreduzierung durch recycelte Formmasse (100 % recycelbar); Hergestellt mit 99 % erneuerbarer Energie im Werk



1. 1x Mikrofon/Kopfhörer Kombo
2. 2x USB 10Gbps Typ A
3. 1x Thunderbolt 4 (USB Typ C)
4. 1x Power button
5. 1x Kensington Lock & Externer Power Knopf Pin Anschluss
6. 1x HDMI™ Ausgang
7. 1x DP Ausgang (1.4)
8. 2x RJ45
9. 2x USB 10Gbps Typ A
10. 1x Stromanschluss

"2026-08-19 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products."

BUSINESS & PRODUCTIVITY PCS

Cubi 5 1M

CUBI 5 1MA-661AT

SPECIFICATION

Betriebssystem	Betriebssystem	Windows 11 Home
	Operating Systems	Windows 11 Home
Prozessor	CPU Number	Intel Core 5 Processor 120U
	CPU Clock	1.4GHz
	CPU Cores	10
	TDP	15W
	Cache	12 MB Intel® Smart Cache
	Threads	12
	Max Turbo Frequency	up to 5.00 GHz
	CPU Cooler	Air cooling
	Platform TOPS	N/A
	NPU TOPS	N/A
Model	MKT Name	Cubi 5 1MA
	MKT Spec	Cubi 5 1MA-661AT
	Color	ID1/Black-Black-Black
	SKU Number	00B0A831-661
	Part No	9S6-B0A831-661
	Model	B0A8
Chipsatz	Chipsets	Soc
Arbeitsspeicher	Memory Size	8GB(8GB*1)
	Memory Type	DDR4 SDRAM
	Memory Speed	1600(3200)MHz
	Module Type	SO-DIMM
	Memory Slot(Total)	2
	Memory Slot(Free)	1
	Max Capacity	Max 64GB
	Memory Slot (Total/Free)	2/1
Grafik	GPU1 VRAM Size	N/A
	VGA I/O Port	N/A
	GPU1 Vendor	N/A
	GPU1 MKT Name	N/A
	GPU1 Number	N/A
Speicher	SSD Interface	PCIe GEN4x4 NVMe
	SSD Form Factor	M.2 2280 M-KEY
	SSD Config	500GB*1
	SSD Size	500GB
	HDD1 Interface	N/A
	HDD1 Form Factor	N/A
	HDD1 Size	N/A
	HDD1 RPM	N/A
	ODD(Type)	N/A
	ODD Height	N/A
	ODD Type	N/A
	M.2 slots (Total/Free)	1/0
	2.5" Drive Bays (Total/Free)	1/1
	3.5" Drive Bays (Total/Free)	0/
	M.2 slots(Total)	1
	M.2 slots(Free)	0
	2.5" Drive Bays(Total)	1
	2.5" Drive Bays (Free)	1
	3.5" Drive Bays(Free)	0
Audio	Audio Chipset	Realtek ALC256
	Audio Type	N/A
	D-MIC	N/A
Kommunikation	LAN	1x Realtek RTL8111H+1x Realtek RTL8125BG-CG
	WLAN Version	Wi-Fi 6E+BT
	BT Version	5.3
	WLAN	INTEL/AX211.NGWG.NV

"2026-08-19 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products."

Cubi 5 1M

CUBI 5 1MA-661AT

Schnittstellen (Vorne)	Thunderbolt	1x (ThunderBolt 4)
	Mic-in/Headphone-out combo	1
	USB 3.2 Gen 2 (10G) Type A	2
	USB 4 (40G) Type C	N/A
	Copilot Button	N/A
Schnittstellen (Rückseite)	RJ45	2
	HDMI out	1x (v2.1)
	DP out	1x (v1.4)
	Mic-in/Headphone-out combo (R)	N/A
	USB 3.2 Gen 2 (10G) Type A (R)	2
	Lock type	Kensington Lock
Schnittstellen (Seite)	Mic-in/Headphone-out combo	1
	Thunderbolt	1x (ThunderBolt 4)
	USB 3.2 Gen 2 (10G) Type A	2
Power	Power	65W
	Power Certification	N/A
	Formfactor	N/A
	Type	ADAPTOR
VESA	VESA size	100 x 100 mm
Garantie	Warranty	24months
Abmessungen & Gewicht	Product Dimension (WxDxH) (mm)	124 x 124 x 53.7
	Product Dimension (WxDxH) (inch)	4.88 x 4.88 x 2.11
	Inside Carton Dimension (WxDxH) (mm)	205 x 220 x 94
	Inside Carton Dimension (WxDxH) (inch)	8.07 x 8.66 x 3.7
	Outer Carton Dimension Standard (WxDxH) (mm)	221 x 506 x 469
	Outer Carton Dimension Standard (WxDxH) (inch)	8.7 x 19.92 x 18.46
	Weight (Net kg)	0.59
	Net Weight (lbs)	1.3
	Weight (Gross kg)	1.33
	Gross Weight (lbs)	2.93
	Liter	0.83L
	Pint	0.83L
Lagerung & Zertifikationen	Regulatory Compliance	BSMI, CB/CE, FCC(Class B), RCM(C-Tick), UL(CUL), VCCI
	Operating, Storage Temperature	0° C ~ 35° C ; -20° C ~ 60° C
	Operating, Storage Humidity	0% ~ 85%;0% ~ 90%
Zubehör	AC Adaptor	1
	Power Cord	1
	Warranty Card	N/A
	Quick Guide	3
	User Manual	N/A
	VESA Mount kit	1
	Keyboard	N/A
	Keyboard Interface	N/A
	Mouse	N/A
	Mouse Interface	N/A
	Power Switch	N/A
Barcode Info	EAN	4711377464970
Security	TPM module	fTPM
	Chassis Lock	Kensington Lock

“2026-08-19 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products.”