




LC-CC-120-LP6

- AERA Series -

Low profile CPU air cooler
with a 120 mm fan

Our CPU coolers of the AERA series impress with a high TDP, making them the ideal all-rounders for the most demanding mid-range gaming systems.

Thanks to their performance, they easily handle the heat dissipation of hot processors and ensure stable and efficient cooling.

This keeps your system reliably cool even under load!

Features:

- Low profile CPU cooler
- one 120 mm fan
- six 6 mm heat pipes
- TDP: 180 W
- for Intel and AMD sockets
- aluminium cooling fins
- copper heat pipes & heat spreader
- Hydro bearing

Technical specification - LC-CC-120-LP6

Cooling type:	air cooling
TDP (Thermal Design Power):	180 W
Number of fans:	1
Number of heat pipes:	6
Heat pipe diameter:	6 mm
Dimension (fan):	120 x 120 x 15 mm
Dimension (heat sink):	123 x 120 x 60 mm
Dimension (CPU cooler overall):	123 x 120 x 75 mm
Dimension (heat spreader):	35 x 41 mm
Dimension (retail):	155 x 155 x 110 mm
Weight (product/overall):	0,465 / 0,572 kg
Rated voltage:	12 V DC
Operating voltage:	12 V DC
Starting voltage:	6 V DC
Rated current (fan):	0,2 A max.
Max. current:	0,2 A
Max. wattage:	2,4 W
Fan speed:	400 - 1500 rpm (±10%)
Airflow:	48,7 CFM (±10%)
Air pressure:	1,58 mm/H ₂ O max.
Fan noise level:	< 27,6 dB(A) max.
Fan bearing:	Hydro bearing
Connection:	4 pin PWM
Fan cable length:	ca. 400 mm

Socket:	Intel LGA: 1851, 1700, 1200, 115x, 1356, 1366, 2011, 2066
	AMD: AM5, AM4, AM3, AM2, FM2, FM1
Material:	cooling fins: aluminium heat pipes: copper heat spreader: copper, aluminium fan: plastic
Mark of conformity:	CE
Colour:	black
Barcode:	4262443281514
Manufacturer code:	LC-CC-120-LP6
Included in delivery:	1x heat sink 1x 120 mm fan 1x mounting material 1x thermal paste 1x user manual