Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: OPPLE Lighting

Supplier's address: Carlo Schmitz, Head of Marketing Europe, Meerenakkerweg 1-07, 5652AR, Eindhoven, Netherlands

Model identifier: 543017020400

Type of light source:

Lighting technology used:	LED	Non-directional or directional:	DLS
Light source cap-type (or other electric interface)	220-240 V AC; 50/60 Hz		
Mains or non-mains:	MLS	Connected light source (CLS):	Nein
Colour-tuneable light source:	Nein	Envelope:	-
High luminance light source:	Nein		
Anti-glare shield:	Nein	Dimmable:	No


Product parameters

Parameter	Value	Parameter	Value
General product parameters:			
Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer	10	Energy efficiency class	F
Useful luminous flux (ϕuse), indicating if it refers to the flux in a sphere (360º), in a wide cone (120º) or in a narrow cone (90º)	874 in Wide cone (120°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	3 000
On-mode power (P_{on}), expressed in W	10,0	Standby power (P_{sb}), expressed in W and rounded to the second decimal	0,00
Networked standby power (P_{net}) for CLS, expressed in W and rounded to the second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	80...89
Outer dimensions — Height	84	Spectral power distribution in the	See image in last page
Outer dimensions — Width	113		

without separate control gear, lighting control parts and non-lighting control parts, if any (millimetre)	Depth	104	range 250 nm to 800 nm, at full-load	
Claim of equivalent power[a]		-	If yes, equivalent power (W)	-
			Chromaticity coordinates (x and y)	0,440 0,403
Parameters for directional light sources:				
Peak luminous intensity (cd)		730	Beam angle in degrees, or the range of beam angles that can be set	100
Parameters for LED and OLED light sources:				
R9 colour rendering index value		1	Survival factor	0,90
the lumen maintenance factor		0,96		
Parameters for LED and OLED mains light sources:				
displacement factor (cos ϕ1)		0,91	Colour consistency in McAdam ellipses	4
Claims that an LED light source replaces a fluorescent light source without integrated ballast of a particular wattage.		-[b]	If yes then replacement claim (W)	-
Flicker metric (Pst LM)		1,0	Stroboscopic effect metric (SVM)	0,4

[a] '-' : not applicable;

[b] '-' : not applicable;


Spectrum
1
0.9
0.8
0.7
0.6
0.5
0.4
0.3
0.2
0.1
0
250
300
350
400
450
500
550
600
650
700
750
800
Wavelength(nm)