

Manhattan TV & Monitor Mount, Wall, Full Motion, 1 screen, Screen Sizes: 23-42", Black, VESA 75x75 to 200x200, Max 20kg, Tilt & Swivel with 3 Pivots, Lifetime Warranty - Klammer - für LCD TV

Produktbeschreibung: Manhattan TV & Monitor Mount, Wall, Full Motion, 1 screen, Screen Sizes: 23-42", Black, VESA 75x75 to 200x200, Max 20kg, Tilt & Swivel with 3 Pivots, Lifetime Warranty - Klammer - für LCD TV - langlebiges Aluminium - Bildschirmgröße: 58.4-106.7 cm (23"-42") - Wandmontage

Gruppe: AV-Möbel
 Hersteller: IC Intracom
 Hersteller Artikel Nr: 423755
 EAN: 0766623423755

Hauptmerkmale	
Produktbeschreibung	Manhattan TV & Monitor Mount, Wall, Full Motion, 1 screen, Screen Sizes: 23-42", Black, VESA 75x75 to 200x200, Max 20kg, Tilt & Swivel with 3 Pivots, Lifetime Warranty - Klammer - für LCD TV
Produkttyp	Klammer - Wandmontage
Abmessungen (Breite x Tiefe x Höhe)	23 cm x 40 cm x 23 cm
Einstellbare Tiefe	8-40 cm
Neigung	-15 ° bis 15 °
Schwenken	180°
Anpassungen	Schwenk, Neigung
Gewicht	1.85 kg
Empfohlene Verwendung	LCD TV
Empfohlene Display-Größe	58.4-106.7 cm (23"-42")
VESA-Halterung	100 x 100 mm, 75 x 75 mm, 200 x 200 mm, 200 x 100 mm
Max. Ladegewicht	20 kg
Material	Langlebiges Aluminium

