Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: SPECTRUM

Supplier's address: Wojnarowscy, Gospodarcza 16 40-432 Katowice Poland

Model identifier: WOJ+14644

Type of light source:

Lighting technology used:	LED	Non-directional or directional:	NDLS
Light source cap-type (or other electric interface)	E27		
Mains or non-mains:	MLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	-
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	Only with specific dimmers


Product parameters

Parameter	Value	Parameter	Value
General product parameters:			
Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer	6	Energy efficiency class	E
Useful luminous flux (ϕuse), indicating if it refers to the flux in a sphere (360º), in a wide cone (120º) or in a narrow cone (90º)	710 in Sphere (360°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	2 700
On-mode power (P_{on}), expressed in W	5,5	Standby power (P_{sb}), expressed in W and rounded to the second decimal	0,00
Networked standby power (P_{net}) for CLS, expressed in W and rounded to the second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	81
Outer dimensions without separate control gear, light-	Height	107	Spectral power distribution in the range 250 nm to 800 nm, at full-load	See image in last page
	Width	60		
	Depth	60		

ing control parts and non-lighting control parts, if any (millimetre)				
Claim of equivalent power[a]		Yes	If yes, equivalent power (W)	56
			Chromaticity coordinates (x and y)	0,455 0,409
Parameters for LED and OLED light sources:				
R9 colour rendering index value		14	Survival factor	0,90
the lumen maintenance factor		0,96		
Parameters for LED and OLED mains light sources:				
displacement factor (cos ϕ1)		0,90	Colour consistency in McAdam ellipses	5
Claims that an LED light source replaces a fluorescent light source without integrated ballast of a particular wattage.		-[b]	If yes then replacement claim (W)	-
Flicker metric (Pst LM)		1,0	Stroboscopic effect metric (SVM)	0,4

[a] '-' : not applicable;

[b] '-' : not applicable;


100
90
80
70
60
50
40
30
20
10
0
Relative Power [%]
250
350
450
550
650
750
Wavelength [nm]

Model placed on the Union market from 01/01/2020

EPREL registration number: 1533204

https://eprel.ec.europa.eu/qr/1533204

Supplier: Wojnarowscy Spółka z Ograniczoną Odpowiedzialnością (Manufacturer)

Website: www.spectrumled.pl

Customer care service:

Name: Wojnarowscy

Website: www.spectrumled.pl

Email: biuro@spectrumled.pl

Phone: +48327350600

Address:
Gospodarcza 16
40-432 Katowice
Poland