

**Cabtite (cable entry system)
CABTITE SE 9-10 SML GY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Whether a large or small cable diameter – Cabtite always offers the right seal insert.

The conical shape of the sealing elements allows the previously positioned snap-in grid inlays to be pushed in easily from the inside to the outside, it reliably seals intermediate spaces and provides strain relief in accordance with DIN EN 62444. The seal inserts combined with the frames achieve an IP 66 degree of protection. As a result of its slotted design with wave cut, it is especially suitable for pre-assembled cables.

- The black seal inserts are designed for a particularly high operating temperature and offer fire safety class UL 94 HB
- The grey sealing elements comply with fire safety class UL 94 V0 and are therefore suitable for the demands of the railway industry
- By using multiple inserts, two or more cables, as well as special cables, can be passed through a sealing element

Általános rendelési adatok

Típus	CABTITE SE 9-10 SML GY
Rendelési szám	2584630000
Verzió	Tömítőelem, Cabtite (cable entry system), TPE, Világosszürke, Magasság: 17.7 mm, Szélesség: 20.3 mm, Mélység: 17.7 mm, -40 °C...90 °C, IP54, IP65, IP66
GTIN (EAN)	4050118616996
Menny.	10 Stück

Cabtite (cable entry system)
CABTITE SE 9-10 SML GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Műszaki adatok**Méretetek és tömegek**

Hossz	20,3 mm	Hossz, inch	0,799 inch
Szélesség	20,3 mm	Szélesség (coll)	0,799 inch
Magasság	17,7 mm	Magasság (coll)	0,697 inch
Mélység	17,7 mm	Mélység (coll)	0,697 inch
Nettó tömeg	5,7 g		

General information

UL 94 éghetőségi osztály	V-0	Sealing element	1 small sealing element
Kábel külső átmérője, min.	9 mm	Kábel külső átmérője, max.	10 mm
Halogén	Nem	Szilikon	Nem
Anyag	TPE		

Besorolások

ETIM 6.0	EC000879	eClass 6.2	27-14-92-01
eClass 9.0	27-14-44-21	eClass 9.1	27-14-44-21

Jóváhagyások

Jóváhagyások



ROHS

Megfelel

Letöltések

Engineering Data	STEP
User Documentation	CabTite Installation Instructions