



MAINS CHOKE F.FU; PHASES:3; UN1(V):480; ITHMAX 1(A) / F1(HZ):1,5 /60; I LN (A):1,35; UK(%):2; LN(MH):9,4; TA/ISOKL:40 /B; IP00; TYPE OF TERMINALS:SCREW/TAB CONNECTION; EN 61558-2-20 >UL/CSA-RECOGNIZED< >CHOKE<

Figure similar

General technical data:		
Product designation		Netzdrossel f. FU
Phase number		3
Type of voltage		AC
Operating voltage rated value	V	400, 480
Operating frequency rated value	Hz	50 ... 60
Current		
• at AC		
— rated value	A	1.35
— maximum	A	1.5
Inductivity rated value	H	0.0094
Relative inductive drop in voltage on the measurement level current, voltage and frequency	%	2
Power loss [W] of the coil	W	16.7
Power loss [W] of the iron core	W	4.5
Mechanical data:		
Type of electrical connection for main current circuit		screw-type terminals / tab terminals

Width	m	0.088
Height	m	0.108
Depth	m	0.057

Ambient conditions:

Thermal class acc. to IEC 60085		B
Ambient temperature rated value	°C	40
Protection class IP		IP00

Certificates/ approvals:

Declaration of Conformity	other
---------------------------	-------



EG-Konf.

[Confirmation](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4EP3200-4US00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4EP3200-4US00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4EP3200-4US00&lang=en

last modified:

09/13/2019