

**Cabtite (cable entry system)
CABTITE CGS M63 BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



For metric M20 to M63 through-holes, the Cabtite cable entry system offers separable cable glands for cables with and without plugs. In case of maintenance or changes in the system, pre-assembled cables with diameters of 2 to 35 mm can be inserted quickly and safely in panels or enclosures. Reliable sealing of IP66 in accordance with DIN EN 60529 and an absolutely secure fitting (strain relief based on DIN EN 62444) is ensured by placing slotted sealing elements with a wave cut around the cable before being inserted into one of the two halves of the cable gland. The separable system ensures easy and fast installation. After inserting the sealing element, the two halves of the cable gland are simply snapped together. A locknut, which is also separable, on the inside of the panel ensures a reliable and secure hold.

Általános rendelési adatok

Típus	CABTITE CGS M63 BK
Rendelési szám	2584120000
Verzió	leválasztható tömszelence, Cabtite (cable entry system), Poliamid, üvegszál-erősítésű, mélyfekete, Magasság: 24.7 mm, M 63, IP54, IP65, IP66
GTIN (EAN)	4050118617238
Menny.	5 Stück

Cabtite (cable entry system)
CABTITE CGS M63 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Műszaki adatok**Méretetek és tömegek**

Hossz	39,7 mm	Hossz, inch	1,563 inch
Szélesség	72 mm	Szélesség (coll)	2,835 inch
Magasság	24,7 mm	Magasság (coll)	0,972 inch
Mélység	39,7 mm	Mélység (coll)	1,563 inch
Nettó tömeg	51 g		

General information

Meghúzási nyomaték, min.	6,8 Nm	Meghúzási nyomaték, max.	7 Nm
UL 94 éghetőségi osztály	V-0	Sealing element	1 nagy tömítőelem, vagy 4 kis tömítőelem
Opening diameter	63 mm	Külső menet	M 63
Menet hossza	15 mm	Menetemelkedés	1,5 mm
AF 1. méret	68 mm	AF 2. méret	82 mm
Halogén	Nem	Szilikon	Nem
Tömítés	TPE	Anyag	Poliamid, üvegszál-erősítésű

Besorolások

ETIM 6.0	EC000441	eClass 6.2	27-14-92-01
eClass 9.0	27-14-44-32	eClass 9.1	27-14-44-32

Jóváhagyások

ROHS	Megfelel
------	----------

Letöltések

Engineering Data	STEP
------------------	----------------------