

**Cabtite (cable entry system)
CABTITE SE 24-25 LRG BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Whether a large or small cable diameter – Cabtite always offers the right seal insert.

The conical shape of the sealing elements allows the previously positioned snap-in grid inlays to be pushed in easily from the inside to the outside, it reliably seals intermediate spaces and provides strain relief in accordance with DIN EN 62444. The seal inserts combined with the frames achieve an IP 66 degree of protection. As a result of its slotted design with wave cut, it is especially suitable for pre-assembled cables.

- The black seal inserts are designed for a particularly high operating temperature and offer fire safety class UL 94 HB
- The grey sealing elements comply with fire safety class UL 94 V0 and are therefore suitable for the demands of the railway industry
- By using multiple inserts, two or more cables, as well as special cables, can be passed through a sealing element

Általános rendelési adatok

Típus	CABTITE SE 24-25 LRG BK
Rendelési szám	2583710000
Verzió	Tömítőelem, Cabtite (cable entry system), TPE, mélyfekete, Magasság: 17.7 mm, Szélesség: 42.8 mm, Mélység: 17.7 mm, -40 °C...120 °C, IP54, IP65, IP66
GTIN (EAN)	4050118617184
Menny.	10 Stück

Cabtite (cable entry system)
CABTITE SE 24-25 LRG BK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Műszaki adatok**Méretetek és tömegek**

Hossz	42,8 mm	Hossz, inch	1,685 inch
Szélesség	42,8 mm	Szélesség (coll)	1,685 inch
Magasság	17,7 mm	Magasság (coll)	0,697 inch
Mélység	17,7 mm	Mélység (coll)	0,697 inch
Nettó tömeg	23,4 g		

General information

UL 94 éghetőségi osztály	HB	Sealing element	1 large sealing element
Kábel külső átmérője, min.	24 mm	Kábel külső átmérője, max.	25 mm
Halogén	Nem	Szilikon	Nem
Anyag	TPE		

Besorolások

ETIM 6.0	EC000879	eClass 6.2	27-14-92-01
eClass 9.0	27-14-44-21	eClass 9.1	27-14-44-21

Jóváhagyások

Jóváhagyások	
ROHS	Megfelel

Letöltések

Engineering Data	STEP
User Documentation	Cabtite Installation Instructions