



MAINS CHOKE F.FU; PHASES:3; UN1(V):480;
 ITHMAX 1(A) / F1(HZ):224 /60; I LN (A):202; UK(%):2;
 LN(MH):0,0629; TA/ISOKL:40 /H; IP00; TYPE OF
 TERMINALS:FLAT-TYPE TERMINAL; EN 61558-2-20
 >UL/CSA-RECOGNIZED< >CHOKE<

Figure similar

| General technical data: | | |
|--|----|-------------------|
| Product designation | | Netzdrossel f. FU |
| Phase number | | 3 |
| Type of voltage | | AC |
| Operating voltage rated value | V | 400, 480 |
| Operating frequency rated value | Hz | 50 ... 60 |
| Current | | |
| • at AC | | |
| — rated value | A | 202 |
| — maximum | A | 224 |
| Inductivity rated value | H | 0.000062 |
| Relative inductive drop in voltage on the measurement level current, voltage and frequency | % | 2 |
| Power loss [W] of the coil | W | 134 |
| Power loss [W] of the iron core | W | 52 |
| Mechanical data: | | |
| Type of electrical connection for main current circuit | | flat connector |

| | | |
|--------|---|-------|
| Width | m | 0.225 |
| Height | m | 0.21 |
| Depth | m | 0.176 |

Ambient conditions:

| | | |
|---------------------------------|----|------|
| Thermal class acc. to IEC 60085 | | H |
| Ambient temperature rated value | °C | 40 |
| Protection class IP | | IP00 |

Certificates/ approvals:

| | |
|--------------------------|-------|
| General Product Approval | other |
|--------------------------|-------|



[Confirmation](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4EU2552-8UA00-0AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4EU2552-8UA00-0AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4EU2552-8UA00-0AA0&lang=en

last modified:

09/13/2019