

SENTRON, cylindrical fuse link, 14x51 mm, 32 A, gG, Un AC: 690 V



Wersja	
Nazwa markowa produktu	SENTRON
oznaczenie produktu	Wkładka bezpiecznika cylindrycznego
Ogólne dane techniczne	
charakterystyka wkładki bezpiecznikowej	gG
wielkość wkładki bezpiecznikowej	14x51 mm
rodzaj napięcia	AC
prąd / przy AC / wartość znamionowa	32 A
napięcie zasilające / przy DC	250 V
napięcie robocze / wartość znamionowa	690 V
Rozpraszanie	
Strata mocy [W] / w przypadku wartości znamionowej prądu / w przypadku AC / w stanie rozgrzanym / na biegun	3,5 W
Obwód główny	
prąd roboczy / wartość nominalna	32 A
Szczegóły produktu	
element składowy produktu / sygnalizator uderzenia	Nigdy

pozycja montażowa	dowolnie, najlepiej pionowo
masa netto	22 g

Certyfikaty

oznaczenie środków roboczych

- zgodnie z DIN EN 61246-2
- zgodnie z IEC 81346-2:2009

F

F

Declaration of Conformity

Test Certificates



EG-Konf.

[Miscellaneous](#)

Więcej informacji

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW6112-1>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pl/ps/3NW6112-1>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW6112-1

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

