

Samsung Frigorifero Combinato EcoFlex 1.85m 344L RB33B610ESA

Marchio : Samsung

Codice prodotto: RB33B610ESA/EF

Nome del prodotto : Frigorifero Combinato EcoFlex 1.85m 344L RB33B610ESA

- Capacità: 344L
- Classe Energetica: E
- Dimensioni: 59,5 x 185,3 x 65,8 cm
- 20 anni di garanzia sul compressore Digital Inverter™

Frigorifero Combinato EcoFlex 1.85m 344L RB33B610ESA

Samsung Frigorifero Combinato EcoFlex 1.85m 344L RB33B610ESA. Capacità netta totale: 344 L. Cerniera porta: Destra. Classe climatica: SN-T, Emissione acustica: 35 dB. Capacità netta frigorifero: 230 L, No Frost (frigorifero), Luce interna, Numero di ripiani frigorifero: 4, Numero di cassetti per verdura: 1. Capacità netta congelatore: 114 L, Capacità di congelamento: 7 kg/24h, No Frost (congelatore). Classe efficienza energetica: E, Consumo energetico annuo: 254 kWh. Colore del prodotto: Grafite, Metallico



Design		Congelatore	
Posizionamento dell'apparecchio *	Libera installazione	Posizione del congelatore *	Posto in basso
Colore del prodotto *	Grafite, Metallico	Capacità netta congelatore *	114 L
Cerniera porta	Destra	Capacità di congelamento *	7 kg/24h
Porte reversibili	✓	Autonomia senza energia elettrica *	9 h
Display incorporato *	✓	Punteggio *	4*
Mezzo refrigerante	R600a	No Frost (congelatore) *	✓
Materiale ripiano	Vetro temperato	Numero di ripiani congelatore *	3
Prestazione		Vaschetta del ghiaccio	✓
Capacità netta totale *	344 L	Ergonomia	
Classe climatica *	SN-T	Allarme porta aperta	✓
Minima temperatura di funzionamento	10 °C	Gestione energetica	
Massima temperatura di funzionamento	43 °C	Scala di efficienza energetica	Da A a G
Classe emissione rumore *	B	Classe efficienza energetica *	E
Emissione acustica *	35 dB	Consumo energetico annuo *	254 kWh
Produzione ghiaccio *	✗	Indice di efficienza energetica (EEI)	100
Frigorifero		Dimensioni e peso	
Capacità netta frigorifero *	230 L	Larghezza *	595 mm
Luce interna	✓	Altezza *	1853 mm
Tipo di lampada	LED	Profondità senza maniglia	65,8 cm
No Frost (frigorifero) *	✓	Peso *	63 kg
Numero di ripiani frigorifero *	4	Profondità netta senza porta	59,5 cm
Numero di cassetti per verdura *	1	Dati su imballaggio	
Porta uova	✓	Larghezza imballo	637 mm
Balconcini del frigorifero	3	Profondità imballo	740 mm
Porta bottiglie	✗	Altezza imballo	1935 mm
Funzione Super Cool *	✗	Peso dell'imballo	66 kg



8806094505597

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity. Automated scraping, data mining, or harvesting for the purpose of training machine learning models, neural networks, or artificial intelligence systems is strictly prohibited without a commercial license.