



SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Name of product Visor Cleaner
Code-Nr. 112110

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended intended purpose(s)

Technical Aerosols

1.3. Details of the supplier of the safety data sheet

Distributor

WEICON GmbH & Co. KG
Königsberger Str. 255, DE-48157 Münster
Postbox 48045, DE-8460 Münster
Phone ++49(0)251 / 9322 - 0, Fax ++49(0)251 / 9322 - 244
E-Mail : msds@weicon.de
Internet : www.weicon.de

Advice

Produktsicherheit / Product-Safety-Department
Phone ++49(0)251 / 9322 - 0
E-mail (competent person):
msds@weicon.de

1.4. Emergency telephone number

GIZ Bonn (German, English) Tel: ++49(0)228-19 240
TRANSPORT: Consultank Lutz Harder GmbH Tel: +49(0)178
433 7434 (24h Emergency Contact)

Manufacturer

WEICON GmbH & Co. KG
Königsberger Str. 255, DE-48157 Münster

1.4. Emergency telephone number

Emergency advice

-
Phone -
GIZ Bonn (Medizinische Auskunft in Deutsch und Englisch)
Tel: ++49(0)228-19 240
TRANSPORT: Consultank Lutz Harder GmbH Tel: +49(0)178
433 7434 (24h Emergency Contact)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008 [CLP/GHS]

Hazard classes and Hazard categories	Hazard Statements	Classification procedure
--------------------------------------	-------------------	--------------------------

Aerosol 1	H222, H229	
-----------	------------	--

Hazard Statements

H222	Extremely flammable aerosol.
H229	Pressurised container: May burst if heated.

2.2. Label elements
Labelling according to Regulation (EC) No 1272/2008 [CLP/GHS]


GHS02

Signal word

Danger

Hazard Statements

H222 Extremely flammable aerosol.
 H229 Pressurised container: May burst if heated.

Precautionary Statements

P102 Keep out of reach of children.
 P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
 P211 Do not spray on an open flame or other ignition source.
 P251 Do not pierce or burn, even after use.
 P410 + P412 Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
 P501 Dispose of contents/container to hazardous or special waste collection point.

2.3. Other hazards
Information pertaining to special dangers for human and environment

In extensive use, formation of flammable / explosive vapour-air mixture is possible.

Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

SECTION 3: Composition/ information on ingredients
3.1. Substances

not applicable

3.2. Mixtures
Description

Mixture of active ingredients with propellant

Hazardous ingredients

CAS No	EC No	Name	[% weight]	Classification according to Regulation (EC) No 1272/2008 [CLP/GHS]
67-63-0	200-661-7	propan-2-ol	1 - 10	Flam. Liq. 2, H225 / Eye Irrit. 2, H319 / STOT SE 3, H336
75-28-5	200-857-2	isobutane	1 - 10	Flam. Gas 1, H220 / Press. Gas
106-97-8	203-448-7	butane	1 - 10	Flam. Gas 1, H220 / Press. Gas
74-98-6	200-827-9	propane	1 - 10	Flam. Gas 1, H220 / Press. Gas
192003-74-0		Acrylcopolymer	< 0,5	Aquatic Chronic 2, H411

REACH

CAS No	Name	REACH registration number
67-63-0	propan-2-ol	01-2119457558-25

Labelling for contents according to regulation (EC) No 648/2004, annex VII

less than 5 % non-ionic surfactants
 5 % or over but less than 15 % aliphatic hydrocarbons



SECTION 4: First aid measures

4.1. Description of first aid measures

General information

Remove contaminated soaked clothing immediately.

In case of inhalation

Ensure of fresh air.

In the event of symptoms refer for medical treatment.

In case of skin contact

In case of contact with skin wash off with water.

In case of eye contact

In case of contact with eyes rinse with plenty of water carefully. In the event of persistent symptoms seek medical treatment.

In case of ingestion

Seek medical advice.

Rinse out mouth thoroughly with water.

4.2. Most important symptoms and effects, both acute and delayed

No information available.

4.3. Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Alcohol-resistant foam

Dry powder

Carbon dioxide

Water spray jet

Unsuitable extinguishing media

Full water jet

5.2. Special hazards arising from the substance or mixture

Danger of bursting

In case of fire formation of dangerous gases possible.

5.3. Advice for firefighters

Special protective equipment for fire-fighters

Fire-fighting operations, rescue and clearing work under effect of combustion and smoulder gases just may be done with breathing apparatus.

Additional information

Cool endangered containers with water spray jet.

Collect contaminated firefighting water separately, must not be discharged into the drains.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel

Ensure adequate ventilation.

Use personal protective clothing.

Keep away sources of ignition.

**6.2. Environmental precautions**

Do not discharge into the drains/surface waters/groundwater.

6.3. Methods and material for containment and cleaning up

Take up with absorbent material (e.g. sand, kieselguhr, acid binder, general-purpose binder, sawdust).

After taking up the material dispose according to regulation.

6.4. Reference to other sections

Safe handling: see section 7

Disposal: see section 13

Personal protection equipment: see section 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling****Advice on safe handling**

Care for thoroughly room ventilation, if necessary use in well ventilated area with local exhaust ventilation at workplace.

General protective measures

Do not inhale gases/vapours/aerosols.

Avoid contact with the eyes.

Hygiene measures

At work do not eat, drink, smoke or take drugs.

Wash hands before breaks and after work.

Advice on protection against fire and explosion

Keep away from sources of ignition - No smoking

Do not spray on a naked flame or any incandescent material.

Pressurized container.

Do not pierce or burn even after use.

Protect from heat and sunlight.

7.2. Conditions for safe storage, including any incompatibilities**Requirements for storage rooms and vessels**

Adhere to administrative regulations relating to storage of compressed gas cylinders / containers.

Further information on storage conditions

Keep container tightly closed.

Protect from direct solar radiation.

Storage temperature may not exceed 50°C (=122°F).

Store container at cool and aired place.

7.3. Specific end use(s)**Recommendation(s) for intended use**

See section 1.2

! SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Ingredients with occupational exposure limits to be monitored**

CAS No	Name	Code	[mg/m3]	[ppm]	Remark
106-97-8	Butane	8 hours	1450	600	EH40/2005
		Short-term	1810	750	
67-63-0	propan-2-ol	8 hours	999	400	EH40/2005
		Short-term	1250	500	

**Additional advice**

The statutory local and national regulations have to be observed.

8.2. Exposure controls**Respiratory protection**

Not required

! Hand protection

In the cases of special applications, it is recommended to check the chemical resistance with the manufacturer of the gloves.

Chemical protective gloves must be chosen carefully in view of their design and depending on the dependence on the concentration and amounts of dangerous goods used in the specific working tasks.

Glove material specification [make/type, thickness, permeation time/life, wetting resistance]: NBR (Nitrile rubber), $\geq 0,5$ mm, ≥ 240 min

Eye protection

tightly fitting goggles

Other protection measures

protective clothing

Appropriate engineering controls

Sufficient ventilation and exhaustion.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties****Appearance**

aerosol

Colour

whitish

Odour

characteristic

Odour threshold

not determined

Important health, safety and environmental information

	Value	Temperature	at	Method	Remark
pH value	7				
Boiling temperature / boiling range	not determined				
Melting point / Freezing point	not determined				
Flash point	not applicable				Aerosol
Vapourisation rate	not determined				
Flammable (solid)	not determined				
Flammability (gas)	not determined				
Ignition temperature	365 °C				
Self ignition temperature					The product is not self-igniting.
Lower explosion limit	not determined				



Safety Data Sheet according to Regulation (EC)

No. 1907/2006 (REACH)

Printed 08.01.2016

revision 18.06.2015 (GB) Version 8.4

Visor Cleaner

	Value	Temperature	at	Method	Remark
Upper explosion limit	not determined				
Vapour pressure	4200 hPa	20 °C			
Relative density	0,92 g/cm ³	20 °C			
Vapour density	not determined				
Solubility in water					miscible
Solubility/other	not determined				
Partition coefficient n-octanol/water (log P O/W)	not determined				
Decomposition temperature	not determined				
Viscosity	not determined				

Oxidising properties

No information available.

Explosive properties

The product is considered non-explosive ; nevertheless explosive vapour/air mixtures can be generated .

9.2. Other information

No information available.

SECTION 10: Stability and reactivity

10.1. Reactivity

No information available.

10.2. Chemical stability

No information available.

10.3. Possibility of hazardous reactions

No information available.

10.4. Conditions to avoid

Keep away from heat.

Formation of explosive gas/air mixtures.

10.5. Incompatible materials

No information available.

10.6. Hazardous decomposition products

Thermal decomposition

Remark No decomposition if used as directed.



SECTION 11: Toxicological information**11.1. Information on toxicological effects****Acute toxicity/Irritation/Sensitization**

	Value/Validation	Species	Method	Remark
Skin irritation	non-irritant			
Eye irritation	non-irritant			
Skin sensitization	non-sensitizing			

Additional information

The product is to be handled with the caution usual with chemicals.
Other hazardous properties may not be excluded.

SECTION 12: Ecological information**12.1. Toxicity**

No information available.

12.2. Persistence and degradability

No information available.

12.3. Bioaccumulative potential

No information available.

12.4. Mobility in soil

No information available.

12.5. Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

12.6. Other adverse effects**General regulation**

Do not allow uncontrolled leakage of product into the environment.
Product is not allowed to be discharged into aquatic environment.

SECTION 13: Disposal considerations**13.1. Waste treatment methods****Waste code No.**

15 01 04

15 01 10*

Name of waste

metallic packaging

packaging containing residues of or contaminated by hazardous substances

Wastes marked with an asterisk are considered to be hazardous waste pursuant to Directive 2008/98/EC on hazardous waste.

Recommendations for the product

Remove in accordance with local official regulations.

Recommendations for packaging

Dispose of according to the local waste regulations.

Recommended cleansing agent

Water

**General information**

For proper waste disposal a complete emptying of the tin is necessary.

SECTION 14: Transport information

	ADR/RID	IMDG	IATA-DGR
14.1. UN number	1950	1950	1950
14.2. UN proper shipping name	AEROSOLS	AEROSOLS	Aerosols, flammable
14.3. Transport hazard class(es)	2.1	2.1	2.1
14.4. Packing group	-	-	-
14.5. Environmental hazards	No	No	No

14.6. Special precautions for user

Caution: Gases

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code
not applicable

Land and inland navigation transport ADR/RID

Hazard label(s) 2.1

tunnel restriction code D

Classification code 5F

transport in "limited quantities" according to 3.4 ADR is possible

Transport/further information

24h EMERGENCY CONTACT (TRANSPORT) +49(0)178 433 7434 (Consultank Lutz Harder GmbH)

! SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****! VOC standard**

VOC content 17,2 %

VOC value 158 g/L

15.2. Chemical Safety Assessment

Chemical safety assessments for substances in this mixture were not carried out.

SECTION 16: Other information**Recommended uses and restrictions**

National and local regulations concerning chemicals shall be observed.

For industrial use only.

Further information

Each user is responsible for the implementation of the national special regulations.

The information contained herein is based on the state of our knowledge. It characterizes the product with regard to the appropriate safety precautions. It does not represent a guarantee of the properties of the product.

Please observe the following disclaimer! --- Our safety data sheets have been compiled according to effective EU-directives, WITHOUT taking into account the special national directives concerning the handling of hazardous substances.

Indication of changes: "!" = Data changed compared with the previous version. Previous version: 8.3



Safety Data Sheet according to Regulation (EC)

No. 1907/2006 (REACH)

Printed 08.01.2016

revision 18.06.2015 (GB) Version 8.4

Visor Cleaner

- H220 Extremely flammable gas.
- H225 Highly flammable liquid and vapour.
- H319 Causes serious eye irritation.
- H336 May cause drowsiness or dizziness.
- H411 Toxic to aquatic life with long lasting effects.