

# Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

**Supplier's name or trade mark:** OPPLE Lighting

**Supplier's address:** Carlo Schmitz, Head of Marketing Europe, Meerenakkerweg 1-07, 5652AR, Eindhoven, Netherlands

**Model identifier:** 543016006000

## Type of light source:

|   |                        |                                 |      |
|---|------------------------|---------------------------------|------|
| Lighting technology used:                           | LED                    | Non-directional or directional: | NDLS |
| Light source cap-type (or other electric interface) | 220-240 V AC; 50/60 Hz |                                 |      |
| Mains or non-mains:                                 | MLS                    | Connected light source (CLS):   | Nein |
| Colour-tuneable light source:                       | Nein                   | Envelope:                       | -    |
| High luminance light source:                        | Nein                   |                                 |      |
| Anti-glare shield:                                  | Nein                   | Dimmable:                       | No   |

## Product parameters

| Parameter | Value | Parameter | Value |
|-----------|-------|-----------|-------|
|-----------|-------|-----------|-------|

### General product parameters:

|  |                        |  |                        |
|--|------------------------|--|------------------------|
| Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer  | 33                     | Energy efficiency class  | E                      |
| Useful luminous flux ( $\phi_{use}$ ), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°) | 4 300 in Sphere (360°) | Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set | 3 000                  |
| On-mode power ( $P_{on}$ ), expressed in W   | 33,0                   | Standby power ( $P_{sb}$ ), expressed in W and rounded to the second decimal   | 0,00                   |
| Networked standby power ( $P_{net}$ ) for CLS, expressed in W and rounded to the second decimal  | -                      | Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set   | 70...79                |
| Outer dimensions   | Height                 | Spectral power distribution in the   | See image in last page |
|  | Width                  |  |                        |
|  |                        |  | 450                    |

|   |       |      |                                       |                |
|---|-------|------|---------------------------------------|----------------|
| without separate control gear, lighting control parts and non-lighting control parts, if any (millimetre)               | Depth | 450  | range 250 nm to 800 nm, at full-load  |                |
| Claim of equivalent power <sup>(a)</sup>  |       | -    | If yes, equivalent power (W)          | -              |
|   |       |      | Chromaticity coordinates (x and y)    | 0,440<br>0,403 |
| <b>Parameters for LED and OLED light sources:</b>   |       |      |                                       |                |
| R9 colour rendering index value   |       | 8    | Survival factor                       | 0,90           |
| the lumen maintenance factor  |       | 0,96 |                                       |                |
| <b>Parameters for LED and OLED mains light sources:</b>   |       |      |                                       |                |
| displacement factor (cos $\phi_1$ )   |       | 0,91 | Colour consistency in McAdam ellipses | 5              |
| Claims that an LED light source replaces a fluorescent light source without integrated ballast of a particular wattage. |       | -(b) | If yes then replacement claim (W)     | -              |
| Flicker metric (Pst LM)   |       | 1,0  | Stroboscopic effect metric (SVM)      | 0,4            |

(a)-: not applicable;

(b)-: not applicable;

### Spectrum

