Basiselement - MSTBV 2,5/10-GF - 1776964

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://download.phoenixcontact.com)



basiselement, nominale stroom: 12 A, nominale spanning (III/2): 320 V, aantal polen: 10, rastermaat: 5 mm, kleur: groen, contactoppervlak: tin, montage: solderen

Product Features

- varianten met schroefdraadflens
- steekrichting verticaal t.o.v. de printplaat

Key commercial data

package_quantity	100
GTIN	4017918039134

Technical data

Afmetingen

lengte	8,6 mm
rastermaat	5 mm
afm. a	45 mm
stiftafmetingen	1 x 1 mm
printgatdiameter	1,4 mm

Algemeen

artikelfamilie	MSTBV 2,5/..-GF
isolatiemateriaalgroep	IIIa
teststootspanning (III/3)	4 kV
teststootspanning (III/2)	4 kV
teststootspanning (II/2)	4 kV
nominale spanning (III/3)	250 V
nominale spanning (III/2)	320 V
nominale spanning (II/2)	400 V
aansluiting overeenkomstig norm	EN-VDE
nominale stroom I_N	12 A
belastingsstroom maximaal	12 A
isolatiemateriaal	PBT
brandbaarheidsklasse volgens UL 94	V0
Kleur	groen
aantal polen	10

Basiselement - MSTBV 2,5/10-GF - 1776964

Technical data

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

approvals

CSA / UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / GOST / GL / RS / IECEE CB Scheme / CSA / CCA / GOST / cULus Recognized /

Approval details

CSA

Usegroups	**B**	**D**
nominale spanning UN	300 V	300 V
nominale stroom IN	12 A	10 A
mm²/AWG/kcmil		

UL Recognized

Usegroups	**B**	**D**
nominale spanning UN	300 V	300 V
nominale stroom IN	12 A	10 A

Basiselement - MSTBV 2,5/10-GF - 1776964

approvals

Usegroups	B	D
mm²/AWG/kcmil		

VDE Gutachten mit Fertigungsüberwachung

nominale spanning UN	250 V
nominale stroom IN	12 A
mm²/AWG/kcmil	

cUL Recognized

Usegroups	B	D
nominale spanning UN	300 V	300 V
nominale stroom IN	12 A	10 A
mm²/AWG/kcmil		

GOST

GL

nominale spanning UN	250 V
nominale stroom IN	8 A
mm²/AWG/kcmil	

RS

IECEE CB Scheme

nominale spanning UN	250 V
nominale stroom IN	12 A
mm²/AWG/kcmil	

Basiselement - MSTBV 2,5/10-GF - 1776964

approvals

Usegroups	B	D
nominale spanning UN	300 V	300 V
nominale stroom IN	12 A	10 A
mm²/AWG/kcmil		

CCA	
nominale spanning UN	250 V
nominale stroom IN	12 A
mm²/AWG/kcmil	

cULus Recognized

accessories

Polarisatie-element

CR-MSTB - 1734401



blinddop

MSTB-BL - 1755477



klemmencodering gecodeerd

Basiselement - MSTBV 2,5/10-GF - 1776964

accessories

SK 5/3,8:FORTL.ZAHLEN - 0804183



klemmencodering niet gecodeerd

SK 5/3,8:UNBEDRUCKT - 0805409



Coderingsstift

B-STIFT - 1051993



accessories


SK 5/3,8:SO - 0805072




Drawings

Basiselement - MSTBV 2,5/10-GF - 1776964

Boorsjabloon



Maatschets



© Phoenix Contact 2013 - all rights reserved
http://www.phoenixcontact.com