

NEOZED, fuse base, D02, 3-pole, 63 A, Un AC: 400 V, Un DC: 250 V



версия	
Фирменное название продукта	NEOZED
Наименование продукта	Основание плавкой вставки
Общие технические данные	
Число полюсов	3
Типоразмер системы безопасности / согласно DIN EN 60269-1	D02
напряжение питания	
рабочее напряжение / расчетное значение	400 V
рассеивание	
Мощность потерь [Вт] / при расчётном токе / при переменном токе / при теплом эксплуатационном состоянии / на полюс	3 W
Главная цепь	
Рабочий ток / расчетное значение	63 A
Подробнее	
Компонент продукта / крышка	да

Механическая конструкция

Высота	59 mm
Ширина	80,8 mm
Глубина	41 mm
Вид крепления	DIN-рейка
вес-нетто	260 g
Материал / цоколя предохранителей D	Фарфор

Сертификаты

Условное обозначение

- согласно DIN EN 61346-2
- согласно IEC 81346-2:2009

F

F

General Product Approval

Declaration of Conformity



VDE



EG-Konf.

Дополнительная информация

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mlfb=5SG5653>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/ru/ps/5SG5653>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG5653

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

