Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: SLV

Supplier's address: Axel Kranz, Daimlerstraße 21-23 52531 Übach-Palenberg Germany

Model identifier: 1004722

Type of light source:

Lighting technology used:	LED	Non-directional or directional:	NDLS
Light source cap-type (or other electric interface)	Unbekannt		
Mains or non-mains:	NMLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	-
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	No

Product parameters			
Parameter	Value	Parameter	Value
General product parameters:			
Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer	193	Energy efficiency class	F
Useful luminous flux (ϕ_{use}), indicating if it refers to the flux in a sphere (360º), in a wide cone (120º) or in a narrow cone (90º)	20 000 in Sphere (360°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	3 000
On-mode power (P_{on}), expressed in W	193,0	Standby power (P_{sb}), expressed in W and rounded to the second decimal	0,00
Networked standby power (P_{net}) for CLS, expressed in W and rounded to the second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	90
Outer dimensions without	Height	2	Spectral power distribution in the	See image in last page
	Width	20		
	Depth	5 000		

separate control gear, lighting control parts and non-lighting control parts, if any (millimetre)			range 250 nm to 800 nm, at full-load	
Claim of equivalent power(a)		-	If yes, equivalent power (W)	-
			Chromaticity coordinates (x and y)	0,433 0,403
Parameters for LED and OLED light sources:				
R9 colour rendering index value	72		Survival factor	1,00
the lumen maintenance factor	0,96			

(a)'-' : not applicable;

(b)'-' : not applicable;