## **Product Information Sheet**

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Sources							
Supplier's name or trade mark: Deko-Light							
Supplier's address: -							
Model identifier: L930512							
Type of light so	urce:						
Lighting technol	ogy used:	LED	Non-directional or directional:	DLS			
Light source cap-type		other electrical					
(or other electri	c interface)						
Mains or non-mains:		NMLS	Connected light source (CLS):	Nein			
Colour-tuneable light source:		Nein	Envelope:	-			
High luminance light source:		Nein					
Anti-glare shield:		Nein	Dimmable:	Only with specific dimmers			
Product parameters							
Parameter		Value	Parameter	Value			
General product parameters:							
Energy consumption in on- mode (kWh/1000 h), rounded up to the nearest integer		6	Energy efficiency class	G			
Useful luminous flux (φuse), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°)		566 in Wide cone (120°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	3 000			
On-mode power (P <sub>on</sub> ), expressed in W		6,0	Standby power (P <sub>sb</sub> ), expressed in W and rounded to the second decimal	0,00			
Networked standby power (P <sub>net</sub> ) for CLS, expressed in W and rounded to the second decimal		-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	90			
Outer	Height	3	Spectral power	See image			
dimensions	Width	8	distribution in the	in last page			

without separate control gear, lighting control parts and non- lighting control parts, if any (millimetre)	Depth	500	range 250 nm to 800 nm, at full-load				
Claim of equivalent power <sup>(a)</sup>		-	If yes, equivalent power (W)	-			
			Chromaticity coordinates (x and y)	0,434 0,403			
Parameters for directional light sources:							
Peak luminous intensity (cd)		188	Beam angle in degrees, or the range of beam angles that can be set	118			
Parameters for LED and OLED light sources:							
R9 colour rende	ring index value	65	Survival factor	0,90			
the lumen maintenance factor		0,70					

(a)'-': not applicable; (b)'-': not applicable;

