

MAINS CHOKE F.FU; PHASES:3; UN1(V):480;
 ITHMAX 1(A) / F1(HZ):63 /60; I LN (A):56,7; UK(%):2;
 LN(MH):0,224; TA/ISOKL:40 /B; IP00; TYPE OF
 TERMINALS:FLAT-TYPE TERMINAL; EN 61558-2-20
 >UL/CSA-RECOGNIZED< >CHOKE<



General technical data:

Product designation		Netzdrossel f. FU
Phase number		3
Type of voltage		AC
Operating voltage rated value	V	400, 480
Operating frequency rated value	Hz	50 ... 60
Current		
• at AC		
— rated value	A	56.7
— maximum	A	63
Inductivity rated value	H	0.00022
Relative inductive drop in voltage on the measurement level current, voltage and frequency	%	2
Power loss [W] of the coil	W	54
Power loss [W] of the iron core	W	13

Mechanical data:

Type of electrical connection for main current circuit		flat connector
Width	m	0.178
Height	m	0.153

Depth	m	0.12
-------	---	------

Ambient conditions:

Thermal class acc. to IEC 60085		B
Ambient temperature rated value	°C	40
Protection class IP		IP00

Certificates/ approvals:

Declaration of Conformity	other
---------------------------	-------



EG-Konf.

[Confirmation](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=4EP3800-7US00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4EP3800-7US00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=4EP3800-7US00&lang=en

last modified:

09/13/2019