

Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: V-TAC

Supplier's address: V-TAC Europe Ltd., bul. Rozhen 41, Sofia, BG

Model identifier: 23348

Type of light source:

| | | | |
|---|----------|---------------------------------|-----|
| Lighting technology used: | LED | Non-directional or directional: | DLS |
| Light source cap-type (or other electric interface) | Terminal | | |
| Mains or non-mains: | NMLS | Connected light source (CLS): | No |
| Colour-tuneable light source: | No | Envelope: | - |
| High luminance light source: | No | | |
| Anti-glare shield: | No | Dimmable: | No |


Product parameters

| Parameter | Value | Parameter | Value |
|--|---------------------------|--|---|
| General product parameters: | | | |
| Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer | 36 | Energy efficiency class | F |
| Useful luminous flux (ϕ_{use}), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°) | 2 880 in Wide cone (120°) | Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set | 3 000 or 4 000 or 6 500 |
| On-mode power (P_{on}), expressed in W | 36,0 | Standby power (P_{sb}), expressed in W and rounded to the second decimal | 0,00 |
| Networked standby power (P_{net}) for CLS, expressed in W and rounded to the second decimal | - | Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set | 80 |
| Outer dimensions without separate control gear, lighting control | Height | 60 | Spectral power distribution in the range 250 nm to 800 nm, at full-load |
| | Width | 50 | |
| | Depth | 1 227 | |
| | | | See image in last page |


| | | | |
|---|-------|--|----------------|
| parts and non-lighting control parts, if any (millimetre) | | | |
| Claim of equivalent power ^(a) | - | If yes, equivalent power (W) | - |
| | | Chromaticity coordinates (x and y) | 0,380 0,380 |
| Parameters for directional light sources: | | | |
| Peak luminous intensity (cd) | 1 283 | Beam angle in degrees, or the range of beam angles that can be set | 100 |
| Parameters for LED and OLED light sources: | | | |
| R9 colour rendering index value | 8 | Survival factor | 0,90 |
| the lumen maintenance factor | 0,96 | | |

(a) : not applicable;

(b) : not applicable;



Model placed on the Union market from 09/01/2024.



EPREL registration number: 1892140

<https://eprel.ec.europa.eu/qr/1892140>

Supplier: V-TAC Europe Ltd (Manufacturer)

Website: www.v-tac.eu

Customer care service:

Name: V-TAC Europe Ltd.

Website: www.v-tac.eu

Email: office@v-tac.eu

Phone: +359290566

Address:

bul. Rozhen 41

Sofia

Bulgaria