

# Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

**Supplier's name or trade mark:** V-TAC

**Supplier's address:** V-TAC Europe Ltd., bul. Rozhen 41, Sofia, BG

**Model identifier:** 23100

## Type of light source:

|   |                |                                 |      |
|---|----------------|---------------------------------|------|
| Lighting technology used:                           | LED            | Non-directional or directional: | NDLS |
| Light source cap-type (or other electric interface) | L/N Connection |                                 |      |
| Mains or non-mains:                                 | MLS            | Connected light source (CLS):   | No   |
| Colour-tuneable light source:                       | No             | Envelope:                       | -    |
| High luminance light source:                        | No             |                                 |      |
| Anti-glare shield:                                  | No             | Dimmable:                       | No   |

## Product parameters

| Parameter  | Value                  | Parameter  | Value   |
|--|------------------------|--|---|
| <b>General product parameters:</b>   |                        |  |   |
| Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer  | 12                     | Energy efficiency class  | E   |
| Useful luminous flux ( $\phi_{use}$ ), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°) | 1 440 in Sphere (360°) | Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set | 3 000   |
| On-mode power ( $P_{on}$ ), expressed in W   | 12,0                   | Standby power ( $P_{sb}$ ), expressed in W and rounded to the second decimal   | 0,00  |
| Networked standby power ( $P_{net}$ ) for CLS, expressed in W and rounded to the second decimal  | -                      | Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set   | 86  |
| Outer dimensions without separate control gear, lighting control   | Height                 | 11 100   | Spectral power distribution in the range 250 nm to 800 nm, at full-load |
|  | Width                  | 800  |   |
|  | Depth                  | 45   |   |
|  |                        |  | See image in last page  |

|   |      |                                       |                |
|---|------|---------------------------------------|----------------|
| parts and non-lighting control parts, if any (millimetre)   |      |                                       |                |
| Claim of equivalent power <sup>(a)</sup>  | -    | If yes, equivalent power (W)          | -              |
|   |      | Chromaticity coordinates (x and y)    | 0,380<br>0,370 |
| <b>Parameters for LED and OLED light sources:</b>   |      |                                       |                |
| R9 colour rendering index value   | 23   | Survival factor                       | 1,00           |
| the lumen maintenance factor  | 0,93 |                                       |                |
| <b>Parameters for LED and OLED mains light sources:</b>   |      |                                       |                |
| displacement factor (cos $\phi_1$ )   | 0,70 | Colour consistency in McAdam ellipses | 6              |
| Claims that an LED light source replaces a fluorescent light source without integrated ballast of a particular wattage. | -(b) | If yes then replacement claim (W)     | -              |
| Flicker metric (Pst LM)   | 1,0  | Stroboscopic effect metric (SVM)      | 0,9            |

(a)-: not applicable;

(b)-: not applicable;

