

**OMNIMATE-data - RJ45-uttag omvandlare
RJ45M R1V 3.3N4YG/YG TY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



RJ45-sändarlansor (magnetiska) för gigabit-ändamål (1000 base-T) med integrerad kompensering motverkar aktivt induktiva och kapacitiva kopplingar och gör att utrymme kan sparas på kretskortet.

- Lödningsprocess THT eller THR
- Brett utbud av olika design typer, även med inbyggda lysdioder och skärmade kontaktflikar
- Förpackad antingen på bricka (TY) eller antistatiskt på tape-on-reel (RL)
- Utvidgat temperaturområde, -40 °C till +85 °C
- Förstärkt guldager för förbättrat korrosionsskydd
- Överföringshastighet upp till 1 Gbit/sek

Allmänna beställningsdata

Typ	RJ45M R1V 3.3N4YG/YG TY
Art.nr.	1534750000
Artikelbeteckning	Kretskortsstickanslutning, RJ45-uttag omvandlare, 10/100 MBit/s , THT/THR lödanslutning, 180°, Skärmflikar: ingen, 30-80 µm Ni / 30- µm Au , LED: Ja, grön/gul, grön/gul, Antal poler: 8, Bricka (manuell montering)
GTIN (EAN)	4050118338416
Frp	120 Stück
Förpackning	Bricka (manuell montering)

**OMNIMATE-data - RJ45-uttag omvandlare
RJ45M R1V 3.3N4YG/YG TY**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Tekniska data**Mått och vikter**

Bredd	16 mm	Byggbredd (tum)	0,63 inch
Höjd	20,3 mm	Bygghöjd (tum)	0,799 inch
Höjd lägstbyggande	17 mm	Djup	16,8 mm
Byggdjup (tum)	0,661 inch	Nettovikt	4,208 g

Temperaturer

Drifttemperatur, max	85 °C	Drifttemperatur, min.	-40 °C
Lagertemperatur, max.	85 °C	Lagertemperatur, min.	-40 °C

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Systemparametrar

Anslutningstyp	Hylsa	Anslutningsvinkel	180°
Antal lödstift per pol	1	Antal poler	8
Avskärmning	Ja	Delning i mm (P)	1,27 mm
Delning i tum (P)	0,05 inch	Diameter bestyckningshål (D)	0,9 mm
Dimensioner för lödstift	0,40 x 0,30 mm, LED-stift = 0,50 x 0,50 mm	Färg på höger LED	grön/gul
Färg på vänster LED	grön/gul	Koppling	8-trådig
Lödstiftlängd (l)	3,2 mm	LED	Ja
Montering på kretskortet	THT/THR lödanslutning	Produktfamilj	OMNIMATE-data - RJ45- uttag omvandlare
Skärmmaterial	Mässing	Skyddsklass	IP20
Skärmarea	förnicklad	Skärmflikar	ingen
Stickcykler	750	Tolerans diameter bestyckningshål (D)	± 0,1 mm
Överföringshastighet	10/100 MBit/s		

Elektriska egenskaper

Isolationshållfasthet	> 500 MΩ	Märkström	1,5 A
Märkspänning	125 V AC	Spänningstålighet kontakt/kontakt	1000 V DC
Spänningstålighet kontakt/skärm	1 500 V DC		

Packaging

Förpackning	Bricka (manuell montering)	VPE-längd	25 mm
VPE-bredd	175 mm	VPE-höjd	305 mm

Materialdata

Isoleringsmaterial	PA 9T	Färgkod	svart
Färgtabell (jämförbar)	RAL 9011	Isoleringsmaterialgrupp	II
CTI	≥ 500	Isolationshållfasthet	> 500 MΩ
Moisture Level (MSL)	1	Brännbarhetsklass enligt UL 94	V-0
Kontaktgrundmaterial	Fosforbrons	Kontaktyta	Guld över nickel
Skiktstruktur för stiftkontakten	30-80 μ" Ni / 30- μ" Au	Lagertemperatur, min.	-40 °C
Lagertemperatur, max.	85 °C	Drifttemperatur, min.	-40 °C
Drifttemperatur, max	85 °C		

OMNIMATE-data - RJ45-uttag omvandlare RJ45M R1V 3.3N4YG/YG TY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Tekniska data

Klassificeringar

ETIM 6.0	EC002637	eClass 6.2	27-25-05-04
eClass 7.1	27-25-05-04	eClass 8.1	19-17-01-25
eClass 9.0	27-44-04-02	eClass 9.1	27-44-04-02

Godkännanden

Godkännanden



ROHS Uppfyllelse

Downloads


Användardokumentation	MAN IE GUIDE DE MAN IE GUIDE EN
Broschyr/Katalog	MB FREECONTACT EN FL FIELDWIRING EN PI PROFINET CABLING EN
Teknikuppgifter Data	STEP

OMNIMATE-data - RJ45-uttag omvandlare RJ45M R1V 3.3N4YG/YG TY


Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Ritningar


Profilritning




Profilritning




Profilritning



Profilritning



Profilritning




OMNIMATE-data - RJ45-uttag omvandlare RJ45M R1V 3.3N4YG/YG TY


Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Ritningar

Kretskortsdesign



Kopplingsbild



OMNIMATE-data - RJ45-uttag omvandlare RJ45M R1V 3.3N4YG/YG TY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Ritningar

Schematic

Characteristics

Inductance	350 µH min. @ 100 kHz, 100 mV, 8 mA DC Bias
Leakage Inductance	0.3 µH max. @ 100 kHz, 100 mV
Insertion Loss	1.1 dB max. @ (1 - 100) MHz
Return Loss	18 dB min. @ (1 - 30) MHz 16 dB min. @ (30 - 60) MHz 12 dB min. @ (60 - 80) MHz
Cross Talk	30 dB min. @ (1 - 100) MHz
Common Mode Rejection	30 dB min. @ (1 - 100) MHz

Type codes

RJ45	G1	R	1	U	3.2	E	4	GY/GY	TY	RJ45G1 R1U 3.2E4GY/GY TY																																																																																																																		
										<table><tr><td>Packaging</td><td>TY</td><td>Tray in box (manual assembly)</td></tr><tr><td></td><td>RL</td><td>Tape on Reel (automated assembly)</td></tr><tr><td>LED</td><td>Y/G</td><td>Yellow/Green</td></tr><tr><td></td><td>G/Y</td><td>Green/Yellow (standard)</td></tr><tr><td></td><td>GY/GY</td><td>Green-Yellow/Green-Yellow</td></tr><tr><td></td><td>O/G</td><td>Orange/Green</td></tr><tr><td></td><td>R/O</td><td>Red/Orange</td></tr><tr><td></td><td>...</td><td>... (further combinations possible)</td></tr><tr><td></td><td>N</td><td>without LED</td></tr><tr><td>Contact surface thickness</td><td>4</td><td>1 = 3µ", 2 = 6µ", 3 = 15µ", 4 = 30µ", 5 = 50µ"</td></tr><tr><td>EMI tabs (ground fingers)</td><td>E</td><td>E = with EMI tabs</td></tr><tr><td></td><td>N</td><td>N = without EMI tabs</td></tr><tr><td>Solder Pin length</td><td>3.2</td><td>3.2 mm</td></tr><tr><td></td><td>1.6</td><td>1.6 mm</td></tr><tr><td></td><td>D</td><td>SMD</td></tr><tr><td>Direction, latch style</td><td>U</td><td>Horizontal (90°, side entry), latch up</td></tr><tr><td></td><td>D</td><td>Horizontal (90°, side entry), latch down</td></tr><tr><td></td><td>V</td><td>Vertical (180°, top entry)</td></tr><tr><td></td><td>Y</td><td>Diagonal (45°), latch up</td></tr><tr><td>Number of Ports</td><td>1</td><td>1 Port</td></tr><tr><td></td><td>12; 14; ...</td><td>multi ports side by side, Multiport</td></tr><tr><td></td><td>2; 4; ...</td><td>multi ports about each other, Multilevel</td></tr><tr><td>Assembly on PCB</td><td>R</td><td>Through Hole Reflow - THR</td></tr><tr><td></td><td>S</td><td>Soldering process: Wave or Reflow soldering</td></tr><tr><td></td><td>T</td><td>Surface Mount Technology - SMT</td></tr><tr><td></td><td></td><td>Soldering process: Reflow soldering</td></tr><tr><td></td><td></td><td>Through Hole Technology - THT</td></tr><tr><td></td><td></td><td>Soldering process: Wave</td></tr><tr><td>Performance Category</td><td>C5</td><td>Category 5</td></tr><tr><td></td><td>C6</td><td>Category 6</td></tr><tr><td></td><td>C6A</td><td>Category 6A</td></tr><tr><td></td><td>C5e</td><td>Category 5e</td></tr><tr><td></td><td>M</td><td>10/100 Mbit</td></tr><tr><td></td><td>G1</td><td>10/100/1000 Mbit</td></tr><tr><td></td><td>G10</td><td>10 Gbit</td></tr><tr><td></td><td>U</td><td>Unshielded</td></tr><tr><td></td><td>MP</td><td>10/100 Mbit with POE</td></tr><tr><td></td><td>MP+</td><td>10/100 Mbit with POE+</td></tr></table>	Packaging	TY	Tray in box (manual assembly)		RL	Tape on Reel (automated assembly)	LED	Y/G	Yellow/Green		G/Y	Green/Yellow (standard)		GY/GY	Green-Yellow/Green-Yellow		O/G	Orange/Green		R/O	Red/Orange		...	... (further combinations possible)		N	without LED	Contact surface thickness	4	1 = 3µ", 2 = 6µ", 3 = 15µ", 4 = 30µ", 5 = 50µ"	EMI tabs (ground fingers)	E	E = with EMI tabs		N	N = without EMI tabs	Solder Pin length	3.2	3.2 mm		1.6	1.6 mm		D	SMD	Direction, latch style	U	Horizontal (90°, side entry), latch up		D	Horizontal (90°, side entry), latch down		V	Vertical (180°, top entry)		Y	Diagonal (45°), latch up	Number of Ports	1	1 Port		12; 14; ...	multi ports side by side, Multiport		2; 4; ...	multi ports about each other, Multilevel	Assembly on PCB	R	Through Hole Reflow - THR		S	Soldering process: Wave or Reflow soldering		T	Surface Mount Technology - SMT			Soldering process: Reflow soldering			Through Hole Technology - THT			Soldering process: Wave	Performance Category	C5	Category 5		C6	Category 6		C6A	Category 6A		C5e	Category 5e		M	10/100 Mbit		G1	10/100/1000 Mbit		G10	10 Gbit		U	Unshielded		MP	10/100 Mbit with POE		MP+	10/100 Mbit with POE+
Packaging	TY	Tray in box (manual assembly)																																																																																																																										
	RL	Tape on Reel (automated assembly)																																																																																																																										
LED	Y/G	Yellow/Green																																																																																																																										
	G/Y	Green/Yellow (standard)																																																																																																																										
	GY/GY	Green-Yellow/Green-Yellow																																																																																																																										
	O/G	Orange/Green																																																																																																																										
	R/O	Red/Orange																																																																																																																										
	...	... (further combinations possible)																																																																																																																										
	N	without LED																																																																																																																										
Contact surface thickness	4	1 = 3µ", 2 = 6µ", 3 = 15µ", 4 = 30µ", 5 = 50µ"																																																																																																																										
EMI tabs (ground fingers)	E	E = with EMI tabs																																																																																																																										
	N	N = without EMI tabs																																																																																																																										
Solder Pin length	3.2	3.2 mm																																																																																																																										
	1.6	1.6 mm																																																																																																																										
	D	SMD																																																																																																																										
Direction, latch style	U	Horizontal (90°, side entry), latch up																																																																																																																										
	D	Horizontal (90°, side entry), latch down																																																																																																																										
	V	Vertical (180°, top entry)																																																																																																																										
	Y	Diagonal (45°), latch up																																																																																																																										
Number of Ports	1	1 Port																																																																																																																										
	12; 14; ...	multi ports side by side, Multiport																																																																																																																										
	2; 4; ...	multi ports about each other, Multilevel																																																																																																																										
Assembly on PCB	R	Through Hole Reflow - THR																																																																																																																										
	S	Soldering process: Wave or Reflow soldering																																																																																																																										
	T	Surface Mount Technology - SMT																																																																																																																										
		Soldering process: Reflow soldering																																																																																																																										
		Through Hole Technology - THT																																																																																																																										
		Soldering process: Wave																																																																																																																										
Performance Category	C5	Category 5																																																																																																																										
	C6	Category 6																																																																																																																										
	C6A	Category 6A																																																																																																																										
	C5e	Category 5e																																																																																																																										
	M	10/100 Mbit																																																																																																																										
	G1	10/100/1000 Mbit																																																																																																																										
	G10	10 Gbit																																																																																																																										
	U	Unshielded																																																																																																																										
	MP	10/100 Mbit with POE																																																																																																																										
	MP+	10/100 Mbit with POE+																																																																																																																										

Recommended wave soldering profiles

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Single Wave:



Double Wave:



Wave soldering profiles

Wired connection elements should be processed in accordance with the DIN EN 61760-1 standard. We have included two recommendations for practical wave soldering profiles, with which Weidmüller PCB terminals and connectors are qualified.

When choosing a suitable profile for your application, the following factors also need to be considered:

- PCB thickness
- Proportion of Cu in the layers
- Single/double-sided assembly
- Product range
- Heating and cooling rates

The single and double wave profiles each indicate the recommended operating range, including the maximum soldering temperature of 260°C. In practice, the maximum soldering temperature is quite often well below the above maximum profile.

We reserve the right to make technical changes.

Recommended reflow soldering profile

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Reflow soldering profile

The perfect soldering profile for SMT Surface Mount Technology is one the most exiting question in SMT production. But there are more than one correct answer: The diagram of temperature-on-time is related to processing features of solder paste and to maximum load of components.

We have to consider the following parameters:

- Time for pre heating
- Maximum temperature
- Time above melting point
- Time for cooling
- Maximum heating rate
- Maximum cooling rate

We recommend a typical solder profile with associated process limits. With preheating components and board are prepared smoothly for the solder phase. Heating rate is typically $\leq +3\text{K/s}$. In parallel the solder paste is 'activated'. The time above melting point of 217°C the paste gets liquid and components and boards begin to connect. The maximum temperature of 245°C to 254°C should stay between 10 and 40 seconds. In the cooling phase at $\geq -6\text{K/s}$ solder is cured. Board and components cool down while avoiding cold cracks.