

**Cabtite (kabelinföringssystem)
CABTITE FR 24/10 BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The frame, fabricated from a single piece, is quick and easy to assemble and consists of dimensionally stable, fibre-glass reinforced plastic. The captive foamed seal guarantees effective IP66 sealing in accordance with DIN EN 60529, even on painted and rough surfaces.

Allmänna beställningsdata

Typ	CABTITE FR 24/10 BK
Art.nr.	2583800000
Artikelbeteckning	Ram, Cabtite (kabelinföringssystem), Polyamid, glasfiberförstärkt, Djupsvalt, Höjd: 19.6 mm, Bredd: 70 mm, Djup: 19.6 mm, -40 °C...120 °C, IP54, IP65, IP66
GTIN (EAN)	4050118616682
Frp	1 Stück

Cabtite (kabelinföringssystem)
CABTITE FR 24/10 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Tekniska data**Mått och vikter**

Längd	153 mm	Bygglängd (tum)	6,024 inch
Bredd	70 mm	Byggbredd (tum)	2,756 inch
Höjd	19,6 mm	Bygghöjd (tum)	0,772 inch
Höjd lägstbyggande	19,6 mm	Djup	19,6 mm
Byggdjup (tum)	0,772 inch	Montagemått bredd	32 mm
Montagemått höjd	130 mm	Nettovikt	60,95 g
Diameter	5,5 mm		

Allmän information

Åtdragningsmoment	3 Nm	Öppningsbredd	46 mm
Öppningslängd	113,5 mm	Brännbarhetsklass enligt UL 94	V-0
Tätningselement	2 stora tätningar plus 4 små tätningar, 1 stor tätning plus 6 små tätningar, eller 10 små tätningar	Halogener	
Silikon	Nej	Tätning	Nej
Material	Polyamid, glasfiberförstärkt		TPE

Klassificeringar

ETIM 6.0	EC002624	eClass 6.2	27-14-92-01
eClass 9.0	27-18-28-15	eClass 9.1	27-18-92-65

Godkännanden

Godkännanden



ROHS

Uppfyllelse

Downloads

Användardokumentation	Cabtite Installation Instructions
Teknikuppgifter Data	STEP

Cabtite (kabelinföringssystem) CABTITE FR 24/10 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Ritningar

