

**Cabtite (kabelinföringssystem)
CABTITE CGS M63 BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



For metric M20 to M63 through-holes, the Cabtite cable entry system offers separable cable glands for cables with and without plugs. In case of maintenance or changes in the system, pre-assembled cables with diameters of 2 to 35 mm can be inserted quickly and safely in panels or enclosures. Reliable sealing of IP66 in accordance with DIN EN 60529 and an absolutely secure fitting (strain relief based on DIN EN 62444) is ensured by placing slotted sealing elements with a wave cut around the cable before being inserted into one of the two halves of the cable gland. The separable system ensures easy and fast installation. After inserting the sealing element, the two halves of the cable gland are simply snapped together. A locknut, which is also separable, on the inside of the panel ensures a reliable and secure hold.

Allmänna beställningsdata

Typ	CABTITE CGS M63 BK
Art.nr.	2584120000
Artikelbeteckning	separerbar kabelförskruvning, Cabtite (kabelinföringssystem), Polyamid, glasfiberförstärkt, Djupsvart, Höjd: 24.7 mm, M 63, IP54, IP65, IP66
GTIN (EAN)	4050118617238
Frp	5 Stück

**Cabtite (kabelinföringssystem)
CABTITE CGS M63 BK**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Tekniska data**Mått och vikter**

Längd	39,7 mm	Bygglängd (tum)	1,563 inch
Bredd	72 mm	Byggbredd (tum)	2,835 inch
Höjd	24,7 mm	Bygghöjd (tum)	0,972 inch
Djup	39,7 mm	Byggdjup (tum)	1,563 inch
Nettovikt	51 g		

Allmän information

Åtdragningsmoment, min.	6,8 Nm	Åtdragningsmoment, max.	7 Nm
Brännbarhetsklass enligt UL 94	V-0	Tätningselement	1 stor tätning eller 4 små tätningar
Öppningsdiameter	63 mm	Gänga (yttre)	M 63
Gängningslängd	15 mm	Gängstigning	1,5 mm
Nyckelbredd 1	68 mm	Nyckelbredd 2	82 mm
Halogener	Nej	Silikon	Nej
Tätning	TPE	Material	Polyamid, glasfiberförstärkt

Klassificeringar

ETIM 6.0	EC000441	eClass 6.2	27-14-92-01
eClass 9.0	27-14-44-32	eClass 9.1	27-14-44-32

Godkännanden

ROHS	Uppfyllelse
------	-------------

Downloads

Teknikuppgifter Data	STEP
----------------------	----------------------