

# Feed-through terminal block - UT 4 - 3044102

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Connection method: Screw connection, Cross section: 0.14 mm<sup>2</sup> - 6 mm<sup>2</sup>, AWG: 26 - 10, Width: 6.2 mm, Color: gray, Mounting type: NS 35/7,5, NS 35/15

## Product Features

- The large wiring space enables the connection of solid and stranded conductors without ferrules, even above the nominal cross section
- Tested for railway applications
- As well as saving space, the compact design enables user-friendly wiring in a small amount of space
- The multi-conductor connection offers maximum flexibility and wiring density
- Optimum screwdriver guidance through closed screw shafts
- The cable entry funnel enables the use of conductors with ferrules and plastic collars within the nominal cross section



## Key commercial data

package_quantity	50
GTIN	4017918960391

## Technical data

### General

Number of levels	1
Number of connections	2
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0
Area of application	Railway industry
Area of application	Mechanical engineering
Area of application	Plant engineering
Area of application	Process industry

### General

Maximum load current	41 A (with 6 mm <sup>2</sup> conductor cross section)
Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III

# Feed-through terminal block - UT 4 - 3044102

## Technical data

### General

Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current $I_N$	32 A (with 4 mm <sup>2</sup> conductor cross section)
Nominal voltage $U_N$	1000 V
Open side panel	ja
Shock protection test specification	DIN EN 50274 (VDE 0660-514):2002-11
Back of the hand protection	guaranteed
Finger protection	guaranteed
Surge voltage test setpoint	9.8 kV
Result of surge voltage test	Test passed
Power frequency withstand voltage setpoint	2.2 kV
Result of power-frequency withstand voltage test	Test passed
Checking the mechanical stability of terminal points (5 x conductor connection)	Test passed
Bending test rotation speed	10 rpm
Bending test turns	135
Bending test conductor cross section/weight	0.14 mm <sup>2</sup> / 0.2 kg
Bending test conductor cross section/weight	4 mm <sup>2</sup> / 0.9 kg
Bending test conductor cross section/weight	6 mm <sup>2</sup> / 1.4 kg
Result of bending test	Test passed
Conductor cross section tensile test	0.14 mm <sup>2</sup>
Tractive force setpoint	10 N
Conductor cross section tensile test	4 mm <sup>2</sup>
Tractive force setpoint	60 N
Conductor cross section tensile test	6 mm <sup>2</sup>
Tractive force setpoint	80 N
Tensile test result	Test passed
Tight fit on carrier	NS 35
Setpoint	1 N
Result of tight fit test	Test passed
Requirements, voltage drop	≤ 3.2 mV
Result of voltage drop test	Test passed
Temperature-rise test	Test passed
Conductor cross section short circuit testing	4 mm <sup>2</sup>
Short-time current	0.48 kA
Conductor cross section short circuit testing	6 mm <sup>2</sup>
Short-time current	0.72 kA
Short circuit stability result	Test passed
Proof of thermal characteristics (needle flame) effective duration	30 s
Result of thermal test	Test passed
Test specification, oscillation, broadband noise	DIN EN 50155 (VDE 0115-200):2008-03

# Feed-through terminal block - UT 4 - 3044102

## Technical data

### General

<b>Test spectrum</b>	Service life test category 1, class B, body mounted
<b>Test frequency</b>	$f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$
<b>ASD level</b>	$1.857 \text{ (m/s}^2\text{)}^2\text{/Hz}$
<b>Acceleration</b>	0.8 g
<b>Test duration per axis</b>	5 h
<b>Test directions</b>	X-, Y- and Z-axis
<b>Oscillation, broadband noise test result</b>	Test passed
<b>Test specification, shock test</b>	DIN EN 50155 (VDE 0115-200):2008-03
<b>Shock form</b>	Half-sine
<b>Acceleration</b>	5 g
<b>Shock duration</b>	30 ms
<b>Number of shocks per direction</b>	3
<b>Test directions</b>	X-, Y- and Z-axis (pos. and neg.)
<b>Shock test result</b>	Test passed
<b>Temperature index, insulating material (DIN EN 60216-1 (VDE 0304-21))</b>	130 °C
<b>Static insulating material application in cold</b>	-60 °C

### Dimensions

<b>Width</b>	6.2 mm
<b>Length</b>	47.7 mm
<b>Height NS 35/7,5</b>	47.5 mm
<b>Height NS 35/15</b>	55 mm

### Connection data

<b>Note</b>	Note: Product releases, connection cross sections and notes on connecting aluminum cables can be found in the download area.
<b>Conductor cross section solid min.</b>	0.14 mm <sup>2</sup>
<b>Conductor cross section solid max.</b>	6 mm <sup>2</sup>
<b>Conductor cross section AWG/kcmil min.</b>	26
<b>Conductor cross section AWG/kcmil max</b>	10
<b>Conductor cross section stranded min.</b>	0.14 mm <sup>2</sup>
<b>Conductor cross section stranded max.</b>	6 mm <sup>2</sup>
<b>Min. AWG conductor cross section, stranded</b>	26
<b>Max. AWG conductor cross section, stranded</b>	10
<b>Conductor cross section stranded, with ferrule without plastic sleeve min.</b>	0.14 mm <sup>2</sup>
<b>Conductor cross section stranded, with ferrule without plastic sleeve max.</b>	4 mm <sup>2</sup>
<b>Conductor cross section stranded, with ferrule with plastic sleeve min.</b>	0.14 mm <sup>2</sup>
<b>Conductor cross section stranded, with ferrule with plastic sleeve max.</b>	4 mm <sup>2</sup>
<b>2 conductors with same cross section, solid min.</b>	0.14 mm <sup>2</sup>

## Feed-through terminal block - UT 4 - 3044102

### Technical data

#### Connection data

2 conductors with same cross section, solid max.	1.5 mm <sup>2</sup>
2 conductors with same cross section, stranded min.	0.14 mm <sup>2</sup>
2 conductors with same cross section, stranded max.	1.5 mm <sup>2</sup>
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm <sup>2</sup>
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	2.5 mm <sup>2</sup>
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.14 mm <sup>2</sup>
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1.5 mm <sup>2</sup>
Connection method	Screw connection
Stripping length	9 mm
Internal cylindrical gage	A4
Screw thread	M3
Tightening torque, min	0.6 Nm
Tightening torque max	0.8 Nm

### classifications

#### eCl@ss

eCl@ss 4.0	27141120
eCl@ss 4.1	27141120
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

#### ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

# Feed-through terminal block - UT 4 - 3044102

## approvals

IECEX / ATEX / CSA / UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / LR / GL / DNV / RS / IEC EE  
 CB Scheme / cULus Recognized /

### Approval details

IECEX	
Nominal voltage UN	690 V
Nominal current IN	30 A
mm <sup>2</sup> /AWG/kcmil	0.14-4

ATEX	
Nominal voltage UN	690 V
Nominal current IN	38 A
mm <sup>2</sup> /AWG/kcmil	0.14-6

CSA		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	30 A	30 A
mm <sup>2</sup> /AWG/kcmil	26-10	26-10

UL Recognized		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	30 A	30 A
mm <sup>2</sup> /AWG/kcmil	26-10	26-10

VDE Gutachten mit Fertigungsüberwachung	
Nominal voltage UN	800 V
Nominal current IN	
mm <sup>2</sup> /AWG/kcmil	0.2-4

# Feed-through terminal block - UT 4 - 3044102

## approvals

<b>cUL Recognized</b>		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	30 A	30 A
mm <sup>2</sup> /AWG/kcmil	26-10	26-10

**LR**

**GL**

**DNV**

**RS**

<b>IECEE CB Scheme</b>	
Nominal voltage UN	800 V
Nominal current IN	
mm <sup>2</sup> /AWG/kcmil	0.2-4

**cULus Recognized**

## accessories

### End cover

D-UT 2,5/10 - 3047028



## Feed-through terminal block - UT 4 - 3044102

### accessories

DP PS-6 - 3036738



---

### Partition plate

ATP-UT - 3047167



---

### Screwdriver tools

SZS 0,6X3,5 - 1205053



SF-SL 0,6X3,5-100 S-VDE - 1212587



---

### Marker pen

X-PEN 0,35 - 0811228



# Feed-through terminal block - UT 4 - 3044102

accessories

**Warning label printed**

WS UT 4 - 3047332



---

## Bridge

FBS 2-6 - 3030336



---

FBS 3-6 - 3030242



---

FBS 4-6 - 3030255



---

FBS 5-6 - 3030349





## Feed-through terminal block - UT 4 - 3044102

### accessories

FBS 10-6 - 3030271



FBS 20-6 - 3030365



FBS 50-6 - 3032224



### Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



## Feed-through terminal block - UT 4 - 3044102

### accessories

NS 35/ 7,5 WH PERF 2000MM - 1204119



---

NS 35/ 7,5 WH UNPERF 2000MM - 1204122



---

NS 35/ 7,5 AL UNPERF 2000MM - 0801704



---

NS 35/ 7,5 ZN PERF 2000MM - 1206421



---

NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



---

NS 35/ 7,5 CU UNPERF 2000MM - 0801762



# Feed-through terminal block - UT 4 - 3044102

accessories

---

NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



## Feed-through terminal block - UT 4 - 3044102

### accessories

NS 35/15 AL UNPERF 2000MM - 1201756



---

NS 35/15 ZN PERF 2000MM - 1206599



---

NS 35/15 ZN UNPERF 2000MM - 1206586



---

NS 35/15 CU UNPERF 2000MM - 1201895



---

NS 35/15 CAP - 1206573



---

NS 35/15-2,3 UNPERF 2000MM - 1201798



# Feed-through terminal block - UT 4 - 3044102

accessories

---

## Terminal marking

ZB 6:UNBEDRUCKT - 1051003



UC-TM 6 - 0818085



UCT-TM 6 - 0828736



## Labeled terminal marker

ZB 6 CUS - 0824992



UC-TM 6 CUS - 0824589



## Feed-through terminal block - UT 4 - 3044102

accessories

UCT-TM 6 CUS - 0829602



---

### Test plug terminal block

MPS-MT - 0201744



---

PAI-4-FIX-5/6 BU - 3035975



---

PAI-4-FIX-5/6 OG - 3035974



---

PAI-4-FIX-5/6 YE - 3035977



## Feed-through terminal block - UT 4 - 3044102

### accessories

PAI-4-FIX-5/6 RD - 3035976



PAI-4-FIX-5/6 GN - 3035978



PAI-4-FIX-5/6 BK - 3035980



PAI-4-FIX-5/6 GY - 3035982



PAI-4-FIX-5/6 VT - 3035979



PAI-4-FIX-5/6 BN - 3035981



# Feed-through terminal block - UT 4 - 3044102

## accessories

---

PS-6 - 3030996



PS-6/2,3MM RD - 3038736



## Insulating sleeve

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689





## Feed-through terminal block - UT 4 - 3044102

### accessories

MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



MPS-IH BK - 0201731



### Planning and marking software

CLIP-PROJECT ADVANCED - 5146040



# Feed-through terminal block - UT 4 - 3044102

accessories

CLIP-PROJECT PROFESSIONAL - 5146053



---

## End block

CLIPFIX 35 - 3022218



---

CLIPFIX 35-5 - 3022276



---

E/NS 35 N - 0800886



---

## Drawings

Circuit diagram

