UNO-PS/1AC/12DC/100W

Primary-switched power supply unit

Data sheet 105987 en 00

© PHOENIX CONTACT 2014-03-14



1 Description

The UNO POWER power supply unit impresses in worldwide use thanks to maximum energy efficiency. Low noload losses and the high degree of efficiency save energy.

Thanks to its high power density, the UNO POWER power supply unit is the ideal solution, particularly in compact control boxes.

Features

- Worldwide use thanks to input voltage range of 85 V AC ... 264 V AC
- Superior system availability through reliable power supply with 12 V DC
- Maximum energy efficiency thanks to optimized efficiency over the entire operating range of the power supply unit and low no-load losses
- Particularly compact: 100 W of power from this narrow power supply, which is just 55 mm wide



Make sure you always use the latest documentation.
It can be downloaded from the product at phoenixcontact.net/products.



2 1		le of contents cription	1
2	Table	e of contents	2
3	Orde	ering data	3
4	Tech	nnical data	4
5	Inter	nded use	7
6	Struc	cture	7
	6.1 6.2	Device elementsBlock diagram	
7	7.1 7.2 7.3 7.4	embly Unpacking Mounting the power supply unit Mounting on a DIN rail Normal mounting position	8 8
8	Insta 8.1 8.2 8.3 8.4	Illing the power supply unit	11 11 12
9	Oper 9.1 9.2 9.3 9.4	rating behavior of the power supply unit Normal operation Overload response Behavior at ambient temperatures > 55°C Behavior in the case of alternative mounting positions.	13 13 13
10	10.1 10.2 10.3	rating the power supply unit Function monitoring Operating power supply units in parallel Operating the power supply unit in series	17 18 19
11	11.1	Oval Removing the power supply unit Notes on disposal	19

3 Ordering data

Description	Туре	Order No.	Pcs. / Pkt.		
Primary-switched UNO power supply for DIN rail mounting, input: single-phase, output: 12 V DC/100 W	UNO-PS/1AC/12DC/100W	2902997	1		
Accessories	Туре	Order No.	Pcs. / Pkt.		
Redundancy module, 5 V 24 V DC, 2 x 10 A, 1 x 20 A.	UNO-DIODE/5-24DC/2X10/1X20	2905489	1		
Our range of accessories is being continually extended, our current range can be found in the download area.					

4 Technical data

Input data		
•	400 V A O	
Nominal input voltage	100 V AC 240 V AC	
Input voltage range	85 V AC 264 V AC	
AC frequency range	45 Hz 65 Hz	
Current consumption	1.7 A (120 V AC) 1 A (230 V AC)	
Inrush current limitation	< 30 A (typical)	
l ² t	< 1.5 A ² s	
Typical response time	<1s	
Power failure bypass	> 20 ms (120 V AC) > 85 ms (230 V AC)	
Protective circuit	Transient surge protection Varistor	
Input fuse, integrated	4 A (slow-blow, internal)	
Choice of suitable fuses	6 A 16 A (Characteristics B, C, D, K)	
Input connection data		
Connection method	Screw connection	
Conductor cross section, solid	0.2 mm ² 2.5 mm ²	
Conductor cross section, stranded	0.2 mm ² 2.5 mm ²	
Conductor cross section AWG/kcmil	24 14	
Stripping length	8 mm	
Screw thread	M3	
Tightening torque	0.5 Nm 0.6 Nm	
Output data		
Nominal output voltage	12 V DC ±1%	
Output current	8.3 A (-25°C 55°C)	
Derating	55 °C 70 °C (2.5%/K)	
Control deviation	< 1 % (change in load, static 10 % 90 %) < 3 % (Dynamic load change 10 % 90 %, 10 Hz) < 0.1 % (change in input voltage ±10 %)	
Ascent time	< 0.5 s (U _{OUT} (10 % 90 %))	
Residual ripple	< 75 mV _{PP} (with nominal values)	
Connection in parallel	yes, with redundancy module	
Connection in series	Yes	
Protection against surge voltage on the output	≤ 25 V DC	
Resistance to reverse feed	<	
Output connection data		
Connection method	Screw connection	
Conductor cross section, solid	0.2 mm ² 2.5 mm ²	
Conductor cross section, stranded	0.2 mm ² 2.5 mm ²	
Conductor cross section AWG/kcmil	24 14	
Stripping length	8 mm	
- 11 3 - 3		
Screw thread	M3	

Power consumption

Efficiency > 89.5 % < 0.4 W Maximum power dissipation NO-Load Power loss nominal load max. < 12 W

General data

Insulation voltage input/output 4 kV AC (type test) 3 kV AC (routine test)

MTBF > 500000 h (According to EN 29500)

Housing material polycarbonate Foot latch material Plastic POM

Dimensions W / H / D 55 mm / 90 mm / 84 mm

Weight 0.34 kg

Security

IP20 Degree of protection

Protection class II (in closed control cabinet)

SELV IEC 60950-1 (SELV) and EN 60204 (PELV)

Ambient conditions

-25 °C ... 70 °C (> 55° C derating) Ambient temperature (operation)

-40 °C ... 85 °C Ambient temperature (storage/transport)

Max. permissible relative humidity (operation) ≤ 95 % (at 25 °C, non-condensing)

Vibration (operation) < 15 Hz, amplitude ±2.5 mm (according to IEC 60068-2-6)

15 Hz ... 150 Hz, 2.3g, 90 min.

Shock 30 g in each direction, according to IEC 60068-2-27

Pollution degree 2

Climatic class 3K3 (in acc. with EN 60721)

Inflammability class in acc. with UL 94 (housing) V0

Standards

Electrical Equipment for Machinery FN 60204-1

Electrical safety (of information technology equipment - Safety - Part 1) IEC 60950-1/VDE 0805 (SELV) Electronic equipment for use in electrical power installations EN 50178/VDE 0160 (PELV)

IEC 60950-1 (SELV) and EN 60204 (PELV)

Safe isolation DIN VDE 0100-410 Protection against electric shock DIN 57100-410 EN 61000-3-2 Limitation of mains harmonic currents Network version/undervoltage EN 61000-4-11

Information technology equipment - Safety (CB Scheme) CB Scheme

Approvals

UL approvals UL/C-UL listed UL 508

UL/C-UL Recognized UL 60950

CSA CAN/CSA-C22.2 No. 60950-1-07

CSA-C22.2 No. 107.1-01



Current approvals/permissions for the product can be found in the download area under phoenixcontact.net/products.

PHOENIX CONTACT 105987_en_00

Noise immunity according to EN 61000-6-2			
		EN 61000-6-2 requirement	Tested
Electrostatic discharge EN 61000-4-2			
Housing contact di	ischarge	4 kV (Test intensity 2)	6 kV (Test intensity 3)
Housing air di	ischarge	8 kV (Test intensity 3)	8 kV (Test intensity 3)
Co	mments	Criterion B	Criterion B
Electromagnetic HF field EN 61000-4-3			
Frequenc	cy range	80 MHz 1 GHz	80 MHz 1 GHz
Test field:	strength	10 V/m	10 V/m
Frequenc	cy range	1.4 GHz 2 GHz	1 GHz 2 GHz
Test field:	strength	3 V/m	10 V/m
Frequenc	cy range	2 GHz 2.7 GHz	2 GHz 3 GHz
Test field:	strength	1 V/m	10 V/m
Co	mments	Criterion A	Criterion A
Fast transients (burst) EN 61000-4-4			
	Input	2 kV (Test intensity 3 - asymmetrical)	4 kV (Test intensity 4 - asymmetrical
	Output	2 kV (Test intensity 3 - asymmetrical)	2 kV (Test intensity 3 - asymmetrical
Co	mments	Criterion B	Criterion B
Surge current loads (surge) EN 61000-4-5			
	Input	1 kV (Test intensity 2 - symmetrical) 2 kV (Test intensity 3 - asymmetrical)	2 kV (Test intensity 3 - symmetrical) 4 kV (Test intensity 4 - asymmetrical
	Output	0.5 kV (Test intensity 1 - symmetrical) 0.5 kV (Test intensity 1 - asymmetrical)	1 kV (Test intensity 2 - symmetrical) 2 kV (Test intensity 3 - asymmetrical
Co	mments	Criterion B	Criterion B
Conducted interference EN 61000-4-6			
Frequenc	cy range	10 kHz 80 MHz	10 kHz 80 MHz
	Voltage	10 V (Test intensity 3)	10 V (Test intensity 3)
Co	mments	Criterion A	Criterion A
Oritorion A		Normal aparating behavior within the an	acified limits
Criterion A Criterion B		Normal operating behavior within the sp Temporary impairment to operational be	
Citterion B		elf.	mayor maris corrected by the device
Emitted interference in acc. with EN 61000-6-3			
Radio interference voltage in acc. with EN 55011		EN 55011 (EN 55022) Class B, area of a	application: Industry and residential
Emitted radio interference in acc. with EN 55011		EN 55011 (EN 55022) Class B, area of a	application: Industry and residential



relative humidity at 100 m above sea level.

PHOENIX CONTACT 6 105987_en_00

5 Intended use

This power supply unit features IP20 protection and is intended for installation in housing. It is suitable for use in industrial applications.

6 Structure

6.1 Device elements





Bild 1 Device elements

- 1. Input voltage: Input AC L/N
- 2. Output voltage: Output DC+/-
- 3. Green LED: DC OK
- 4. Universal snap-on foot: 35 mm DIN rail according to EN 60715

6.2 Block diagram



Element	Meaning
=	Fuse
\bowtie	Decoupling
1	Switch
	Transmitter
\sim	Filter
	Disconnect transducer
	Controller

7 Assembly

7.1 Unpacking

Before mounting the power supply unit, it must be checked for damage:

- Take the device out of its packaging.
- Check the device for any damage sustained during transport.
- Retain the package slip for future use.
- Dispose of packaging in an environmentally-friendly way.

7.2 Mounting the power supply unit



The power supply unit is intended for installation in a distributor box or control cabinet.



The power supply unit is designed for convection cooling. Maintain a minimum distance from other devices in order to ensure convection cooling.






Bild 2 Convection


Please note the following before mounting the power supply unit:

 The minimum distance from other devices that must be observed in order to ensure convection cooling is: 30 mm vertically, 0 mm horizontally



- The device dimensions





7.3 Mounting on a DIN rail

The power supply unit can be installed on all 35 mm DIN rails according to EN 60175.




Bild 3 Mounting on a DIN rail

7.4 Normal mounting position

When installed, the input terminal blocks must be at the bottom and the output terminal blocks at the top.

If the power supply unit is installed in a mounting position other than the normal mounting position, the output power must be reduced.




Bild 4 Normal mounting position

8 Installing the power supply unit

8.1 Safety regulations and installation notes



WARNING: risk of electric shock!

Only qualified specialist personnel may install, start up, and operate the device. Observe the national safety and accident prevention regulations.

Prior to installation, disconnect the input voltage and make sure that it cannot be switched on again unintentionally.

Mains connection must be performed by specialist personnel and protection against electric shock ensured.

Make sure that the device can be switched off outside the power supply according to the regulations in EN 60950 (e.g., by line protection on the primary side).

Cover termination area after installation in order to avoid accidental contact with live parts (e.g., by installing in a control cabinet).

Protect the device against ingress by foreign bodies, e.g., paper clips or metal parts.



WARNING: risk of electric shock!

Make sure that all supply lines are sufficiently dimensioned and have sufficient fuse protection.

Make sure that all output cables are dimensioned accordingly for the maximum device output current or have separate fuse protection.



WARNING: risk of electric shock!

Never open or repair the device yourself.

Internal fuses will only blow in the event of device malfunction. Do not modify or attempt to repair the device. Send the device to the factory for examination.

8.2 Mains connection

The device can be connected to single-phase AC or three-phase power grids (TN-S, TN-C, TT, and IT) while considering the nominal input voltage.



For operation on two of the phase conductors of a three-phase system, an isolating facility for all poles must be provided.




Bild 5 Network types

8.3 Device connections

Screw connection for input AC L/N




Bild 6 Screw connection for input AC L/N

Screw connection for output DC +/-




Bild 7 Screw connection for output DC +/-

8.4 Connecting cables



Use copper cables with an operating temperature > 75°C (ambient temperature < 55°C) and > 90°C (ambient temperature < 75°C).




Bild 8 Connecting cables

- Connect the supply lines to the input AC L/N connection terminal blocks.
- Connect the output cables to the output DC +/- connection terminal blocks.

The power supply unit is operational as soon as the input terminal blocks are supplied with voltage.

9 Operating behavior of the power supply unit

9.1 Normal operation

In normal operation, the loads are supplied with a constant output voltage of 12 V DC.

9.2 Overload response

In the event of overload ($I > I_N$), the device reduces its output voltage. If the output voltage is greater than $U_N \times 0.9$, the green DC OK LED lights up. If the output voltage drops below $U_N \times 0.5$, the device shuts down. After a short time, the device attempts to start up again. If the overload has been rectified, it will start up as normal. If the overload has still not been rectified, it will shut down again and attempt to restart again (automatic restart).




Bild 9 Output characteristic curve

9.3 Behavior at ambient temperatures > 55°C

At an ambient temperature of up to 55 °C, the power supply unit supplies the nominal output current. At ambient temperatures upwards of 55 °C, the output power must be reduced by 2.5 % per Kelvin temperature increase (temperature-dependent derating).




Bild 10 Temperature-dependent derating

70


80 [°C]

9.4 Behavior in the case of alternative mounting positions


For mounting positions that differ from the normal mounting position, the output power must be reduced (position-dependent derating).

The characteristic curve can be used to determine the maximum output power to be drawn for each ambient temperature for different mounting positions.


Normal mounting position




Rotated mounting position 90° X-axis




Rotated mounting position 180° X-axis




Rotated mounting position 270° X-axis





Rotated mounting position 90° Z-axis





Rotated mounting position 270° Z-axis





10 Operating the power supply unit

10.1 Function monitoring

DC OK LED

The DC OK LED is available for visual function monitoring of the power supply unit.

	Status 1	Status 2
DC OK LED	Lit	OFF
Meaning	Output voltage > 10.5 V	Output voltage < 10.5 V, overload mode or no mains voltage
State description	The device is operating, output voltage and output current are OK	The device is in operation, but there is a fault on the side of the consumer; the current consumption is greater than I_N or the output is short-circuited. The device is out of operation because there is no mains voltage, the fuse on the primary side has been triggered, or the device is faulty.
Remedy		Remove the error at the load, use a more powerful power supply unit, connect a power supply unit of the same type parallel to the existing device, remove the short circuit, apply mains voltage, enable the fuse again or replace the power supply unit.

10.2 Operating power supply units in parallel

Power supply units of the same type can be connected in parallel to increase both redundancy and power.



To ensure symmetrical current distribution, all cable connections from the power supply unit to the busbar must be the same length and have the same conductor cross section.

Redundant operation

Redundant circuits are suitable for supplying systems which place particularly high demands on operational safety. If a fault occurs in the primary circuit of the first power supply unit, the second device automatically takes over the complete power supply without interruption, and vice versa.

Using a redundancy module, it is possible for two power supply units of the same type that are connected in parallel on the output side for redundancy to be decoupled from one another.




Bild 11 Redundant circuit with redundancy module

Increased performance

Power supply units of the same type can be connected in parallel to increase the power to n x I_N . Parallel connection is recommended if existing systems are to be extended and the power supply unit that is installed here does not cover the current consumption of the most powerful load. Otherwise, the loads should be distributed between individual devices that are independent of one another.

Using a redundancy module, it is possible for two power supply units of the same type that are connected in parallel on the output side to increase power to be decoupled from one another.




Bild 12 Parallel connection to increase power with a redundancy module

10.3 Operating the power supply unit in series

Two devices can be connected in series to double the voltage. Only power supply units of the same type should be connected in series. Series connection should always be used when the output voltage of the module is not sufficient. For example, devices with 24 V DC nominal output voltage each supply 48 V DC in series. Depending on the specification of functional earth ground, output voltages of \pm 48 V/48 V as well as \pm 24 V DC can also be made available.





Bild 13 Series operation

11 Removal

11.1 Removing the power supply unit



11.2 Notes on disposal



Do not dispose of the power supply unit with household waste. It should be disposed of in accordance with the currently applicable national regulations.