

Cisco Catalyst 9300 Series Switches

Built for Security, IoT, Mobility, and Cloud

The Cisco® Catalyst® 9300 Series Switches are Cisco's lead stackable enterprise switching platform built for security, IoT, mobility, and cloud. They are the next generation of the industry's most widely deployed switching platform. The Catalyst 9300 Series switches form the foundational building block for Software-Defined Access (SD-Access), Cisco's lead enterprise architecture. At 480 Gbps, they are the industry's highest-density stacking bandwidth solution with the most flexible uplink architecture. The Catalyst 9300 Series is the first optimized platform for high-density 802.11ac Wave2. It sets new maximums for network scale. These switches are also ready for the future, with an x86 CPU architecture and more memory, enabling them to host containers and run third-party applications and scripts natively within the switch.

The Catalyst 9300 Series is designed for Cisco StackWise[®] virtual technology, providing flexible deployment with support for nonstop forwarding with stateful switchover (NSF/SSO), for the most resilient architecture in a stackable (sub-50-ms) solution. The highly resilient and efficient power architecture features Cisco StackPower[®], which delivers high-density Cisco Universal Power Over Ethernet (Cisco UPOE[®]) and Power over Ethernet Plus (PoE+) ports. The switches are based on the Cisco Unified Access[™] Data Plane 2.0 (UADP) 2.0 architecture which not only protects your investment but also allows a larger scale and higher throughput. A modern operating system, open Cisco IOS XE with programmability offers advanced security capabilities and Internet of Things (IoT) convergence.

The Foundation of Software-Defined Access

Advanced persistent security threats. The exponential growth of Internet of Things (IoT) devices. Mobility everywhere. Cloud adoption. All of these require a network fabric that integrates advanced hardware and software innovations to automate, secure, and simplify customer networks. The goal of this network fabric is to enable customer revenue growth by accelerating the rollout of business services.

The Cisco Digital Network Architecture (Cisco DNA[™]) with SD-Access is the network fabric that powers business. It is an open and extensible, software-driven architecture that accelerates and simplifies your enterprise network operations. The programmable architecture frees your IT staff from time-consuming, repetitive network configuration tasks so they can focus instead on innovation that positively transforms your business. SD-Access enables policy-based automation from edge to cloud with foundational capabilities. These include:

- · Simplified device deployment
- · Unified management of wired and wireless networks
- · Network virtualization and segmentation
- · Group-based policies
- Context-based analytics

Product Overview: Features

Product Highlights

- Highest wireless scale with Wave 2 access points supported on a single switch with select models
- UADP 2.0 Application-Specific Integrated Circuit (ASIC) with programmable pipeline and microengine capabilities, along with template-based, configurable allocation of Layer 2 and Layer 3 forwarding, access control lists (ACLs), and quality of service (QoS) entries
- Intel[®] x86 CPU complex with 8-GB memory, and 16 GB of flash and external USB 3.0 SSD pluggable storage slot to host containers
- USB 2.0 slot to load system images and set configurations
- · Up to 480 Gbps of local stackable switching bandwidth
- Flexible and dense uplink offerings with 1G, Multigigabit, 10G, and 40G, with platform readiness for 25G
- · Flexible downlink options with 1G and Multigigabit links
- Leading PoE capabilities with up to 384 ports of PoE per stack, 60W Cisco UPOE, and PoE+
- Intelligent Power Management with Cisco StackPower technology, providing power stacking among members for power redundancy
- · Line-rate, hardware-based Flexible NetFlow (FNF), delivering flow collection of up to 64,000 flows
- IPv6 support in hardware, providing wire-rate forwarding for IPv6 networks
- Dual-stack support for IPv4/IPv6 and dynamic hardware forwarding table allocations, for ease of IPv4-to-IPv6 migration
- Open IOS XE, a modern operating system for the enterprise with support for model-driven programmability including NETCONF, RESTCONF, YANG, on-box Python scripting, streaming telemetry, container-based application hosting, and patching for critical bug fixes. The OS also has built-in defenses to protect against runtime attacks
- SD-Access: The Cisco Catalyst 9300 Series Switches form the foundational building block for SD-Access,
 Cisco's lead enterprise architecture:
 - Policy-based automation from edge to cloud
 - Simplified segmentation and micro-segmentation, with predictable performance and scalability
 - Automation through the Cisco Application Policy Infrastructure Controller Enterprise Module (APIC-EM)
 - Policy handled through the Cisco Identity Services Engine (ISE)
 - Network assurance provided through the Network Data Platform
 - Faster launch of new business services and significantly improved issue resolution time
- Plug and Play (PnP) enabled: A simple, secure, unified, and integrated offering to ease new branch or campus device rollouts or updates to an existing network

· Advanced security:

- Encrypted Traffic Analytics (ETA): You benefit from the power of machine learning to identify and take
 actions toward threats or anomalies in your network, including malware detection in encrypted traffic
 (without decryption) and distributed anomaly detection
- Support for AES-256 with the powerful MACsec 256-bit encryption algorithm available on all models
- Trustworthy systems: Hardware anchored Secure Boot and Secure Unique Device Identification (SUDI)
 support for Plug and Play, to verify the identity of the hardware and software

Platform Details

Switch Models and Configurations

The Cisco Catalyst 9300 Series is made up of seven different switch models. Any of the models can be used together in a stack of up to eight units.

Figure 1. Cisco Catalyst 9300 Series Switches



Table 1 lists port scale and power details for the Cisco Catalyst 9300 Series models.

 Table 1.
 Cisco Catalyst 9300 Series Switch Configurations

Model	Total 10/100/1000 or Multigigabit copper ports	Default AC power supply	Available PoE power	Cisco StackWise-480	Cisco StackPower
C9300-24T	24	350W AC		Yes	Yes
C9300-48T	48	350W AC		Yes	Yes
C9300-24P	24 POE+	715W AC	445W	Yes	Yes
C9300-48P	48 POE+	715W AC	437W	Yes	Yes
C9300-24U	24 Cisco UPOE	1100W AC	830W	Yes	Yes
C9300-48U	48 Cisco UPOE	1100W AC	822W	Yes	Yes
C9300-24UX	24 Multigigabit Cisco UPOE (100 Mbps or 1, 2.5, 5, or 10 Gbps)	1100W AC	490W	Yes	Yes

Network Modules

The Cisco Catalyst 9300 Series Switches support optional network modules for uplink ports. The default switch configuration does not include the network module. When you purchase the switch, you can choose from the network modules described in Table 2.

Figure 2. Cisco Catalyst 9300 Series Network Modules



 Table 2.
 Network Module Numbers and Descriptions

Network module	Description
C9300-NM-4G	9300 Series 4x 1G Network Module
C9300-NM-8X	9300 Series 8x 10G Network Module
C9300-NM-2Q	9300 Series 2x 40G Network Module
C9300-NM-4M	9300 Series 4x Multigigabit Network Module

Please note: Existing 3850 network modules are also supported in the Cisco Catalyst 9300 Series platforms.

For additional details, please read our FAQs:

https://www.cisco.com/c/dam/en/us/products/collateral/switches/catalyst-9300-series-switches/nb-09-cat-9k-faq-cte-en.pdf

Power Supplies

The Cisco Catalyst 9300 Series Switches support dual redundant power supplies. The switches ship with one power supply by default, and the second power supply can be purchased when the switch is ordered or at a later time. If only one power supply is installed, it should always be in power supply bay #1. The switches also ship with three field-replaceable fans.

Figure 3. Cisco Catalyst 9300 Series Dual Redundant Power Supplies



Table 3 lists the different power supplies available in these switches and available PoE power.

 Table 3.
 Power Supply Models

Models	Default power supply	Available PoE power
24-port data switch	PWR-C1-350WAC	-
48-port data switch	PWR-C1-350WAC	
24-port PoE+ switch	PWR-C1-715WAC	445W
48-port PoE+ switch	PWR-C1-715WAC	437W
24-port Cisco UPOE switch	PWR-C1-1100WAC	830W
48-port Cisco UPOE switch	PWR-C1-1100WAC	822W
24-port Multigigabit Cisco UPOE switch	PWR-C1-1100WAC	490W – Support in Open Cisco IOS XE 16.6

Performance and Scalability

Performance and scalability metrics for the Catalyst 9300 Series are provided in Table 4.

Table 4. Performance Specifications

Description F	Performance
2	208 Gbps on 24-port Gigabit Ethernet model 256 Gbps on 48-port Gigabit Ethernet model 640 Gbps on 24-port Multigigabit Ethernet model
Stacking bandwidth 4	480 Gbps
Total number of MAC addresses 3	32,000
Total number of IPv4 routes (ARP plus learned routes)	32,000 (24,000 direct routes and 8000 indirect routes)
IPv4 routing entries 3	32,000
IPv6 routing entries	16,000
Multicast routing scale	8000
QoS scale entries 5	5120
ACL scale entries 5	5120
·	16 MB buffer for 24- or 48-port Gigabit Ethernet models 32 MB buffer for 24-port Multigigabit
	64,000 flow on 24- and 48-port Gigabit Ethernet models 128,000 flows on 24-port Multigigabit
DRAM 8	3 GB
Flash 1	16 GB
VLAN IDs 4	4000
Total Switched Virtual Interfaces (SVIs)	2000
Jumbo frames	9198 bytes
Total routed ports per 9300 Series stack	208
Wireless	
·	Up to 96 Gbps on 48-port Gigabit Ethernet model Up to 48 Gbps on 24-port Gigabit Ethernet model
Forwarding rate of switch models (with 2x 40 Gigabit Ethernet uplinks for	or 24-port models and 48-port models)
Model F	Forwarding rate
C9300-24T 1	154.76 Mpps
C9300-24P 1	154.76 Mpps

Description	Performance
C9300-48T	190.48 Mpps
C9300-48P	190.48 Mpps
C9300-48U	190.48 Mpps
C9300-24UX	400 Mpps
Forwarding rate for both IPv4 and IPv6	

SD-Access Architecture

What if you could give time back to IT? Provide network access in minutes for any user or device to any application – without compromise? SD-Access is industry's first policy-based automation from network edge to cloud. Your foundation for your digital network, Cisco[®] Software-Defined Access (SD-Access). Built on the principles of the Cisco Digital Network Architecture (Cisco DNA[™]), SD-Access provides end-to-end segmentation to keep user, device and application traffic separate without a redesign of the network. It automates user access policy so organizations can make sure the right policies are set for any user or device with any application across the network. This is all done with a single network fabric, to enable a consistent user experience anywhere without compromising on security, meaning common user policy for LAN, WAN and

There are many challenges today in managing the network to drive business outcomes. These limitations are due to manual configuration and fragmented tool offerings. SD-Access provides:

- A transformational management solution that reduces operational expenses and enhances business agility
- · Consistent management of wired and wireless network provisioning and policy
- · Automated network segmentation and group-based policy
- Contextual insights for fast issue resolution and capacity planning
- Open and programmable interfaces for integration with third-party solutions

For an overview of key use-cases SD-Access addresses, refer to SD-Access Solution Overview.

Platform Benefits

Cisco IOS XE opens a completely new paradigm in network configuration, operation, and monitoring through network automation. Cisco's automation solution is open, standards-based, and extensible across the entire lifecycle of a network device. The various automation mechanisms are outlined below.

- Automated device provisioning is the ability to automate the process of upgrading software images and
 installing configuration files on Cisco Catalyst switches when they are being deployed in the network for the
 first time. Cisco provides both turnkey solutions such as Plug and Play and off-the-shelf tools such as ZeroTouch Provisioning (ZTP) and Preboot Execution Environment (PXE) that enable an effortless and
 automated deployment.
- API-driven configuration is available with modern network switches such as the Cisco Catalyst 9300
 Series. It supports a wide range of automation features and provides robust open APIs over NETCONF
 using YANG data models for external tools, both off-the-shelf and custom built, to automatically provision
 network resources.
- Granular visibility enables model-driven telemetry to stream data from a switch to a destination. The data
 to be streamed is identified through subscription to a data set in a YANG model. The subscribed data set is
 streamed to the destination at specified intervals. Additionally, Open IOS-XE enables the push model. It
 provides near-real-time monitoring of the network, leading to quick detection and rectification of failures.

• Seamless software upgrades and patching supports OS resilience. Open IOS-XE supports patching, which provides fixes for critical bugs and security vulnerabilities between regular maintenance releases. This support lets you add patches without having to wait for the next maintenance release.

Security

- Encrypted Traffic Analytics (ETA) is a unique capability for identifying malware in encrypted traffic coming
 from the access layer. Since more and more traffic is becoming encrypted, the visibility this feature affords
 for threat detection is critical for keeping your network secure at different layers.
- AES-256 MACsec encryption is the IEEE 802.1AE standard for authenticating and encrypting packets between switches. The Catalyst 9300 Series switches support 256-bit and 128-bit Advanced Encryption Standard (AES) on all ports at all speeds, providing the most secure link encryption.
- Trustworthy systems built with Cisco Trust Anchor Technologies provide a highly secure foundation for Cisco products. With The Catalyst 9300 Series, these technologies enable hardware and software authenticity assurance for supply chain trust and strong mitigation against man-in-the-middle attacks that compromise software and firmware. Trust Anchor capabilities include:
 - Image signing: Cryptographically signed images provide assurance that the firmware, BIOS, and other software are authentic and unmodified. As the system boots, the system's software signatures are checked for integrity.
 - Secure Boot: Cisco Secure Boot technology anchors the boot sequence chain of trust to immutable
 hardware, mitigating threats against a system's foundational state and the software that is to be loaded,
 regardless of a user's privilege level. It provides layered protection against the persistence of illicitly
 modified firmware.
 - Cisco Trust Anchor module: A tamper-resistant, strong cryptographic, single-chip solution provides
 hardware authenticity assurance to uniquely identify the product so that its origin can be confirmed to
 Cisco. This provides assurance that the product is genuine.

Resiliency and High Availability

- **StackWise-480:** The Catalyst 9300 Series supports the industry's highest back-panel stacking bandwidth solution (480 Gbps) with StackWise-480.
- Cisco StackPower: Cisco StackPower is an innovative power interconnect system that allows the power supplies in a stack to be shared as a common resource among all the switches. This allows you to simply add one extra power supply in any switch of the stack and either provide power redundancy for any of the stack members or simply add more power to the shared pool.

Figure 4. Cisco Catalyst 9300 Series StackPower



- High availability: The Catalyst 9300 Series supports high-availability features, including the following:
 - Cross-stack EtherChannel provides the ability to configure Cisco EtherChannel technology across different members of the stack for high resiliency.
 - IEEE 802.1s Multiple Spanning Tree Protocol (MSTP) provides rapid spanning tree convergence independent of spanning tree timers and also offers the benefit of Layer 2 load balancing and distributed processing.
 - Per-VLAN Rapid Spanning Tree (PVRST+) allows rapid spanning tree (IEEE 802.1w) reconvergence on a per-VLAN spanning tree basis, providing simpler configuration than MSTP. In both MSTP and PVRST+ modes, stacked units behave as a single spanning tree node.
 - Switch-port auto-recovery ("err-disable" recovery) automatically attempts to reactivate a link that is disabled because of a network error.
 - The Catalyst 9300 Series platform delivers the best NSF/SSO resiliency architecture in a stackable solution with sub-50-ms failover.

Flexible NetFlow

• Flexible NetFlow (FNF): Cisco IOS® Software FNF is the next generation in flow visibility technology. It enables optimization of the network infrastructure, reduces operation costs, and improves capacity planning and security incident detection with increased flexibility and scalability. The Catalyst 9300 Series is capable of up to 64,000 flow entries on 48-port and 24 port models and up to 128,00 flow entries on 24-port mGig.

Application Visibility and Control

• NBAR2: Next-Generation Network-Based Application Recognition (NBAR2) enables advanced application classification techniques, accuracy with up to 1400 predefined and well-known application signatures and up to 150 encrypted applications on the Cisco Catalyst 9000 Series. The most popular applications included are Skype, Office 365, Microsoft Lync, Cisco WebEx[®], and Facebook, among many others that are predefined and easy to configure. NBAR2 provides the network administrator with an important tool to identify, control, and monitor end-user application usage while helping ensure a quality user experience and securing the network from malicious attacks. NBAR2 leverages FNF to report application performance and activities within the network to any supported NetFlow collector, such as Cisco Prime[®], Cisco Stealthwatch[®], or any compliant third-party tool.

QoS

• Superior QoS: The Cisco Catalyst 9300 Series offers Gigabit Ethernet speeds with intelligent services that keep traffic flowing smoothly, even at 10 times the normal network speed. Industry-leading mechanisms for cross-stack marking, classification, and scheduling deliver superior performance for data, voice, and video traffic at wire speed. Superior QoS includes granular wireless bandwidth management and fair sharing, 802.1p Class of Service (CoS) and Differentiated Services Code Point (DSCP) field classification, Shaped Round Robin (SRR) scheduling, Committed Information Rate (CIR), and eight egress queues per port.

Service Discovery

Multicast DNS (mDNS) gateway: This service discovery gateway capability facilitates sharing of services
advertised using the Apple mDNS (Bonjour) protocol, such as printers, Apple TVs, and file services across
the network. Additionally, the administrator can create policies defining which services can be seen and
accessed by the users in the network. This capability facilitates a Bring-Your-Own-Device (BYOD) rollout.

Smart Operation

- Bluetooth ready: The Catalyst 9300 Series has hardware support to connect a Bluetooth dongle to your switch, enabling you to use this wireless interface as an IP management port interface. The port can be used for configuration and troubleshooting using WebUI or the Command-Line Interface (CLI), and to transfer images and configurations.
- WebUI: WebUI is an embedded GUI-based device-management tool that provides the ability to provision
 the device, to simplify device deployment and manageability, and to enhance the user experience. It comes
 with the default image, so there is no need to enable anything or install any license on the device. You can
 use WebUI to build configurations, and to monitor and troubleshoot the device without having CLI expertise.
- Efficient switch operation: Cisco Catalyst 9300 Series Switches provide optimum power saving with Energy Efficient Ethernet (EEE) on the RJ-45 ports and low-power operations for industry best-in-class power management and power consumption capabilities. The ports support reduced power modes so that ports not in use can move into a lower power utilization state. Other efficient switch operation features are as follows:
 - Per-port power consumption command allows customers to specify a maximum power setting on an individual port.
 - Per-port PoE power sensing measures actual power being drawn, enabling more intelligent control of powered devices. The PoE MIB provides proactive visibility into power usage and allows you to set different power-level thresholds.
- **RFID tags:** The Catalyst 9300 Series switches have an embedded RFID tag that facilitates easy asset and inventory management using commercial RFID readers.
- Blue beacon: The Catalyst 9300 Series switches support a blue beacon LED for easy identification of the switch being accessed.

High-Performance IP Routing

The Cisco Express Forwarding hardware routing architecture delivers extremely high-performance IP routing in Cisco Catalyst 9300 Series Switches, based on:

- IP unicast routing protocols (including static, Routing Information Protocol Version 1 [RIPv1], RIPv2, RIPng, and Open Shortest Path First [OSPF], Routed Access) are supported for small network routing applications with the Network Essentials stack. Equal-cost routing facilitates Layer 3 load balancing and redundancy across the stack.
- Advanced IP unicast routing protocols (including Full [OSPF], Enhanced Interior Gateway Routing Protocol [EIGRP], Border Gateway Protocol Version 4 [BGPv4], and Intermediate System-to-Intermediate System Version 4 [IS-ISv4]) are supported for load balancing and for constructing scalable LANs. IPv6 routing (using OSPFv3 and EIGRPv6) is supported in hardware for maximum performance.
- Protocol-Independent Multicast (PIM) for IP multicast routing is supported, including PIM sparse mode (PIM SM), and Source-Specific Multicast (SSM).
- IPv6 addressing is supported on interfaces with appropriate show commands for monitoring and troubleshooting.

Multigigabit Ethernet technology: Cisco Multigigabit Ethernet technology allows you to achieve bandwidth speeds from 1 Gbps to 10 Gbps over traditional Category 5e cabling or above. This technology addresses the need for exponential increases in bandwidth with the enormous growth of 802.11ac and new wireless applications without having to replace current cabling infrastructure.

Power Over Ethernet Leadership

Cisco Universal Power over Ethernet (Cisco UPOE): PoE removes the need for wall sockets to power each PoE-enabled device and eliminates the cost of additional electrical cabling and circuits that would otherwise be necessary in IP phone and WLAN deployments. Cisco UPOE extends the IEEE PoE+ standard to double the power per port to 60 watts. This facilitates delivery of network power to a broad range of devices requiring higher power, including virtual desktop terminals, IP turrets, compact switches, building management gateways, LED lights, wireless access points, and IP phones. The Catalyst 9300 Series supports Cisco UPOE, PoE+ and PoE, thereby addressing the largest range of network power needs.

Tables 5 and 6 show the power supply combinations required for different PoE needs.

Table 5. Power Supply Requirements

	24-port PoE switch	48-port PoE switch
PoE on all ports (15.4W per port)	1 PWR-C1-715WAC	1 PWR-C1-1100WAC or 2 PWR-C1-715WAC
PoE+ on all ports (30W per port)	1 PWR-C1-1100WAC or 2 PWR-C1-715WAC	2 PWR-C1-1100WAC or 1 PWR-C1-1100WAC and 1 PWR-C1-715WAC

Power Supply Requirements for Cisco UPOE

	24-port Cisco UPOE switch	48-port Cisco UPOE switch	24-port Multigigabit Cisco UPOE switch
Cisco UPOE (60W per port) on all ports (24-port switch) or up to 30 ports (48-port switch)	1 PWR-C1-1100WAC and 1 PWR- C1-715WAC	2 PWR-C1-1100WAC	2 PWR-C1-1100WAC

- **Perpetual PoE:** With Perpetual PoE, the PoE power is maintained during a switch reload. This is important for IoT endpoints such as PoE-powered lights, so that there is no disruption during switch reboot.
- Fast PoE: When power is restored to a switch, PoE starts delivering power to endpoints without waiting for the operating system to fully load, thereby speeding up the time for the endpoint to start up.

Software Requirements

Cisco Catalyst 9300 Series Switches run on Open IOS XE 16.5.1a release or later. This software release includes all the features listed earlier in the Platform Benefits section.

Packaging

The Cisco Catalyst 9000 family of switches introduces a new and simplified licensing package in the form of base and add-on licenses.

- The base licensing package includes the Network Essentials and Network Advantage licensing options
 that are tied to the hardware. Between them, the base licensing packages cover switching fundamentals,
 management automation, troubleshooting, and advanced switching features.
- The add-on licensing package includes the Cisco DNA Essentials and Cisco DNA Advantage options. In addition to on-box capabilities, the features available with this package provide Cisco innovations on the switch, as well as on Cisco DNA Center, in the APIC-EM.

License consumption is easily determined by the package itself. While base licenses are always permanent and without an expiration date, add-on licenses may be purchased for a 3-, 5-, or 7-year term (and hence are also known as term-based licenses). Table 7 shows the combinations of base and add-on licenses may be purchased.

Licensing Combinations

	Cisco DNA Essentials	Cisco DNA Advantage
Network Essentials	Yes	No
Network Advantage	Yes	Yes

^{*} For this combination, the Cisco DNA Essentials license must be ordered separately using Cisco Smart Software Manager.

Ordering and managing licenses with Smart Accounts: Creating Smart Accounts by using the Cisco Smart Software Manager (SSM) enables you to order devices and licensing packages and also manage your software licenses from a centralized website. You can set up Cisco SSM to receive daily email alerts and to be notified of expiring add-on licenses that you want to renew.

You must order an add-on license in order to purchase a switch. When the license term expires, you can either renew the add-on license to continue using it or deactivate the add-on license and then reload the switch to continue operating with the base license capabilities.

Both the base and add-on licenses are also available for a 90-day evaluation period. An evaluation license is activated temporarily, without purchase. An expired evaluation license cannot be reactivated after reload.

Note: It is not required to deploy Cisco DNA Center just to use one of the above packages.

Table 6 shows the features included in the Essentials and Advantage packages.

 Table 6.
 Essentials and Advantage Package Features

Features	Network Essentials	Network Advantage	Cisco DNA Essentials	Cisco DNA Advantage
Switch features				
Switch fundamentals Spanning Tree Protocol (STP), Rapid STP (RSTP), VLAN Trunking Protocol (VTP), trunking, Private VLAN (PVLAN), dynamic voice VLAN, IPv6, PnP, Cisco Discovery Protocol, 802.1Q tunneling (Q-in-Q), Routed Access – OSPF and RIP, Policy-Based Routing (PBR), Virtual Router Redundancy Protocol (VRRP), Internet Group Management Protocol (IGMP), PIM Stub, Weighted Random Early Detection (WRED), First Hop Security (FHS), 802.1X, MACsec-128, Control Plane Policing (CoPP), Cisco TrustSec® SGT Exchange Protocol (SXP), IP SLA Responder, SSO, EIGRP Stub, Microflow Policing, Class-Based Weighted Fair Queuing (CBWFQ), hierarchical QoS (H-QoS), Application Reporting, Syslog, SNMP			×	×
Advanced switch capabilities and scale BGP, EIGRP, Hot Standby Router Protocol (HSRP), IS- IS, Bootstrap Router (BSR), Multicast Source Discovery Protocol (MSDP), Bidirectional PIM (PIM-BIDIR), Label Switched Multicast (LSM), IP SLA, Full OSPF	X	/	×	x
Network segmentation VPN Routing and Forwarding (VRF), Virtual Extensible LAN (VXLAN), Cisco Locator/ID Separation Protocol (LISP), Cisco TrustSec, SD-Wireless, Multiprotocol Label Switching (MPLS), Layer 3 VPN (L3VPN), Multicast VPN (mVPN)	×	/	×	x
Optimized network deployments mDNS gateway	×	X	×	✓
Automation Netconf/YANG, PnP Agent, ZTP/Open PnP	✓	1	x	×
Advanced automation Containers, Python, Cisco IOS Embedded Event Manager (EEM), Autonomic Networking Infrastructure	X	×	✓	/
Telemetry and visibility Streaming telemetry, sampled NetFlow, Switched Port Analyzer (SPAN), Remote SPAN (RSPAN)	✓	/	X	×
Advanced telemetry and visibility Flexible NetFlow, Wireshark	×	X	1	1
Optimized telemetry a visibility Encapsulated Remote SPAN (ERSPAN), Application Visibility and Control (AVC), NBAR2	X	X	X	1
High availability and resiliency NSF, Graceful Insertion and Removal (GIR), StackWise Virtual, In-Service Software Upgrade (ISSU)	X	✓	X	×
High availability and resiliency Patching	x	×	x	1
Security MACsec-256	х	1	x	х
Advanced security Encrypted Traffic Analytics (ETA)	х	х	x	✓
IOT integration Audio Video Bridging (AVB), Precision Time Protocol (PTP), Constrained Application Protocol (CoAP)	×	1	x	Х
Cisco DNA Center Features				
Day 0 network bring-up automation Cisco Network Plug-n-Play application, network settings, device credentials	×	х	1	✓

Features	Network Essentials	Network Advantage	Cisco DNA Essentials	Cisco DNA Advantage
Element management Discovery, inventory, topology, software image, licensing, and configuration management	х	×	✓	✓
Element management Patching	×	X	×	1
Network monitoring Product Security Incident Response Team (PSIRT) compliance, end-of-life/end-of-sale reporting, telemetry quotient, client 360, device 360, top talkers/ NetFlow/streaming telemetry collection and correlation	X	×	✓	✓
Static QoS configuration and monitoring EasyQoS application	x	x	1	1
Policy-based automation SD-Access, group-based policy for access, app prioritization, monitoring, and path selection; SD-Access with Integrated Wireless	х	х	х	1
Network assurance and analytics Insights driven from analytics and machine learning for the network, clients and applications that cover onboarding, connectivity, and performance	X	х	X	✓

Dimensions, Weight, Acoustic, Mean Time Between Failures

Table 7 shows the dimensions and mean time between failures of all models of 9300 Series switches.

 Table 7.
 Model Dimensions, Weight, and Mean Time Between Failures Metrics

	Dimensions (H x W x D)	
Model	Inches	Centimeters
C9300-24T	1.73 x 17.5 x 17.5	4.4 x 44.5 x 44.5
C9300-24P	1.73 x 17.5 x 17.5	4.4 x 44.5 x 44.5
C9300-24U	1.73 x 17.5 x 17.5	4.4 x 44.5 x 44.5
C9300-24UX	1.73 x 17.5 x 18.5	4.4 x 44.5 x 47.0`
C9300-48T	1.73 x 17.5 x 17.5	4.4 x 44.5 x 44.5
C9300-48P	1.73 x 17.5 x 17.5	4.4 x 44.5 x 44.5
C9300-48U	1.73 x 17.5 x 17.5	4.4 x 44.5 x 44.5
	Weight	
Model	Pounds	Kilograms
C9300-24T	16.03	7.27
C9300-24P	16.33	7.4
C9300-24U	16.63	7.54
C9300-24UX	18.18	8.25
C9300-48T	16.43	7.45
C9300-48P	16.73	7.59
C9300-48U	17.03	7.72
Mean time between failures (hours)		
C9300-24T	314,790	
C9300-24P	299,000	
C9300-24U	238,410	
C9300-24UX	214,760	
C9300-48T	305,870	

	Dimensions (H x W x D)		
C9300-48P	277,770		
C9300-48U	227,410		

Connectors

Table 8 shows the supported connectors for the Cisco Catalyst 9300 Series.

Table 8. Connectors

Connectors and cabling	• 1000BASE-T ports: RJ-45 connectors, 4-pair Cat 5E UTP cabling						
	Multigigabit-T ports: RJ-45 connectors, 4-pair Cat 5E, Cat 6, Cat 6A UTP cabling						
	• 1000BASE-T SFP-based ports: RJ-45 connectors, 4-pair Cat 5E UTP cabling						
	 100BASE-FX, 1000BASE-SX, -LX/LH, -ZX, -BX10, dense wavelength-division multiplexing (DWDM) and Coarse Wavelength-Division Multiplexing (CWDM) SFP transceivers: LC fiber connectors (single-mode or multimode fiber) 						
	 10GBASE-SR, LR, LRM, ER, ZR, DWDM SFP+ transceivers: LC fiber connectors (single-mode or multimode fiber) 						
	• QSFP						
	SFP+ connector						
	Cisco StackWise-480 stacking ports: copper-based Cisco StackWise cabling						
	Cisco StackPower: Cisco proprietary power stacking cables						
	 Ethernet management port: RJ-45 connectors, 4-pair Cat 5 UTP cabling 						
	Management console port: RJ-45-to-DB9 cable for PC connections						
Power connectors	 Customers can provide power to a switch by using either the internal power or Cisco StackPower from another member in the power stack. The connectors are located at the back of the switch. 						
	 Internal power supply connector: The internal power supply is an auto-ranging unit. It supports input voltages between 100 and 240 VAC. Use the supplied AC power cord to connect the AC power connector to an AC power outlet. 						

For the latest Cisco transceiver module compatibility information, refer to

https://www.cisco.com/c/en/us/support/interfaces-modules/transceiver-modules/products-device-support-tables-list.html.

Management and Standards Support

Table 9 shows management and standards support for the Cisco Catalyst 9300 Series.

Table 9. Management and Standards Support

Description	Specification	
Management	BRIDGE-MIB	CISCO-SNMP-TARGET-EXT-MIB
	CISCO-AUTH-FRAMEWORK-MIB	CISCO-STACKMAKER-MIB
	CISCO-BGP4-MIB, BGP4-MIB	CISCO-MEMORY-POOL-MIB
	CISCO-BRIDGE-EXT-MIB	CISCO-STP-EXTENSIONS-MIB
	CISCO-BULK-FILE-MIB	CISCO-SYSLOG-MIB
	CISCO-CABLE-DIAG-MIB	CISCO-TCP-MIB
	CISCO-CALLHOME-MIB	CISCO-UDLDP-MIB
	CISCO-CEF-MIB	CISCO-VLAN-IFTABLE-RELATIONSHIP-MIB
	CISCO-CIRCUIT-INTERFACE-MIB	CISCO-VLAN-MEMBERSHIP-MIB
	CISCO-ENTITY-VENDORTYPE-OID-MIB	CISCO-VTP-MIB
	CISCO-CONTEXT-MAPPING-MIB	EtherLike-MIB
	CISCO-DEVICE-LOCATION-MIB	HC-RMON-MIB
	CISCO-DHCP-SNOOPING-MIB	IEEE8021-PAE-MIB
	CISCO-EIGRP-MIB	IEEE8023-LAG-MIB
	CISCO-EMBEDDED-EVENT-MGR-MIB	IF-MIB
	CISCO-ENTITY-FRU-CONTROL-MIB	IGMP-MIB
	CISCO-ENTITY-SENSOR-MIB	IGMP-STD-MIB

Description	Specification	
	ENTITY-MIB	IP-FORWARD-MIB
	CISCO-ERR-DISABLE-MIB	IP-MIB
	CISCO-CONFIG-COPY-MIB	IPMROUTE-STD-MIB
	CISCO-FLOW-MONITOR-MIB	LLDP-EXT-MED-MIB
	CISCO-FTP-CLIENT-MIB	LLDP-MIB
	CISCO-HSRP-EXT-MIB	NOTIFICATION-LOG-MIB
	CISCO-HSRP-MIB	OLD-CISCO-MEMORY-MIB
	CISCO-ITSKF-WIB	CISCO-CDP-MIB
	CISCO-IF-EXTENSION-MIB	POWER-ETHERNET-MIB
	CISCO-IGMP-FILTER-MIB	RMON2-MIB
	CISCO-CONFIG-MAN-MIB	RMON-MIB
	CISCO-IP-CBR-METRICS-MIB	SNMP-COMMUNITY-MIB
	CISCO-IPMROUTE-MIB	SNMP-FRAMEWORK-MIB
	CISCO-IP-STAT-MIB	SNMP-MPD-MIB
	CISCO-IP-URPF-MIB	SNMP-NOTIFICATION-MIB
	CISCO-L2L3-INTERFACE-CONFIG-MIB	SNMP-PROXY-MIB
	CISCO-LAG-MIB	SNMP-TARGET-MIB
	CISCO-LICENSE-MGMT-MIB	SNMP-USM-MIB
	CISCO-MAC-AUTH-BYPASS-MIB	SNMPv2-MIB
	CISCO-MAC-NOTIFICATION-MIB	SNMP-VIEW-BASED-ACM-MIB
	CISCO-MDI-METRICS-MIB	TCP-MIB
	CISCO-FLASH-MIB	UDP-MIB
	CISCO-OSPF-MIB	CISCO-IMAGE-MIB
	CISCO-OSPF-TRAP-MIB	CISCO-STACKWISE-MIB
	CISCO-PAE-MIB	
	CISCO-PAGP-MIB	
	CISCO-PIM-MIB	
	CISCO-PING-MIB	
	CISCO-PORT-QOS-MIB	
	CISCO-PORT-SECURITY-MIB	
	CISCO-PORT-STORM-CONTROL-MIB	
	CISCO-POWER-ETHERNET-EXT-MIB	
	CISCO-PRIVATE-VLAN-MIB	
	CISCO-PROCESS-MIB	
	CISCO-PRODUCTS-MIB	
	CISCO-RF-MIB	
	CISCO-RTP-METRICS-MIB	
	CISCO-RTTMON-MIB	
	CISCO-SMART-INSTALL-MIB	
Standards	EEE 802.1s	RMON I and II standards
Gianualus	IEEE 802.1w	SNMPv1, v2c, and v3
		SINIVIE VI, VZC, AIIU VS
	IEEE 802.1x	
	IEEE 802.1x-Rev	
	IEEE 802.3ad	
	IEEE 802.3af	
	IEEE 802.3at	
	IEEE 802.3x full duplex on 10BASE-T, 100BASE-TX, and 1000BASE-T ports	
	IEEE 802.1D Spanning Tree Protocol	
	IEEE 802.1p CoS prioritization	
	IEEE 802.1Q VLAN	
	IEEE 802.3 10BASE-T specification	
	IEEE 802.3u 100BASE-TX specification	
	IEEE 802.3ab 1000BASE-T specification	
	IEEE 802.3z 1000BASE-X specification	
	IEEE 802.3bz 10G BASE-T specification	

Power Supply Specifications

Table 10 lists the power specifications for the Cisco Catalyst 9300 Series based on the kind of power supply used.

 Table 10.
 Power Specifications

Description	Specification						
	PWR-C1-1100WAC	PWR-C1-715WAC	PWR-C1-350WAC				
Power supply rated maximum	1100W	715W	350W				
Total output BTU (note: 1000 BTU/hr = 293W)	3793 BTU/hr, 1100W	2465 BTU/hr, 715W	1207BTU/hr, 350W				
Input-voltage range and frequency	115V to 240 VAC, 50 to 60 Hz	100 to 240 VAC, 50 to 60 Hz	100 to 240 VAC, 50 to 60 Hz				
Input current	12-6A	10-5A	4-2A				
Output ratings	-56V at 19.64A	-56V at 12.8A	-56V at 6.25A				
Output holdup time	10 ms minimum at 102.5VAC	16.7 ms minimum at 100VAC	16.7 ms minimum at 100VAC				
Power-supply input receptacles	IEC 320-C16 (IEC60320-C16)	IEC 320-C16 (IEC60320-C16)	IEC 320-C16 (IEC60320-C16)				
Power cord rating	13A	13A	10A				
Physical specifications	(H x W x D): 1.58 x 3.25 s 13.7 in Weight: 3 lb (1.4 kg)	(H x W x D): 1.58 x 3.25 x 12.20 in Weight: 2.8 lb (1.3 kg)	(H x W x D): 1.58 x 3.25 x 12.20 in Weight: 2.6 lb (1.2 kg)				
Operating temperature	23° to 113°F (-5° to 45°C)						
Storage temperature	-40° to 158°F (-40° to 70°C)						
Relative humidity operating and non-operating noncondensing	5% to 90% noncondensing						
Altitude	10,000 ft. (3000 meters), up to 45°C	;					
Mean Time Between Failures (MTBF)	Calculated MTBF must be greater th MTBF is 500,000 hr (with 90% confi	nan 300,000 using Telcordia SR-332, Midence level).	Method 1, Case 3. Demonstrated				
EMI and EMC compliance	FCC Part 15 (CFR 47) Class A ICES-003 Class A EN 55022 Class A CISPR 22 Class A AS/NZS 3548 Class A BSMI Class A (AC input models only) VCCI Class A EN 55024, EN300386, EN 50082-1, EN 61000-3-2, EN 61000-3-3 EN61000-4-2, EN61000-4-3, EN61000-4-4, EN61000-4-5, EN61000-4-6, EN 61000-6-1						
Safety compliance	UL 60950-1, CAN/CSA-C22.2 No. 6	60950-1, EN 60950-1, IEC 60950-1, CC	CC, CE Marking				
LED indicators	"AC OK": Input power to the power support of the power support of the power from						

Power Consumption of Standalone 9300 Series Switches

Table 11 shows the power consumption of standalone Cisco Catalyst 9300 Series Switches based on Alliance for Telecommunications Industry Solutions (ATIS) testing using Internet Mix (IMIX) distribution stream traffic, with input voltage of 115VAC at 60 Hz and no PoE loading. The values given are the maximum possible power consumption numbers under the respective test scenarios.

 Table 11.
 Power Consumption of Standalone 9300 Series Switches

											Meas	sured P(W	<i>I</i>)						
				Half Port Traffic					Full Port Traffic					Weighted Average Pw	No Link	PoE Te	st (No Tr	affic)	
SKU	FEP	Uplink	Input	0.01% / EEE	10%	30%	50%	100%	0.01% / EEE	10%	30%	50%	100%			25%	50%	90%	100%
C9300-	350W	Not	115Vac	77.7	86.1	89.1	89.5	89.7	77.5	91.0	91.7	91.9	92.5	89.8	78.1				
24T		Installed	230Vac	77.4	85.4	88.5	88.7	88.8	77.0	89.8	90.7	90.9	91.3	88.7	77.7				
		NM-4-	115Vac	82.5	88.4	92.1	93.3	94.1	85.9	96.0	98.9	99.7	100.0	95.4	81.2				
		1G	230Vac	81.8	87.6	90.4	92.0	92.9	84.9	94.2	96.9	97.9	98.3	93.7	80.5				
		NM-4-	115Vac	86.4	96.3	98.0	98.2	98.7	90.2	103.7	104.5	104.9	105.9	102.6	87.0				
		10G	230Vac	85.4	95.1	96.6	96.8	97.3	89.1	102.1	102.9	103.3	104.2	101.0	86.0				
		NM-2-	115Vac	84.0	94.7	95.7	95.9	96.1	87.1	101.1	101.7	102.1	103.0	99.9	83.9				
		40G	230Vac	83.2	93.6	94.4	94.6	95.1	86.2	99.2	100.1	100.5	101.4	98.1	83.2				
		NM-8-	115Vac	86.3	95.6	97.5	97.8	98.2	90.7	103.9	104.7	105.1	106.1	102.8	85.0				
		10G	230Vac	85.4	94.5	96.2	96.4	97.0	89.7	102.2	103.2	103.6	104.5	101.2	84.3				
C9300-	715W	Not	115Vac	82.6	91.0	93.4	93.7	93.9	82.0	94.8	95.9	96.1	96.6	93.7	82.9	202.3	325.8	527.5	579.0
24P		Installed	230Vac	81.6	89.8	92.2	92.4	92.6	81.7	93.7	94.6	94.7	95.2	92.6	82.3	199.0	318.2	510.6	559.9
		NM-4-	115Vac	87.5	93.0	96.5	97.7	98.5	89.8	99.5	102.4	103.0	103.4	98.9	85.4	211.4	334.5	537.8	585.7
		1G	230Vac	86.1	91.3	94.4	95.8	96.6	88.9	98.5	101.5	101.9	102.4	97.9	84.6	207.9	328.0	520.3	568.2
		NM-4-	115Vac	90.4	100.4	101.6	101.9	102.3	94.1	106.8	107.8	108.2	109.1	105.7	90.8	214.9	337.9	539.4	590.8
		10G	230Vac	89.4	99.1	100.3	100.5	100.7	92.8	106.1	106.5	106.9	107.8	104.9	89.6	211.0	329.7	522.2	571.0
		NM-2- 40G	115Vac	88.1	98.6	99.5	99.6	99.9	91.1	104.4	105.2	105.6	106.5	103.3	88.4	212.2	335.2	536.2	586.5
			230Vac	87.1	97.2	98.1	98.3	98.8	90.0	103.3	103.9	104.3	105.2	102.1	87.5	208.0	326.8	519.3	567.6
		NM-8-	115Vac	90.0	99.4	101.0	101.2	101.6	94.2	107.1	107.9	108.3	109.2	106.0	88.7	215.3	339.6	541.4	591.3
		10G	230Vac	89.0	97.9	99.8	100.0	100.5	93.1	105.8	106.7	107.1	108.1	104.8	87.8	211.7	331.9	524.2	572.3
C9300-	1100W	Not	115Vac	87.4	95.9	99.0	99.2	99.4	87.0	100.8	101.5	101.8	102.3	99.6	87.8	313.7	547.9	940.3	1041.4
24U		Installed	230Vac	85.9	94.7	97.3	97.6	97.8	85.5	98.0	99.6	99.8	100.3	96.9	86.4	306.2	529.1	895.6	988.7
		NM-4-	115Vac	92.2	97.8	101.2	102.7	103.6	95.4	105.2	108.3	109.0	109.4	104.6	94.4	321.0	554.0	943.5	1045.5
		1G	230Vac	90.6	96.1	99.4	100.9	101.7	93.7	103.4	106.4	107.2	107.6	102.8	93.2	313.5	536.6	901.5	994.6
		NM-4-	115Vac	96.0	106.2	107.6	107.8	108.4	99.7	113.4	114.2	114.6	115.6	112.3	96.1	325.7	559.0	950.6	1053.0
		10G	230Vac	94.3	104.5	105.8	106.1	106.6	97.9	112.1	112.8	113.2	114.0	110.8	94.4	318.3	541.9	906.2	997.8
		NM-2-	115Vac	93.4	103.9	104.8	105.0	105.5	96.5	110.4	111.3	111.5	112.4	109.2	93.4	323.2	555.8	946.7	1048.6
		40G	230Vac	91.8	102.0	103.0	103.3	103.7	94.8	108.7	109.4	109.8	110.6	107.5	91.8	314.9	538.4	902.2	994.5
		NM-8-	115Vac	95.8	105.4	107.3	107.6	108.1	100.2	114.0	114.8	115.2	116.2	112.8	94.4	324.4	557.7	946.6	1049.0
		10G	230Vac	94.0	103.0	105.1	105.4	106.0	98.4	112.0	113.1	113.5	114.5	110.9	93.2	317.8	541.8	907.7	999.1
C9300-	350W	Not	115Vac	81.5	94.9	95.7	95.9	96.4	80.8	98.6	100.2	101.3	102.3	97.2	82.2				
48T		Installed	230Vac	80.5	93.7	94.6	94.8	95.3	80.1	97.3	99.5	99.9	100.8	96.0	81.5				

											Mea	sured P(W	Measured P(W)								
			Half Por	t Traffic				Full Por	t Traffic				Weighted Average Pw	No Link	PoE Test (No Traffic)						
SKU	FEP	Uplink	Input	0.01% / EEE	10%	30%	50%	100%	0.01% / EEE	10%	30%	50%	100%			25%	50%	90%	100%		
		NM-4-	115Vac	86.4	94.9	97.8	99.4	100.4	89.3	104.6	107.6	108.6	108.9	103.5	85.7						
		1G	230Vac	85.3	93.8	96.6	98.4	99.1	88.2	103.4	106.2	106.9	107.2	102.3	84.8						
		NM-4-	115Vac	89.6	103.4	104.2	104.6	105.4	93.0	112.7	113.5	114.1	115.7	111.0	90.6						
		10G	230Vac	89.0	102.0	102.8	103.1	103.9	91.9	111.0	111.8	112.4	114.0	109.4	89.3						
		NM-2-	115Vac	88.3	102.4	102.9	103.3	104.2	91.0	110.5	111.3	112.1	113.9	108.9	88.6						
		40G	230Vac	87.3	100.9	101.4	101.8	102.7	89.9	108.8	109.6	110.3	112.1	107.2	87.6						
		NM-8-	115Vac	92.1	105.2	106.1	106.5	107.4	98.6	117.6	118.4	119.1	120.9	116.0	91.0						
		10G	230Vac	91.1	103.9	104.7	105.1	106.0	97.3	115.8	116.6	117.3	119.0	114.3	90.0						
C9300-	715W	Not	115Vac	90.5	103.2	104.5	104.7	105.2	89.9	104.9	107.8	109.2	110.2	103.9	91.3	206.1	324.1	514.4	563.2		
48P		Installed	230Vac	89.4	102.2	103.4	103.6	104.1	88.9	103.7	106.9	108.4	109.3	102.7	89.9	202.9	316.9	500.6	547.5		
		NM-4- 1G	115Vac	95.3	103.5	106.2	108.1	108.8	98.0	112.1	114.9	115.9	116.2	111.1	94.3	215.0	332.6	523.4	572.1		
			230Vac	94.0	102.2	105.2	106.9	107.8	96.4	111.3	114.1	115.2	115.5	110.2	93.1	211.2	324.8	509.3	555.8		
		NM-4- 10G	115Vac	98.7	111.5	112.3	112.7	113.5	101.5	119.7	120.5	121.2	122.8	118.2	99.2	219.1	336.5	528.8	576.6		
			230Vac	97.1	110.7	111.5	111.9	112.7	100.6	119.2	120.0	120.7	122.3	117.6	97.9	215.5	329.5	514.2	560.5		
		NM-2-	115Vac	96.9	110.1	110.7	111.0	111.9	99.3	118.2	119.0	119.7	121.5	116.7	97.6	217.4	335.4	527.4	577.8		
		40G	230Vac	95.6	109.2	109.7	110.1	111.0	98.1	117.5	118.2	119.0	120.6	115.8	96.0	213.0	326.9	511.9	558.8		
		NM-8-	115Vac	100.5	113.4	114.2	114.6	115.5	106.4	124.5	125.4	126.1	128.0	123.0	99.5	215.1	334.7	520.8	568.8		
		10G	230Vac	99.4	112.8	113.5	113.9	114.9	105.3	124.0	124.9	125.6	127.4	122.5	98.4	212.3	327.4	507.4	553.1		
C9300-	1100W	Not	115Vac	96.0	110.2	110.9	111.2	111.7	95.6	112.5	114.3	115.9	116.9	111.3	97.0	315.1	544.0	925.9	1023.0		
48U		Installed	230Vac	94.8	108.5	109.2	109.4	109.9	94.2	110.0	112.5	114.1	115.0	108.9	95.6	308.6	529.4	889.9	978.8		
		NM-4-	115Vac	97.4	105.8	109.0	110.7	111.0	99.9	115.1	117.8	118.9	119.2	114.0	96.4	319.2	547.3	928.0	1026.3		
		1G	230Vac	95.4	103.9	107.4	108.7	110.0	98.8	113.4	116.2	117.0	117.4	112.4	94.9	314.3	535.6	896.0	984.3		
		NM-4-	115Vac	104.4	118.5	119.0	119.5	120.1	107.4	126.8	127.6	128.3	130.0	125.2	104.9	326.2	556.0	938.6	1035.6		
		10G	230Vac	102.8	116.0	117.1	117.5	118.2	106.4	124.8	125.5	126.2	127.7	123.2	103.6	320.4	541.4	903.0	991.6		
		NM-2-	115Vac	102.9	117.2	117.6	118.0	119.0	104.8	123.8	124.6	125.3	127.0	122.2	102.5	324.1	552.4	934.4	1032.6		
		40G	230Vac	101.2	114.9	115.5	115.9	117.0	103.9	123.0	123.7	124.4	126.1	121.4	101.7	316.9	537.9	898.2	988.3		
		NM-8-	115Vac	106.7	120.4	121.1	121.5	122.3	112.7	131.5	132.4	133.0	134.8	130.0	105.7	330.0	563.7	941.8	1043.4		
		10G	230Vac	105.0	118.5	119.2	119.6	120.2	110.9	129.4	130.2	131.0	132.6	127.9	104.1	324.5	549.0	908.0	998.9		
C9300-	1100W	NM-8-	115Vac	188.0	195.7	196.8	197.4	198.9	208.8	224.6	227.0	228.6	232.0	223.8	168.6	364.2	521.6	784.3	851.4		
24XU		10G	230Vac	184.4	192.2	192.9	193.5	195.1	204.6	220.0	222.0	223.5	226.9	219.2	165.3	354.2	505.0	749.7	810.6		

Safety and Compliance

Table 12 lists the safety and compliance information for the Cisco Catalyst 9300 Series.

 Table 12.
 Safety and Compliance Information

Description	Specification
Safety certifications	 UL 60950-1 CAN/CSA-C222.2 No. 60950-1 EN 60950-1 IEC 60950-1 AS/NZS 60950.1 IEEE 802.3
Electromagnetic emissions certifications	 47 CFR Part 15 CISPR22 Class A EN 300 386 V1.6.1 EN 55022 Class A EN 55032 Class A CISPR 32 Class A EN61000-3-2 EN61000-3-3 ICES-003 Class A TCVN 7189 Class A V-3 Class A CISPR24 EN 300 386 EN55024 TCVN 7317
Environmental	Reduction of Hazardous Substances (ROHS) 5

Cisco Enhanced Limited Lifetime Hardware Warranty

The Cisco Catalyst 9300 Series Switches come with a Cisco Enhanced Limited Lifetime Warranty (E-LLW) that includes Next-Business-Day (NBD) delivery of replacement hardware where available and 90 days of 8x5 Cisco Technical Assistance Center (TAC) support.

Your formal warranty statement, including the warranty applicable to Cisco software, appears in the information packet that accompanies your Cisco product. We encourage you to review the warranty statement shipped with your specific product carefully before use.

Cisco reserves the right to refund the purchase price as its exclusive warranty remedy.

For further information about warranty terms, visit https://www.cisco.com/go/warranty. Table 13 provides information about the E-LLW.

Table 13. E-LLW Details

	Cisco E-LLW
Devices covered	Applies to Cisco Catalyst 9300 Series Switches.
Warranty duration	As long as the original customer owns the product.
End-of-life policy	In the event of discontinuance of product manufacture, Cisco warranty support is limited to 5 years from the announcement of discontinuance.
Hardware replacement	Cisco or its service center will use commercially reasonable efforts to ship a replacement for NBD delivery, where available. Otherwise, a replacement will be shipped within 10 working days after receipt of the Return Materials Authorization (RMA) request. Actual delivery times might vary depending on customer location.

	Cisco E-LLW
Effective date	Hardware warranty commences from the date of shipment to customer (and in case of resale by a Cisco reseller, not more than 90 days after original shipment by Cisco).
TAC support	Cisco will provide during business hours, 8 hours per day, 5 days per week, basic configuration, diagnosis, and troubleshooting of device-level problems for up to a 90-day period from the date of shipment of the originally purchased Cisco Catalyst 9300 Series product. This support does not include solution or network-level support beyond the specific device under consideration.
Cisco.com access	Warranty allows guest access only to Cisco.com.

Cisco Services For Next-Generation Cisco Catalyst Fixed Switches

Achieve infrastructure excellence faster and with less risk. Cisco Catalyst 9K Services provide expert guidance to help you successfully deploy, manage and support the new Catalyst 9K Series Switches. With unmatched networking expertise, best practices and innovative tools, we can help you reduce overall upgrade, refresh, and migration costs as you introduce new hardware, software and protocols into the network. Offering a comprehensive lifecycle of services – from implementation, optimization, technical and managed services – Cisco experts help you minimize disruption and achieve operational excellence to extract maximum value from your DNA-ready infrastructure.

Learn more about Cisco Services for Enterprise Networks

Software Policy for Cisco Catalyst 9300 Series Switches

Software Policy For Network Stack Components

Customers with the Network Essential Stack and Network Advantage Stack software feature sets are provided with maintenance updates and bug fixes designed to maintain compliance of the software. This includes compliance with published specifications, release notes, and industry standards as long as the original end user continues to own or use the product or up to one year from the end-of-sale date for the product, whichever occurs earlier.

Cisco Embedded Support for Cisco DNA Term Components

Cisco Embedded Support delivers the right support for Cisco software products and suites. It will keep your business applications performing as expected and protect your investment. Cisco Embedded Support for the DNA Essentials and DNA Advantage term components is included. Cisco Embedded Support provides access to TAC support, major software updates, maintenance and minor software releases, and the Cisco Embedded Support site, for increased productivity with anytime access.

Ordering Information

Table 16 lists ordering information for the Cisco Catalyst 9300 Series. To place an order, visit the Cisco Ordering home page at https://www.cisco.com/en/US/ordering/or13/or8/order customer help how to order listing.html.

Table 14. Ordering Information

Switches							
Product Number	Product Description						
C9300-24T-E	Catalyst 9300 24-port data only, Network Essentials						
C9300-24T-A	Catalyst 9300 24-port data only, Network Advantage						
C9300-24P-E	Catalyst 9300 24-port PoE+, Network Essentials						
C9300-24P-A	Catalyst 9300 24-port PoE+, Network Advantage						
C9300-24U-E	Catalyst 9300 24-port UPOE, Network Essentials						
C9300-24U-A	Catalyst 9300 24-port UPOE, Network Advantage						

0.774	
Switches	
C9300-48T-E	Catalyst 9300 48-port data only, Network Essentials
C9300-48T-A	Catalyst 9300 48-port data only, Network Advantage
C9300-48P-E	Catalyst 9300 48-port PoE+, Network Essentials
C9300-48P-A	Catalyst 9300 48-port PoE+, Network Advantage
C9300-48U-E	Catalyst 9300 48-port UPOE, Network Essentials
C9300-48U-A	Catalyst 9300 48-port UPOE, Network Advantage
Network modules	
Product Number	Product Description
C9300-NM-4G	Catalyst 9300 4 x 1GE Network Module
C9300-NM-4G=	Catalyst 9300 4 x 1GE Network Module, spare
C9300-NM-8X	Catalyst 9300 8 x 10GE Network Module
C9300-NM-8X=	Catalyst 9300 8 x 10GE Network Module, spare
C9300-NM-2Q	Catalyst 9300 2 x 40GE Network Module
C9300-NM-2Q=	Catalyst 9300 2 x 40GE Network Module, spare
C9300-NM-4M	Catalyst 9300 4 x MGig Network Module
C9300-NM-4M=	Catalyst 9300 4 x MGig Network Module, spare
Stacking cables	
Product Number	Product Description
STACK-T1-50CM	50CM Type 3 Stacking Cable
STACK-T1-50CM=	50CM Type 3 Stacking Cable, spare
STACK-T1-1M	1M Type 3 Stacking Cable
STACK-T1-1M=	1M Type 3 Stacking Cable, spare
STACK-T1-3M	3M Type 3 Stacking Cable
STACK-T1-3M=	3M Type 3 Stacking Cable, spare
Software licenses	
Product Number	Product Description
C9300-DNA-E-24-3Y	C9300 DNA Essentials, 24-port, 3 Year Term license
C9300-DNA-E-24-5Y	C9300 DNA Essentials, 24-port, 5 Year Term license
C9300-DNA-E-24-7Y	C9300 DNA Essentials, 24-port, 7 Year Term license
C9300-DNA-A-24-3Y	C9300 DNA Advantage, 24-port, 3 Year Term license
C9300-DNA-A-24-5Y	C9300 DNA Advantage, 24-port, 5 Year Term license
C9300-DNA-A-24-7Y	C9300 DNA Advantage, 24-port, 7 Year Term license
C9300-DNA-E-48-3Y	C9300 DNA Essentials, 48-port, 3 Year Term license
C9300-DNA-E-48-5Y	C9300 DNA Essentials, 48-port, 5 Year Term license
C9300-DNA-E-48-7Y	C9300 DNA Essentials, 48-port, 7 Year Term license
C9300-DNA-A-48-3Y	C9300 DNA Advantage, 48-port, 3 Year Term license
C9300-DNA-A-48-5Y	C9300 DNA Advantage, 48-port, 5 Year Term license
C9300-DNA-A-48-7Y	C9300 DNA Advantage, 48-port, 7 Year Term license
Power supplies	
Product Number	Product Description
PWR-C1-350WAC=	350WAC power supply spare
PWR-C1-715WAC=	715WAC power supply spare
PWR-C1-1100WAC=	1100WAC power supply spare
OI 110011A0=	Trooting power supply space

Switches	
Cisco StackWise-480 and StackPo	ower cables
STACK-T1-50CM=	Cisco StackWise-480 50cm stacking cable spare
STACK-T1-1M=	Cisco StackWise-480 1m stacking cable spare
STACK-T1-3M=	Cisco StackWise-480 3m stacking cable spare
CAB-SPWR-30CM=	Cisco Catalyst 3850 StackPower cable 30cm spare
CAB-SPWR-150CM=	Cisco Catalyst 3850 StackPower cable 150cm spare
Spare power cords	
CAB-TA-NA=	AC power cord for Cisco Catalyst (North America)
CAB-TA-AP=	AC power cord for Cisco Catalyst (Australia)
CAB-TA-AR=	AC power cord for Cisco Catalyst (Argentina)
CAB-TA-SW=	AC power cord for Cisco Catalyst (Switzerland)
CAB-TA-UK=	AC power cord for Cisco Catalyst (United Kingdom)
CAB-TA-JP=	AC power cord for Cisco Catalyst (Japan)
CAB-TA-250VAC-JP=	Japan 250VAC power cord for Cisco Catalyst (Japan)
CAB-TA-EU=	AC power cord for Cisco Catalyst (Europe)
CAB-TA-IT=	AC power cord for Cisco Catalyst (Italy)
CAB-TA-IN=	AC power cord for Cisco Catalyst (India)
CAB-TA-CN=	AC power cord for Cisco Catalyst (China)
CAB-TA-DN=	AC power cord for Cisco Catalyst (Denmark)
CAB-TA-IS=	AC power cord for Cisco Catalyst (Israel)
CAB-ACBZ-12A=	AC power cord for Cisco Catalyst (Brazil), 12A/125V BR-3-20 plug up to 12A
CAB-ACBZ-10A=	AC power cord for Cisco Catalyst (Brazil), 10A/250V BR-3-10 plug up to 10A
CAB-C15-CBN	Cabinet jumper power cord, 250VAC 13A, C14-C15 connectors

Optics online reference

The Cisco Catalyst 9300 Series supports a wide range of optics. Because the list of supported optics is updated on a regular basis, consult the tables available here for the latest QSFP+, SFP+, and SFP compatibility information: https://www.cisco.com/en/US/products/hw/modules/ps5455/products_device_support_tables_list.html.

Cisco Capital

Financing to Help You Achieve Your Objectives

Cisco Capital® can help you acquire the technology you need to achieve your objectives and stay competitive. We can help you reduce CapEx. Accelerate your growth. Optimize your investment dollars and ROI. Cisco Capital financing gives you flexibility in acquiring hardware, software, services, and complementary third-party equipment. And there's just one predictable payment. Cisco Capital is available in more than 100 countries. Learn more.



Americas Headquarters Cisco Systems, Inc. San Jose, CA Asia Pacific Headquarters Cisco Systems (USA) Pte. Ltd. Singapore

Europe Headquarters Cisco Systems International BV Amsterdam, The Netherlands

Cisco has more than 200 offices worldwide. Addresses, phone numbers, and fax numbers are listed on the Cisco Website at https://www.cisco.com/go/offices.

Cisco and the Cisco logo are trademarks or registered trademarks of Cisco and/or its affiliates in the U.S. and other countries. To view a list of Cisco trademarks, go to this URL: https://www.cisco.com/go/trademarks. Third-party trademarks mentioned are the property of their respective owners. The use of the word partner does not imply a partnership relationship between Cisco and any other company. (1110R)

Printed in USA C78-738977-03 08/17