

# CUS200M

## EVALUATION DATA

DWG No. CA811-53-01		
APPD	CHK	DWG
Wang YQ 22-Jan-'16	Wang HL 22-Jan-'16	Zhang BC 22-Jan-'16

## INDEX

	PAGE
<b>1. Evaluation Method</b>	
1.1 Circuit used for determination	
Circuit 1 used for determination .....	T-1
Steady state data	
Over current protection (OCP) characteristics	
Over voltage protection (OVP) characteristics	
Output rise characteristics	
Output fall characteristics	
Hold up time characteristics	
Circuit 2 used for determination .....	T-1
Dynamic load response characteristics	
Circuit 3 used for determination .....	T-1
Inrush current waveform	
Circuit 4 used for determination .....	T-2
Leakage current characteristics	
Circuit 5 used for determination .....	T-2
Output ripple and noise waveform	
Configuration used for determination .....	T-2
Electro-Magnetic Interference characteristics	
(a) Conducted Emission	
(b) Radiated Emission	
1.2 List of equipment used .....	T-3
<b>2. Characteristics</b>	
2.1 Steady state data	
(1) Regulation - line and load, Temperature drift / Start up voltage and Drop out voltage .....	T-4~5
(2) Efficiency vs. Output current .....	T-6~7
(3) Input current vs. Output current .....	T-8~9
(4) Input power vs. Output current .....	T-10~11
(5) Input power at remote OFF state .....	T-12
2.2 Over current protection (OCP) characteristics .....	T-13
2.3 Over voltage protection (OVP) characteristics .....	T-14
2.4 Output rise characteristics .....	T-15~16
2.5 Output fall characteristics .....	T-17~18
2.6 Hold up time characteristics .....	T-19~20
2.7 Dynamic load response characteristics .....	T-21~22
2.8 Response to brown out characteristics .....	T-23~24
2.9 Inrush current waveform .....	T-25
2.10 Leakage current characteristics .....	T-26
2.11 Output ripple and noise waveform .....	T-27~28
2.12 Electro-Magnetic Interference characteristics .....	T-29~44

Terminology used


Definition	
Vin	..... Input voltage
Vout	..... Output voltage
Iin	..... Input current
Iout	..... Output current
Ta	..... Ambient temperature
f	..... Frequency

## 1. Evaluation Method

### 1.1 Circuit used for determination



#### Circuit 1 used for determination

- Steady state data
- Over current protection (OCP) characteristics
- Over voltage protection (OVP) characteristics
- Output rise characteristics
- Output fall characteristics
- Hold up time characteristics




#### Circuit 2 used for determination

- Dynamic load response characteristics




#### Circuit 3 used for determination

- Inrush current waveform




Circuit 4 used for determination

- Leakage current characteristics


Circuit 5 used for determination

- Output ripple and noise waveform


Configuration used for determination

- Electro-Magnetic Interference characteristics

## (a) Conducted Emission



## (b) Radiated Emission



## 1.2 List of equipment used

	EQUIPMENT USED	MANUFACTURER	MODEL NO.
1	DIGITAL STORAGE OSCILLOSCOPE	YOKOGAWA ELECT.	DLM2054
2	DIGITAL MULTIMETER	FLUKE	111
3	DIGITAL POWER METER	YOKOGAWA ELECT.	WT210
4	CURRENT PROBE	YOKOGAWA ELECT.	701932
5	DYNAMIC DUMMY LOAD	CHROMA	63201
6	CVCF	KIKUSUI	PCR2000LE
7	LEAKAGE CURRENT METER	SIMPSON	228
8	CONTROLLED TEMP. CHAMBER	TABA-E SPEC	SH-661
9	EMI TEST RECEIVER	ROHDE & SCHWARZ	ESCI-03
10	LISN	ROHDE & SCHWARZ	ENV216
11	BICONICAL ANTENNA	EMCO	63208

## 2 Characteristics

CUS200M

### 2.1 Steady state data

#### (1) Regulation - line and load, Temperature drift / Start up voltage and Drop out voltage

**12V**

##### 1. Regulation - line and load

Condition Ta : 25°C  
Istandby : 0A

Iout \ Vin	85VAC	115VAC	230VAC	265VAC	Line regulation	
0A (0%)	12.006V	12.007V	12.008V	12.008V	2mV	0.017%
8.35A (50%)	12.001V	12.001V	12.001V	12.001V	0mV	0.000%
16.7A (100%)	-	11.994V	11.993V	11.993V	1mV	0.008%
Load regulation	5mV	13mV	15mV	15mV		
	0.042%	0.108%	0.125%	0.125%		

##### 2. Temperature drift

Conditions Iout : 16.7A (100%)  
Istandby : 0A

	Vin \ Ta	-20°C	+25°C	+50°C	Temperature stability	
Vout	115VAC	11.982V	11.994V	11.983V	12mV	0.100%
	230VAC	11.982V	11.993V	11.983V	11mV	0.092%

##### 3. Start up voltage and Drop out voltage

Conditions Ta : 25°C  
Iout : 16.7A (100%)  
Istandby : 0A

Start up voltage (Vin)	79VAC
Drop out voltage (Vin)	76VAC

**18V**

##### 1. Regulation - line and load

Condition Ta : 25°C  
Istandby : 0A

Iout \ Vin	85VAC	115VAC	230VAC	265VAC	Line regulation	
0A (0%)	18.005V	18.007V	18.009V	18.008V	4mV	0.022%
5.6A (50%)	18.001V	18.000V	18.000V	18.000V	1mV	0.006%
11.2A (100%)	-	17.998V	17.998V	17.998V	0mV	0.000%
Load regulation	4mV	9mV	11mV	10mV		
	0.022%	0.050%	0.061%	0.056%		

##### 2. Temperature drift

Conditions Iout : 11.2A (100%)  
Istandby : 0A

	Vin \ Ta	-20°C	+25°C	+50°C	Temperature stability	
Vout	115VAC	17.945V	17.998V	17.966V	53mV	0.294%
	230VAC	17.945V	17.998V	17.966V	53mV	0.294%

##### 3. Start up voltage and Drop out voltage

Conditions Ta : 25°C  
Iout : 11.2A (100%)  
Istandby : 0A

Start up voltage (Vin)	79VAC
Drop out voltage (Vin)	76VAC

## (1) Regulation - line and load, Temperature drift / Start up voltage and Drop out voltage

**24V**

## 1. Regulation - line and load

Condition Ta : 25°C  
Istandby : 0A

Iout \ Vin	85VAC	115VAC	230VAC	265VAC	Line regulation	
0A (0%)	24.027V	24.028V	24.027V	24.027V	1mV	0.004%
4.2A (50%)	24.019V	24.020V	24.019V	24.019V	1mV	0.004%
8.4A (100%)	-	24.020V	24.020V	24.020V	0mV	0.000%
Load regulation	8mV	8mV	8mV	8mV		
	0.033%	0.033%	0.033%	0.033%		

## 2. Temperature drift

Conditions Iout : 8.4A (100%)  
Istandby : 0A

	Vin \ Ta	-20°C	+25°C	+50°C	Temperature stability	
Vout	115VAC	23.937V	24.020V	23.991V	83mV	0.346%
	230VAC	23.937V	24.020V	23.992V	83mV	0.346%

## 3. Start up voltage and Drop out voltage

Conditions Ta : 25°C  
Iout : 8.4A (100%)  
Istandby : 0A

Start up voltage (Vin)	79VAC
Drop out voltage (Vin)	76VAC

**48V**

## 1. Regulation - line and load

Condition Ta : 25°C  
Istandby : 0A

Iout \ Vin	85VAC	115VAC	230VAC	265VAC	Line regulation	
0A (0%)	48.028V	48.027V	48.031V	48.026V	5mV	0.010%
2.1A (50%)	48.006V	48.006V	48.006V	48.006V	0mV	0.000%
4.2A (100%)	-	48.006V	48.006V	48.006V	0mV	0.000%
Load regulation	22mV	21mV	25mV	20mV		
	0.046%	0.044%	0.052%	0.042%		

## 2. Temperature drift

Conditions Iout : 4.2A (100%)  
Istandby : 0A

	Vin \ Ta	-20°C	+25°C	+50°C	Temperature stability	
Vout	115VAC	47.786V	48.006V	47.996V	220mV	0.458%
	230VAC	47.785V	48.006V	47.996V	221mV	0.460%



## 3. Start up voltage and Drop out voltage

Conditions Ta : 25°C  
Iout : 4.2A (100%)  
Istandby : 0A


Start up voltage (Vin)	79VAC
Drop out voltage (Vin)	76VAC

## (2) Efficiency vs. Output current

Conditions Vin : 85 VAC -----  
                  : 115 VAC - - - - -  
                  : 230 VAC - - - - -  
                  : 265 VAC - - - - -  
                  Ta : 25 °C  
                  Istandby : 0 A  
                  Cooling : Convection




## (2) Efficiency vs. Output current



### (3) Input current vs. Output current


12V

Io: 0 A	
Vin	Input current
85VAC	0.046A
115VAC	0.049A
230VAC	0.077A
265VAC	0.096A



18V


Io: 0 A	
Vin	Input current
85VAC	0.046A
115VAC	0.050A
230VAC	0.086A
265VAC	0.095A



## (3) Input current vs. Output current


24V

Io: 0 A	
Vin	Input current
85VAC	0.047A
115VAC	0.050A
230VAC	0.080A
265VAC	0.095A



48V

Io: 0 A	
Vin	Input current
85VAC	0.050A
115VAC	0.050A
230VAC	0.076A
265VAC	0.098A




## (4) Input power vs. Output current

Conditions Vin : 85 VAC -----  
                  : 115 VAC - - -  
                  : 230 VAC ———  
                  : 265 VAC - - - -  
                  Ta : 25 °C  
                  Istandby : 0 A  
                  Cooling : Convection


12V

Io: 0 A	
Vin	Input power
85VAC	2.18W
115VAC	1.82W
230VAC	1.62W
265VAC	1.78W



18V

Io: 0 A	
Vin	Input power
85VAC	2.23W
115VAC	1.82W
230VAC	1.90W
265VAC	2.00W




## (4) Input power vs. Output current

**24V**


Io: 0 A

Vin	Input power
85VAC	2.41W
115VAC	1.78W
230VAC	1.60W
265VAC	1.80W

**48V**

Io: 0 A

Vin	Input power
85VAC	2.62W
115VAC	1.92W
230VAC	1.80W
265VAC	2.00W




## (5) Input power at Remote OFF state


Conditions      Istandby : 0A  
R- : 0V (Low level)  
Ta : 25°C

12V

Input power vs. Input voltage




## 2.2 Over current protection (OCP) characteristics



## 2.3 Over voltage protection (OVP) characteristics

Conditions Vin : 115 VAC  
 Iout : 0 %  
 Ta : 25 °C





## 2.4 Output rise characteristics

Conditions Vin : 85 VAC (A)  
115 VAC (B)  
230 VAC (C)  
265 VAC (D)



Ta : 25 °C

Istandby : 0 A





## 2.4 Output rise characteristics

Conditions    Vin : 85 VAC (A)  
                   115 VAC (B)  
                   230 VAC (C)  
                   265 VAC (D)  
                   Ta : 25 °C  
                   Istandby : 0 A




## 2.5 Output fall characteristics

Conditions    Vin :    85 VAC (A)  
                     115 VAC (B)  
                     230 VAC (C)  
                     265 VAC (D)  
                     Ta :    25 °C  
                     Istandby :    0 A



## 2.5 Output fall characteristics


Conditions    Vin : 85 VAC (A)  
                   115 VAC (B)  
                   230 VAC (C)  
                   265 VAC (D)  
                   Ta : 25 °C  
                   Istandby : 0 A




## 2.6 Hold up time characteristics

Conditions    Vin : 115 VAC -----  
                  230 VAC ——  
                  Ta : 25 °C  
                  Istandby : 0 A

12V




18V




## 2.6 Hold up time characteristics

Conditions    Vin : 115 VAC -----  
                  230 VAC ——  
                  Ta : 25 °C  
                  Istandby : 0 A

24V





48V





## 2.7 Dynamic load response characteristics

Conditions    Vin : 115 VAC  
 Iout : 50 %  $\leftrightarrow$  100 %  
 (tr = tf = 75us)  
 Ta : 25 °C  
 Istandby : 0 A



## 2.7 Dynamic load response characteristics

Conditions      Vin : 115 VAC  
 Iout : 50 %  $\leftrightarrow$  100 %  
 (tr = tf = 75us)  
 Ta : 25 °C  
 Istandby : 0 A



## 2.8 Response to brown out characteristics

Conditions: Iout : 100%  
 Istandby : 0A  
 Ta : 25°C  
 Cooling : Convection


## Interruption time

- A : Output voltage does not drop
- B : Output voltage drops down not reaching 0V
- C : Output voltage drops until 0V

**12V**


Vin :115VAC

A: 16ms, B: 22ms, C: 25ms




Vin :230VAC

A: 16ms ,B: 22ms, C: 27ms

**18V**


Vin :115VAC

A: 17ms, B: 22ms, C: 32ms



Vin :230VAC

A: 18ms ,B: 22ms,C: 36ms



## 2.8 Response to brown out characteristics

Interruption time

A : Output voltage does not drop

B : Output voltage drops down not reaching 0V

C : Output voltage drops until 0V

Conditions:

Iout : 100%

Istandby : 0A


Ta : 25°C

Cooling : Convection

**24V**


Vin :115VAC

A: 17ms, B: 22ms, C: 33ms




Vin :230VAC

A: 18ms , B: 22ms, C: 36ms

**48V**


Vin :115VAC

A: 18ms, B: 22ms,C :34ms



Vin :230VAC

A: 18ms ,B: 22ms,C: 38ms




## 2.9 Inrush current waveform


12V

Conditions    Vin : 115 VAC  
 Iout : 16.7A (100%)  
 Istandby : 0 A  
 Ta : 25 °C


Switch on phase angle of input AC voltage  
 $\phi = 0^\circ$




Switch on phase angle of input AC voltage  
 $\phi = 90^\circ$



Switch on phase angle of input AC voltage  
 $\phi = 0^\circ$



Switch on phase angle of input AC voltage  
 $\phi = 90^\circ$




## 2.10 Leakage current characteristics


Conditions  
Iout : 0A -----  
16.7A (100%) ———  
Istandby : 0A  
Ta : 25°C  
Equipment used : 228 (Simpson)

12V

L





N



## 2.11 Output ripple and noise waveform

Conditions      Vin : 115 VAC  
                   Ta : 25 °C  
                   Istandby : 0 A





## 2.11 Output ripple and noise waveform

Conditions

Vin : 115 VAC

Ta : 25 °C

Istandby : 0 A




## 2.12 Electro-Magnetic Interference characteristics

Conditions    Vin : 115VAC  
                  Iout : 16.7A (100%)  
                  Istandby : 0A  
                  Ta : 25°C


## Conducted Emission

12V

Point A (6.54MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	56.0	50.1
AV	46.0	35.0



Point B (6.73MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	56.0	49.6
AV	46.0	35.1



Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55022 class B.


## 2.12 Electro-Magnetic Interference characteristics

Conditions    Vin : 230VAC  
                  Iout : 16.7A (100%)  
                  Istandby : 0A  
                  Ta : 25°C


## Conducted Emission

12V

Point A (6.60MHz))		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	56.0	49.3
AV	46.0	34.3



Point B (4.99MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	56.0	50.0
AV	46.0	35.2



Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55022 class B.


## 2.12 Electro-Magnetic Interference characteristics

Conditions    Vin : 115VAC  
                  Iout : 11.2A (100%)  
                  Istandby : 0A  
                  Ta : 25°C


## Conducted Emission

18V

Point A (1.057MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	56.0	46.8
AV	46.0	31.9



Point B (1.06MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	56.0	46.4
AV	46.0	31.0



Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55022 class B.


## 2.12 Electro-Magnetic Interference characteristics

Conditions    Vin : 230VAC  
                  Iout : 11.2A (100%)  
                  Istandby : 0A  
                  Ta : 25°C


## Conducted Emission

18V

Point A (8.75MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	56.0	46.6
AV	46.0	31.4



Point B (1.0665MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	56.0	46.8
AV	46.0	31.9



Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55022 class B.


## 2.12 Electro-Magnetic Interference characteristics

Conditions    Vin : 115VAC  
                  Iout : 8.4A (100%)  
                  Istandby : 0A  
                  Ta : 25°C


## Conducted Emission

24V

Point A (1.089MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	56.0	47.3
AV	46.0	32.8



Point B (1.0915MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	56.0	47.3
AV	46.0	32.7



Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55022 class B.


## 2.12 Electro-Magnetic Interference characteristics

Conditions    Vin : 230VAC  
                  Iout : 8.4A (100%)  
                  Istandby : 0A  
                  Ta : 25°C


## Conducted Emission

24V

Point A (1.1015MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	56.0	47.5
AV	46.0	32.4



Point A (1.101MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	56.0	47.6
AV	46.0	32.6




Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55022 class B.

## 2.12 Electro-Magnetic Interference characteristics


Conditions    Vin : 115VAC  
                  Iout : 4.2A (100%)  
                  Istandby : 0A  
                  Ta : 25°C

## Conducted Emission

48V		
Point A (1.2855MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	56.0	48.4
AV	46.0	33.9



Point B (1.283MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	56.0	49.4
AV	46.0	35.3



Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55022 class B.


## 2.12 Electro-Magnetic Interference characteristics

Conditions    Vin : 230VAC  
                  Iout : 4.2A (100%)  
                  Istandby : 0A  
                  Ta : 25°C


## Conducted Emission

48V

Point A (1.8955MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	56.0	49.0
AV	46.0	33.2



Point B (1.497MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	56.0	49.2
AV	46.0	32.6



Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55022 class B.


## 2.12 Electro-Magnetic Interference characteristics

Conditions      Vin : 115VAC  
                   Iout : 16.7A (100%)  
                   Istandby : 0A  
                   Ta : 25°C


Radiated Emission

12V

HORIZONTAL



VERTICAL



Limit of EN55011-B,EN55022-B are same as its VCCI class B.  
    Indication is peak values.

## 2.12 Electro-Magnetic Interference characteristics

Conditions

Vin : 230VAC

Iout : 16.7A (100%)


Istandby : 0A

Ta : 25°C


Radiated Emission

12V

HORIZONTAL



VERTICAL



Limit of EN55011-B,EN55022-B are same as its VCCI class B.  
Indication is peak values.


## 2.12 Electro-Magnetic Interference characteristics

Conditions      Vin : 115VAC  
                   Iout : 11.2A (100%)  
                   Istandby : 0A  
                   Ta : 25°C


Radiated Emission

18V

HORIZONTAL



VERTICAL



Limit of EN55011-B, EN55022-B are same as its VCCI class B.  
        Indication is peak values.

## 2.12 Electro-Magnetic Interference characteristics

Conditions

Vin : 230VAC

Iout : 11.2A (100%)


Istandby : 0A

Ta : 25°C


Radiated Emission

18V

HORIZONTAL



VERTICAL



Limit of EN55011-B,EN55022-B are same as its VCCI class B.  
Indication is peak values.


## 2.12 Electro-Magnetic Interference characteristics

Conditions      Vin : 115VAC  
                   Iout : 8.4A (100%)  
                   Istandby : 0A  
                   Ta : 25°C


Radiated Emission

24V

HORIZONTAL



VERTICAL



Limit of EN55011-B, EN55022-B are same as its VCCI class B.  
    Indication is peak values.


## 2.12 Electro-Magnetic Interference characteristics

Conditions      Vin : 230VAC  
                   Iout : 8.4A (100%)  
                   Istandby : 0A  
                   Ta : 25°C


Radiated Emission

24V

HORIZONTAL



VERTICAL



Limit of EN55011-B, EN55022-B are same as its VCCI class B.  
        Indication is peak values.


## 2.12 Electro-Magnetic Interference characteristics

Conditions      Vin : 115VAC  
                   Iout : 4.2A (100%)  
                   Istandby : 0A  
                   Ta : 25°C


Radiated Emission

48V

HORIZONTAL



VERTICAL



Limit of EN55011-B,EN55022-B are same as its VCCI class B.  
        Indication is peak values.


## 2.12 Electro-Magnetic Interference characteristics

Conditions      Vin : 230VAC  
                   Iout : 4.2A (100%)  
                   Istandby : 0A  
                   Ta : 25°C


Radiated Emission

48V

HORIZONTAL



VERTICAL



Limit of EN55011-B,EN55022-B are same as its VCCI class B.  
    Indication is peak values.