NOT FOR NEW DESIGN Polypropylene Pulse/High Frequency Capacitors

R79, Single Metallized Polypropylene Film, Radial, 5 mm Lead Spacing, Multipurpose Applications



Overview

The R79 Series is constructed of metallized polypropylene film with radial leads of tinned wire. The radial leads are electrically welded to the metal layer on the ends of the capacitor winding. The capacitor is encapsulated with a self-extinguishing thermosetting resin in a box material meeting the UL 94 V-0 requirements.

Applications

Typical applications include timing, oscillator circuits, high frequency coupling and decoupling applications.

Not suitable for across-the-line application (see Suppressor Capacitors).

ATTENTION -- This series was replaced by the R75 series. Please click on the link to the R75 series datasheet HERE.

Benefits

Voltage range: 160 – 630 VDC

Capacitance range: 0.001 – 0.22 μF

• Lead Spacing: 5 mm


• Capacitance tolerance: ±5%, ±10%, ±20% Climatic category: 55/105/56 IEC 60068-1

• Operating temperature range of -55°C to +105°C

· RoHS compliance and lead-free terminations

• Tape & Reel packaging in accordance with IEC 60286-2

Self-healing



Part Number System

R79	G	C	2390	AA	40	K
Series	Rated Voltage (VDC)	Lead Spacing (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
Metallized Polypropylene	G = 160 I = 250 M = 400 P = 630	C = 5	The last three digits represent significant figures. The first digit specifies the total number of zeros to be added.	See Ordering Options Table	40 45	H = 2.5% J = ±5% K = ±10%

Film Capacitors - Polypropylene Pulse/High Frequency Capacitors

R79, Single Metallized Polypropylene Film, Radial, 5 mm Lead Spacing, Multipurpose Applications





Ordering Options Table

Lead Spacing Nominal (mm)	Type of Leads and Packaging	Lead Length (mm)	Lead and Packaging Code
	Standard Lead and Packaging Options		
	Bulk (Bag) – Short Leads	4 +1.5/-0	AA
	Ammo Pack	$H_0 = 18.5 \pm 0.5$	DQ
_	Other Lead and Packaging Options		
5	Tape & Reel (Standard Reel Ø 355 mm)	$H_0 = 18.5 \pm 0.5$	CK
	Bulk (Bag) – Short Leads	10±1	JC
	Bulk (Bag) – Short Leads	4.0 +0.5/-0	JE
	Bulk (Bag) – Short Leads	3.2 +0.3/-0.2	JH
	Bulk (Bag) – Long Leads	17 +1/-2	Z3

Dimensions - Millimeters







S	3		r H		H L		L		F
Nominal	Tolerance								
5.0	±0.4	3.5	+0.1/-0.5	7.5	+0.1/-0.5	7.2	+0.2/-0.5	0.5	±0.05
5.0	±0.4	4.5	+0.1/-0.5	9.5	+0.1/-0.5	7.2	+0.3/-0.5	0.5	±0.05
5.0	±0.4	5.0	+0.1/-0.5	10.0	+0.1/-0.5	7.2	+0.3/-0.5	0.5	±0.05
5.0	±0.4	6.0	+0.1/-0.5	11.0	+0.1/-0.5	7.2	+0.3/-0.5	0.5	±0.05
5.0	±0.4	7.2	+0.1/-0.5	13.0	+0.1/-0.5	7.2	+0.3/-0.5	0.5	±0.05

Note: See Ordering Options Table for lead length (LL/Ho) options.

Film Capacitors – Polypropylene Pulse/High Frequency Capacitors R79, Single Metallized Polypropylene Film, Radial, 5 mm Lead Spacing, Multipurpose Applications



Performance Characteristics

Dielectric	Polypropylene film							
Plates	Metal layer depo	Metal layer deposited by evaporation under vacuum						
Winding	Non-inductive ty	Non-inductive type						
Leads	Tinned wire							
Protection	Plastic case, ther	mosetting resin fille	ed. Box material is so	olvent resistant and	flame retardant according to UL94.			
Related Documents	IEC 60384-16							
Rated Voltage V _R (VDC)	160	250	400	630				
Rated Voltage V _R (VAC)	70	160	200	220				
Capacitance Range (μF)	0.039 - 0.22	0.012 - 0.15	0.0039 - 0.047	0.001 - 0.018				
Capacitance Values	E12 series (IEC 6	0063) measured at	1 kHz and +20 ±1°C	;	•			
Capacitance Tolerance	±2.5%, ±5%, ±10%	, 0						
Operating Temperature Range	-55°C to +105°C							
Rated Temperature T _R	+85°C	+85°C						
Voltage Derating	Above +85°C DC	and AC voltage der	ating is 1.25%/°C					
Climatic Category	55/105/56 IEC 60	0068-1						
	Storage time: ≤ 24 months from the date marked on the label package							
	Average relative humidity per year ≤ 70%							
Storage Conditions	RH ≤ 85% for 30 days randomly distributed throughout the year							
	Dew is absent							
	Temperature: −40 to 80°C (see "Maximum Humidity in Storage Conditions" graph below)							
Test Voltage	11		n terminations) at +2					
Capacitance Drift	Maximum 0.5% a 40% to 60%	fter a 2 year storag	e period at a tempe	rature of +10°C to	+40°C and a relative humidity of			
Maximum Pulse Steepness	dV/dt according	to Table 1. For work		than rated voltage	(V < VR), the specified dV/dt			
Temperature Coefficient	-(200 ±100) ppm	/°C at 1 kHz						
Self Inductance	Approximately 6	nH. Maximum 1 nH	per 1 mm lead and	capacitor length.				
			Maximum Value	es at 25°C ±5°C				
	Frequ	iency	C ≤ 0	.1 μF	C > 0.1 µF			
Dissipation Factor tanδ	1 k	Hz	0.0	6%	0.06%			
	10	кНz	0.1	0%	0.10%			
	100	kHz	0.3	0%	-			

Film Capacitors - Polypropylene Pulse/High Frequency Capacitors


R79, Single Metallized Polypropylene Film, Radial, 5 mm Lead Spacing, Multipurpose Applications





Performance Characteristics cont.

	Measured at +25°C ±5°C, 100 VDC 60 seconds
	Minimum Values Between Terminals
Insulation Resistance	All Capacitance Values
	≥ 100,000 MΩ
	(≥ 500,000 MΩ)*

^{*} Typical value








 T_h is the maximum ambient temperature surrounding the capacitor or hottest contact point (e.g. tracks), whichever is higher, in the worst operation conditions in °C.


Film Capacitors - Polypropylene Pulse/High Frequency Capacitors


R79, Single Metallized Polypropylene Film, Radial, 5 mm Lead Spacing, Multipurpose Applications




Maximum Voltage (V_{rms}) vs. Frequency (Sinusoidal Waveform/Th ≤ 85°C)











Film Capacitors - Polypropylene Pulse/High Frequency Capacitors


R79, Single Metallized Polypropylene Film, Radial, 5 mm Lead Spacing, Multipurpose Applications




Maximum Current (I_{rms}) vs. Frequency (Sinusoidal Waveform/Th ≤ 85 °C)









Film Capacitors - Polypropylene Pulse/High Frequency Capacitors

R79, Single Metallized Polypropylene Film, Radial, 5 mm Lead Spacing, Multipurpose Applications



Environmental Test Data

Damp Heat, Steady State Test	Test Cor	nditions:	Performances
	Temperature: Relative humidity (RH): Test duration:	+40°C ±2°C 93% ±2% 56 days	$ \Delta$ C/C ≤ 3%, Δ tan δ ≤ 0.001 at 1 kHz IR after test ≥ 50% of initial limit
Endurance Test	Test Conditions		Performances
	Temperature: Voltage applied: Test duration:	+85°C ±2°C 1.25 x V _R (DC) 2,000 hours	$ \Delta$ C/C ≤ 3%, Δ tan δ ≤ 0.001 at 10 kHz IR after test ≥ 50% of initial limit
Resistance to Soldering Heat Test	Test Conditions		Performances
	Solder bath temperature: Dipping time (with heat screen):	260°C ±5°C 10 seconds ±1 second	$ \Delta$ C/C ≤ 2%, Δ tan δ ≤ 0.001 at 10 kHz for C ≤ 1 μ F IR after test ≥ initial limit

Environmental Compliance

All KEMET pulse capacitors are RoHS Compliant.



Film Capacitors – Polypropylene Pulse/High Frequency Capacitors

R79, Single Metallized Polypropylene Film, Radial, 5 mm Lead Spacing, Multipurpose Applications

KEVET

a VAGEO company

Table 1 - Ratings & Part Number Reference

VDC	VAC	Capacitance	Dime	nsions i	n mm	Lead	dV/dt	Max K₀	KEMET Internal	Customer
VDC	VAC	Value (µF)	Т	Н	L	Spacing (S)	(V/µs)	(V ² /μs)	Part Number	Part Number
160	70	0.039	3.5	7.5	7.2	5.0	100	32,000	79GC2390(1)40(2)	R79GC2390(1)40(2)
160	70	0.047	4.5	9.5	7.2	5.0	100	32,000	79GC2470(1)40(2)	R79GC2470(1)40(2)
160	70	0.056	4.5	9.5	7.2	5.0	100	32,000	79GC2560(1)40(2)	R79GC2560(1)40(2)
160	70	0.068	4.5	9.5	7.2	5.0	100	32,000	79GC2680(1)40(2)	R79GC2680(1)40(2)
160	70	0.082	5.0	10.0	7.2	5.0	100	32,000	79GC2820(1)40(2)	R79GC2820(1)40(2)
160	70	0.10	5.0	10.0	7.2	5.0	100	32,000	79GC3100(1)40(2)	R79GC3100(1)40(2)
160	70	0.12	6.0	11.0	7.2	5.0	100	32,000	79GC3120(1)40(2)	R79GC3120(1)40(2)
160	70	0.15	6.0	11.0	7.2	5.0	100	32,000	79GC3150(1)40(2)	R79GC3150(1)40(2)
160	70	0.18	7.2	13.0	7.2	5.0	100	32,000	79GC3180(1)40(2)	R79GC3180(1)40(2)
160	70	0.22	7.2	13.0	7.2	5.0	100	32,000	79GC3220(1)40(2)	R79GC3220(1)40(2)
250	160	0.012	3.5	7.5	7.2	5.0	250	125,000	79IC2120(1)45(2)	R79IC2120(1)45(2)
250	160 160	0.015 0.018	3.5	7.5 7.5	7.2 7.2	5.0	250	125,000	79IC2150(1)45(2)	R79IC2150(1)45(2)
250 250	160	0.018	3.5 3.5	7.5 7.5	7.2	5.0 5.0	250 250	125,000 125,000	79IC2180(1)45(2) 79IC2220(1)45(2)	R79IC2180(1)45(2) R79IC2220(1)45(2)
250	160	0.027	3.5	7.5	7.2	5.0	250	125,000	791C2220(1)45(2) 791C2270(1)45(2)	R79IC2270(1)45(2)
250	160	0.027	3.5	7.5	7.2	5.0	250	125,000	79IC2270(1)45(2) 79IC2330(1)45(2)	R79IC2270(1)45(2)
250	160	0.033	4.5	9.5	7.2	5.0	250	125,000	791C2330(1)43(2) 791C2390(1)40(2)	R79IC2330(1)43(2)
250	160	0.047	4.5	9.5	7.2	5.0	250	125,000	79IC2470(1)40(2)	R79IC2470(1)40(2)
250	160	0.056	4.5	9.5	7.2	5.0	250	125,000	79IC2560(1)40(2)	R79IC2560(1)40(2)
250	160	0.068	5.0	10.0	7.2	5.0	250	125,000	79IC2680(1)40(2)	R79IC2680(1)40(2)
250	160	0.082	6.0	11.0	7.2	5.0	250	125,000	79IC2820(1)40(2)	R79IC2820(1)40(2)
250	160	0.10	6.0	11.0	7.2	5.0	250	125,000	79IC3100(1)40(2)	R79IC3100(1)40(2)
250	160	0.12	7.2	13.0	7.2	5.0	250	125,000	79IC3120(1)40(2)	R79IC3120(1)40(2)
250	160	0.15	7.2	13.0	7.2	5.0	250	125,000	79IC3150(1)40(2)	R79IC3150(1)40(2)
400	200	0.0039	3.5	7.5	7.2	5.0	400	320,000	79MC1390(1)40(2)	R79MC1390(1)40(2)
400	200	0.0047	3.5	7.5	7.2	5.0	400	320,000	79MC1470(1)40(2)	R79MC1470(1)40(2)
400	200	0.0056	3.5	7.5	7.2	5.0	400	320,000	79MC1560(1)40(2)	R79MC1560(1)40(2)
400	200	0.0068	3.5	7.5	7.2	5.0	400	320,000	79MC1680(1)40(2)	R79MC1680(1)40(2)
400	200	0.0082	3.5	7.5	7.2	5.0	400	320,000	79MC1820(1)40(2)	R79MC1820(1)40(2)
400	200	0.010	3.5	7.5	7.2	5.0	400	320,000	79MC2100(1)40(2)	R79MC2100(1)40(2)
400	200	0.012	4.5	9.5	7.2	5.0	400	320,000	79MC2120(1)40(2)	R79MC2120(1)40(2)
400	200	0.015	4.5	9.5	7.2	5.0	400	320,000	79MC2150(1)40(2)	R79MC2150(1)40(2)
400	200	0.018	5.0	10.0	7.2	5.0	400	320,000	79MC2180(1)40(2)	R79MC2180(1)40(2)
400	200	0.022	5.0	10.0	7.2	5.0	400	320,000	79MC2220(1)40(2)	R79MC2220(1)40(2)
400	200	0.027	6.0	11.0	7.2	5.0	400	320,000	79MC2270(1)40(2)	R79MC2270(1)40(2)
400	200	0.033	6.0	11.0	7.2	5.0	400 400	320,000	79MC2330(1)40(2)	R79MC2330(1)40(2)
400	200	0.039 0.047	7.2	13.0	7.2 7.2	5.0		320,000	79MC2390(1)40(2)	R79MC2390(1)40(2)
400 630	200 220	0.047	7.2 3.5	13.0 7.5	7.2 7.2	5.0 5.0	400 500	320,000 630,000	79MC2470(1)40(2) 79PC1100(1)40(2)	R79MC2470(1)40(2) R79PC1100(1)40(2)
630	220	0.0010	3.5	7.5 7.5	7.2	5.0	500	630.000	79PC1100(1)40(2) 79PC1120(1)40(2)	R79PC1120(1)40(2)
630	220	0.0012	3.5	7.5	7.2	5.0	500	630,000	79PC1150(1)40(2)	R79PC1120(1)40(2)
630	220	0.0018	3.5	7.5	7.2	5.0	500	630,000	79PC1180(1)40(2)	R79PC1180(1)40(2)
630	220	0.0022	3.5	7.5	7.2	5.0	500	630,000	79PC1220(1)40(2)	R79PC1220(1)40(2)
630	220	0.0027	3.5	7.5	7.2	5.0	500	630,000	79PC1270(1)40(2)	R79PC1270(1)40(2)
630	220	0.0033	3.5	7.5	7.2	5.0	500	630,000	79PC1330(1)40(2)	R79PC1330(1)40(2)
630	220	0.0039	4.5	9.5	7.2	5.0	600	756,000	79PC1390(1)40(2)	R79PC1390(1)40(2)
630	220	0.0047	4.5	9.5	7.2	5.0	600	756,000	79PC1470(1)40(2)	R79PC1470(1)40(2)
630	220	0.0056	4.5	9.5	7.2	5.0	600	756,000	79PC1560(1)40(2)	R79PC1560(1)40(2)
630	220	0.0068	5.0	10.0	7.2	5.0	600	756,000	79PC1680(1)40(2)	R79PC1680(1)40(2)
630	220	0.0082	5.0	10.0	7.2	5.0	600	756,000	79PC1820(1)40(2)	R79PC1820(1)40(2)
630	220	0.010	6.0	11.0	7.2	5.0	600	756,000	79PC2100(1)40(2)	R79PC2100(1)40(2)
630	220	0.012	6.0	11.0	7.2	5.0	600	756,000	79PC2120(1)40(2)	R79PC2120(1)40(2)
630	220	0.015	7.2	13.0	7.2	5.0	600	756,000	79PC2150(1)40(2)	R79PC2150(1)40(2)
630	220	0.018	7.2	13.0	7.2	5.0	600	756,000	79PC2180(1)40(2)	R79PC2180(1)40(2)
VDC	VAC	Capacitance Value (µF)	T (mm)	H (mm)	L (mm)	Lead Spacing (S)	dV/dt (V/μs)	Max K ₀ (V²/μs)	KEMET Internal Part Number	Customer Part Number

⁽¹⁾ Insert lead and packaging code. See Ordering Options Table for available options.

⁽²⁾ J = 5%, K = 10%, M = 20%

Film Capacitors – Polypropylene Pulse/High Frequency Capacitors

R79, Single Metallized Polypropylene Film, Radial, 5 mm Lead Spacing, Multipurpose Applications



Soldering Process


The implementation of the RoHS directive has resulted in the selection of SnAgCu (SAC) alloys or SnCu alloys as a primary solder. This has increased the liquidus temperature from that of 183°C for SnPb eutectic alloy to 217 – 221°C for the new alloys. As a result, the heat stress to the components, even in wave soldering, has increased considerably due to higher pre-heat and wave temperatures. Polypropylene capacitors are especially sensitive to heat (the melting point of polypropylene is 160 – 170°C). Wave soldering can be destructive, especially for mechanically small polypropylene capacitors (with lead spacing of 5 mm to 15 mm), and great care has to be taken during soldering. The recommended solder profiles from KEMET should be used. Please consult KEMET with any questions. In general, the wave soldering curve from IEC Publication 61760–1 Edition 2 serves as a solid guideline for successful soldering. Please see Figure 1.

Reflow soldering is not recommended for through-hole film capacitors. Exposing capacitors to a soldering profile in excess of the above recommended limits may result in degradation or permanent damage to the capacitors.

Do not place the polypropylene capacitor through an adhesive curing oven to cure resin for surface mount components. Insert through-hole parts after the curing of surface mount parts. Consult KEMET to discuss the actual temperature profile in the oven, if through-hole components must pass through the adhesive curing process. A maximum two soldering cycles is recommended. Please allow time for the capacitor surface temperature to return to a normal temperature before the second soldering cycle.


Manual Soldering Recommendations

The following is recommended for manual soldering with a soldering iron.



The soldering iron tip temperature should be set at 350°C (+10°C maximum) with the soldering duration not to exceed more than 3 seconds.

Wave Soldering Recommendations



Film Capacitors – Polypropylene Pulse/High Frequency Capacitors

R79, Single Metallized Polypropylene Film, Radial, 5 mm Lead Spacing, Multipurpose Applications



Soldering Process cont.

Wave Soldering Recommendations cont.


1. The table indicates the maximum set-up temperature of the soldering process Figure 1.

Dielectric Film		n Preheat erature	Maximum Peak Soldering Temperature		
Material	Capacitor Pitch ≤ 15 mm	Capacitor Pitch > 15 mm	Capacitor Pitch ≤ 15 mm	Capacitor Pitch > 15 mm	
Polyester	130°C	130°C	270°C	270°C	
Polypropylene	110°C	130°C	260°C	270°C	
Paper	130°C	140°C	270°C	270°C	
Polyphenylene Sulphide	150°C	160°C	270°C	270°C	

2. The maximum temperature measured inside the capacitor:

Set the temperature so that inside the element the maximum temperature is below the limit:

Dielectric Film Material	Maximum temperature measured inside the element
Polyester	160°C
Polypropylene	110°C
Paper	160°C
Polyphenylene Sulphide	160°C



Temperature monitored inside the capacitor.

Selective Soldering Recommendations

Selective dip soldering is a variation of reflow soldering. In this method, the printed circuit board with through-hole components to be soldered is preheated and transported over the solder bath as in normal flow soldering without touching the solder. When the board is over the bath, it is stopped and pre-designed solder pots are lifted from the bath with molten solder only at the places of the selected components, and pressed against the lower surface of the board to solder the components.


The temperature profile for selective soldering is similar to the double wave flow soldering outlined in this document, however, instead of two baths, there is only one bath with a time from 3 to 10 seconds. In selective soldering, the risk of overheating is greater than in double wave flow soldering. Great care must be taken so that the parts are not overheated.

Film Capacitors - Polypropylene Pulse/High Frequency Capacitors


R79, Single Metallized Polypropylene Film, Radial, 5 mm Lead Spacing, Multipurpose Applications



Construction



Winding Scheme




Film Capacitors - Polypropylene Pulse/High Frequency Capacitors

R79, Single Metallized Polypropylene Film, Radial, 5 mm Lead Spacing, Multipurpose Applications



Voltage Code

Marking



Film Capacitors - Polypropylene Pulse/High Frequency Capacitors





Marking cont.

	Manufacturing Date Code (IEC-60062)									
Year	Code	Year	Code	Month	Code	Month	Code			
2010	Α	2020	М	January	1	July	7			
2011	В	2021	N	February	2	August	8			
2012	С	2022	Р	March	3	September	9			
2013	D	2023	R	April	4	October	0			
2014	E	2024	S	May	5	November	N			
2015	F	2025	T	June	6	December	D			
2016	Н	2026	U							
2017	J	2027	V							
2018	K	2028	W							
2019	L	2029	Х]						
2020	М	2030	А	1						

Packaging Quantities


Lead Spacing	Thickness (mm)	Height (mm)	Length (mm)	Bulk Short Leads	Bulk Long Leads	Standard Reel ø 355 mm	Ammo Taped
Spassing	Lead	and Packaging	Code	AA - JC JE - JH	Z3	СК	DQ
	3.5	7.5	7.2	2,000	3,000	1,800	2,500
	4.5	9.5	7.2	1,500	2,000	1,400	1,900
5.0	5.0	10	7.2	1,000	1,500	1,200	1,700
	6.0	11	7.2	2,000	1,000	1,000	1,400
	7.2	13	7.2	1,500	750	800	1,150

Film Capacitors - Polypropylene Pulse/High Frequency Capacitors

R79, Single Metallized Polypropylene Film, Radial, 5 mm Lead Spacing, Multipurpose Applications



Lead Taping & Packaging (IEC 60286-2)



Taping Specification

		Dimensio	ons (mm)
Description	Symbol	Lead Spacing	
Becomption	- Cymbon	5	Tolerance
		Figure 1	
Lead wire diameter	d	0.5	±0.05
Taping lead space	Р	12.7	±1
Feed hole lead space	P ₀	12.7	±0.2**
Centering of the lead wire	P ₁	3.85	±0.7
Centering of the body	P ₂	6.35	±1.3
Lead spacing	F	5	+0.6/-0.1
Component alignment	Dh	0	±2
Height of component from tape center	H ₀ *	18.5	±0.5
Carrier tape width	W	18	+1/-0.5
Hold down tape width	W _o	6	Minimum
Hole position	W ₁	9	±0.5
Hold down tape position	W ₂	3	Maximum
Feed hole diameter	D ₀	4	±0.2
Total Tape thickness	t	0.7	±0.2

^{*} H_0 = 16.5 mm is available upon request.

^{**}Maximum 1 mm on 20 lead spacing.

Film Capacitors - Polypropylene Pulse/High Frequency Capacitors

R79, Single Metallized Polypropylene Film, Radial, 5 mm Lead Spacing, Multipurpose Applications




Lead Taping & Packaging (IEC 60286-2) cont.

Ammo Specifications


Dimensions (mm)			
Н	W	Т	
360*	340	59	


^{*} Lower dimension available upon request (Maximum 295 mm)



Reel Specifications

Dimensions (mm)			
D	H	W	
355	30	55 Maximum	





Film Capacitors – Polypropylene Pulse/High Frequency Capacitors

R79, Single Metallized Polypropylene Film, Radial, 5 mm Lead Spacing, Multipurpose Applications



KEMET Electronics Corporation Sales Offices

For a complete list of our global sales offices, please visit www.kemet.com/sales.

Disclaimer

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicted or that other measures may not be required.