



VDB-218

denver.eu

04/2026



FR
Cet appareil,
ses accessoires
et ses batteries
sont recyclables



A DÉPOSER
EN MAGASIN
OU



Points de collecte sur www.quefairedesdechets.fr
Privilégiez la réparation ou le don de votre appareil !

Safety information

Please read the safety instructions carefully before using the product for the first time and keep the instructions for future reference.

- This product is not a toy. Keep it out of the reach of children.
- Warning: this product includes built-in lithium batteries.
- Keep the batteries out of the reach of children.
- Never use old and new batteries or different types of batteries together.
- Remove the batteries from the chime when not using it for long periods of time. Check the polarity (+/-) of the batteries when inserting them in the chime. Incorrect positioning may cause the risk of an explosion.
- The product's operating and storage temperature range is between -10 degree Celsius to +50 degree Celsius
- Environments under and above this temperature might affect functionality.
- Only use the accessories which are packaged with the doorbell.
- Using third party accessories can cause interference signal issues which can also cause the product to work abnormally.

- Repairs or service should only be performed by qualified personnel.

Denver A/S reserve the rights for print errors.

Denver A/S cannot be held responsible for any technical or typographical errors and reserves the right to make changes to the product and manuals without prior notice. if you detect any inaccuracies or omissions, please inform us at the address on the back cover.

Basic Parameters

Product Name: Smart Doorbell Camera	
Resolution: 4MP	PIR human detection: Supports PIR detection to wake up
Day and night conversion: dual filters automatically switch	Two-Way Audio: support fullduplex real-time calls
Local storage: 256GB Micro SD card	Wireless Network : 2.4G 802.11 b/g/n
Supported platforms: Android /iOS	Audio input / output: -38dB microphone/ speaker


Get Started:


For the best experience: We recommend you fully charge your battery before setup. Access the charging port by using the included Release Pin to remove the Mounting Plate . The LED on the front of the video doorbell will turn off when 100% charged.

Packing list: smart doorbell camera x 1, manual x 1, USB Power Cord screw accessory package x1



Product Introduction

1. Doorbell Camera







2. Doorbell Chime




What's in the box




Doorbell
Camera




Mounting
Bracket




Template
Sticker




Inclined
Bracket



Chime



AAA
Battery*3



Pack of
Screws



8-24V AC
Power Cable



Power Cord

Setup

- Download the "Tuya Smart" app, create an account and then log in.
- Make sure the camera is fully charged. Press the power button for about 5 seconds until you hear the startup voice prompt. Then press the reset button for about 5 seconds until the indicator light flashes red and blue alternately.

- Open the "Tuya Smart" app, tap the "+" or "Add device" button, find the Denver VDB-218 - Video Doorbell camera in the list, then follow the in-app instruc-




Indicator lights status

Light Status	Camera Status
 Slowly flashing red light	Camera powered-on
 Rapidly flashing blue light	Wi-Fi connection in progress
 Solid blue light	Camera working properly
 Slowly flashing blue light	Camera charging
 Light off	Camera standby / fully charged

Connect to the chime

- ① Make sure the chime is loaded with usable batteries.
- ② Press the configuration button of the chime. The indicator light will flash and you will hear a tone indicating it enters pairing mode.




- ③ Press the call button on the video doorbell to request pairing within 30 seconds.
- ④ The chime indicator light stops flashing and rings when pairing is successful.


Chime buttons

 Configuration Button	Reset/Single press to enter configuration mode
 Volume Button	Loop button to adjust volume level
 Music Button	Loop button to switch music

non-15-degree mounting bracket



15-degree mounting bracket



- ① Mount by Screw
- ② Insert the doorbell
- ③ Tight it by the screw

Install APP


Download APP: scan the QR code below to download and install.

Register and login: open the "Tuya Smart" APP to register and login according to the prompts.




Add The Device-ScanQRcode mode

- Make sure Wi-Fi is available and connected to the Internet.
- Connect the camera to the power, then system startup completed.
- Open "Tuya Smart" APP, press the '+' in the upper right corner of the main screen (Figure 01); choose "Camera & Lock", click "Doorbell Camera" (Figure 02) to add camera; and then click "Next step" (Figure 03);





Please note that only 2.4 GHz Wi-Fi network is supported;


- If the mobile phone is not connected to Wi-Fi, please click "Connect to Wi-fi" (Figure 04);
- It will jump to the WLAN interface and connects Wi-Fi (Figure 05).
- If the phone is connected to Wi-Fi (Figure 06);




- A QR code will prompt on your screen and you need to scan it with the Smart Camera. (the camera is about 20-30 cm away from the mobile phone lens). Then click "hear the prompt sound" (Figure. 07.)
- "connecting" (Figure. 08);



- Connection completed(Figure 09), and click "Done";
- Then jump to preview interface (Figure 10)
- After closing the device preview interface, the interface returns to the APP home page. At this time, the connected device will appear on the APP home page (Figure 11). Then you can click directly to the device interface to see the monitoring situation without re-adding afterwards.



Video Call Function



Call operation diagram



FAQ:

Q: How do I reset the doorbell?

A: Press and hold the RESET button for around 5 seconds.

Q: How do I share the video doorbell with my family?

A: 1. Tap the doorbell to live view from the home page of the app.
2. Tap the 'Settings' icon on the top right corner of the home page.
3. Select 'Share device'.
4. Tap 'Add sharing', then enter the name of the account you want share to, or you can follow the in-app instructions to set up family sharing.

Q: How do I adjust PIR motion detection sensitivity?

A: 1. From the home page, tap the doorbell to see the live view.
2. Tap the settings icon of the top right corner.

3. Select the PIR and choose the High, Medium, Low level as desired.

Options for PIR motion sensitivity

High: Records and notifies you about every motion. -- Shortest battery life.

Medium: Records and notifies you about motion less often. -- Standard battery life.

Low: Records and notifies you about motion even less often than the medium setting. -- Standard maximum battery life.

Q: How many users can view the video at the same time?

A: Up to 4 users may view the video feed. Both iOS and Android are compatible.

Q: Does the doorbell support 5GHz Wi-Fi?

A: No. The doorbell only supports 2.4GHz Wi-Fi.

Q: The signal is poor on my doorbell.


A: Your doorbell may be too far away from your wireless router or you may have some obstructions in between that reduce signal strength. You might try repositioning your router or getting a signal extender/repeater for your wireless router.

Warning! 

1. Lithium battery inside!
2. Do not try to open the product!
3. Do not expose to heat, water, moisture or direct sunlight!

Please notice - All products are subject to change without any notice. We take reservations for errors and omissions in the manual.

ALL RIGHTS RESERVED, COPYRIGHT DENVER A/S



Electric and electronic equipment and included batteries contains materials, components and substances that can be hazardous to your health and the environment, if the waste material (discarded electric and electronic equipment and batteries) is not handled correctly.

Electric and electronic equipment and batteries is marked with the crossed out trash can symbol, seen above. This symbol signifies that electric and electronic equipment and batteries should not be disposed of with other household waste, but should be disposed of separately.

As the end user it is important that you submit your used batteries to the appropriate and designated facility. In this manner you make sure that the batteries are recycled in accordance with legislature and will not harm the environment.

All cities have established collection points, where electric and electronic equipment and batteries can either be submitted free of charge at recycling stations and other collection sites, or be collected from the households. Additional information is available at the technical department of your city.

Hereby, Denver A/S declares that the radio equipment type VDB-218 is in compliance with Directive 2014/53/EU. The full text of the RED declaration of conformity is available at the following internet address: denver.eu and then click the search ICON on topline of website. Write model number: VDB-218 . Now enter product page, and RED directive is found under downloads/other downloads. Alternatively, the QR code below can be scanned and the file can be accessed directly.

Hereby, Denver A/S declares that this connected device is in compliance with Data Act Regulation (EU) 2023/2854. The Data Act (EU) 2023/2854 product data sheet is available at the following internet address: denver.eu and then click the search ICON on topline of website. Write model number: VDB-218 . Now enter product page, and the

Data Act (EU) 2023/2854 product data sheet is found under downloads/other downloads. Alternatively, the QR code below can be scanned and the file can be accessed directly.

Information on standby/off mode power consumption and power management for products compliant with Commission Regulation (EU) 2023/826 can be found at the following internet address: denver.eu and then click the search ICON on topline of website. Write model number: VDB-218 and enter the page.



Operating frequency range:
2400 MHz-2483 MHz
Max RF output power: 20 dBm

DENVER A/S
Omega 5A, Soeflen
DK-8382 Hinnerup
Denmark

www.denver.eu
www.facebook.com/denver.eu

Contact

Main contact point:
contact.hq@denver.eu

Nordics

Headquarter

Denver A/S
Omega 5A, Soefte
DK-8382 Hinnerup
Denmark

Phone: **+45 86 22 61 00**
(Push "1" for support)

E-Mail

For technical questions, please write to:
support.hq@denver.eu

For all other questions please write to:
contact.hq@denver.eu

Benelux

DENVER BENELUX B.V.

Barwoutswaarder 13C+D
3449 HE Woerden
The Netherlands

Phone: **0900-3437623**
E-Mail: **support.nl@denver.eu**

Spain/Portugal

DENVER SPAIN S.A

Ronda Augustes y Louis Lumiere,
nº 23 - nave 16

Parque Tecnológico
46980 PATERNA
Valencia (Spain)

Spain

Phone: **+34 960 046 883**

Mail: **support.es@denver.eu**

Portugal:

Phone: **+35 1255 240 294**

E-Mail: **denver.service@satfiel.com**

Germany

Denver Germany GmbH Service

Service Center
Max-Emanuel-Str. 4
94036 Passau

Phone: **+49 851 379 369 40**

E-Mail

support.de@denver.eu

Monday - Thursday 09:00 - 16:30

Friday 09:00 - 14:00

Austria

Lurf Premium Service GmbH
Deutschstrasse 1
1230 Wien

Phone: **+43 1 904 3085**

E-Mail: **denver@lurfservice.at**

Poland

LetMeRepair Poland sp. z o.o.

ul. Częstochowska 140
62-800 Kalisz

Phone: **62 75 38 092**

E-Mail: **denver-service@letmerepair.pl**

Godziny pracy: 8 – 18 (poniedziałek – piątek)

If your country is not listed above,
please write an email to
contact.hq@denver.eu



Denver A/S
Omega 5A, Soefte
DK-8382 Hinnerup
Denmark

denver.eu
facebook.com/denver.eu

