

DATA SHEET

0043006

ÖLFLEX® CRANE NSHTÖU

valid from:

11.09.2008

Application

ÖLFLEX® CRANE NSHTÖU cables are connecting and control cables special for use in drum guidance, hoists, transport and conveyor systems for high mechanical load considering the admissible values. Furthermore they are for use as hawser, drum and drag cable as well as for power chains. They are among others useable in dry and damp rooms and in industrial water. Considering the indicated temperature range an outdoor use is possible. Usage under a strain of more than 20 N / mm² is not allowed. At room temperature they are widely resistant to acids, chemical resistant and certain oils.

Design

Design acc. to VDE 0250 part 814

Conductor fine strands of tinned copper wires acc. to IEC 60228 resp. VDE 0295, class 5

Core insulation rubber compound 3GI3 acc. to VDE 0207 part 20

Core identification acc. to VDE 0293-1, with gn/ye ground conductor

up to 5 cores coloured in acc. to HD 308 S2 resp. VDE 0293-308;

more than 5 cores: Black cores with white numbers acc. to DIN EN 50334 resp. VDE 0293 part 334

Outer sheath rubber compound 5GM3 acc. to VDE 0207 part 21, colour black

Braiding supporting braid of textile integrated in the outer sheath

Electrical properties at 20 °C

Nominal voltage 600 / 1000 V

Test voltage 4000 V AC

Mechanical and thermal properties

Temperature range fixed installation -45 °C up to +60 °C max. ambient temperature

for flex. applications $-25 \, ^{\circ}\text{C}$ up to $+60 \, ^{\circ}\text{C}$ max. ambient temperature

up to +80 °C max. conductor temperature

Min. bending radius for flex. applications

with an outer diameter < 21.5 mm : 5 x cable diameter with an outer diameter > 21.5 mm : 6.25 x cable diameter

Flammability flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2

Oil resistance acc. to IEC 60811-2-1 resp. VDE 0473 part 811-2-1

Tests acc. to IEC 60811 resp. VDE 0473 and VDE 0472

Approvals acc. to VDE 0250 part 814

EC directive This cable is conform to ECD 2006/95/EC (low voltage directive).

Originator: M. Herb / TE-K			
approved: W. Körner / TE	Document:	DB0043006EN	page 1 of 1