

# HD32.2, HD32.2A, WBGT Index



## HD 32.2, HD32.2A **INSTRUMENT FOR THE ANALYSIS OF THE WBGT INDEX**

HD32.2 - WBGT Index is an instrument made by Delta OHM srl for the analysis of WBGT index (Wet Bulb Glob Temperature: wet bulb temperature and globe thermometer temperature) in presence or in absence of solar radiation.

#### **Reference Regulations:**

**ISO 7243:** Hot environments. Estimation of the heat stress on working man, based on WBGT index (wet bulb temperature and Globe thermometer).

ISO 8996: Ergonomics of the thermal environment - Determination of the energy metabolism.

ISO 7726: Ergonomics of the thermal environment - Instruments for measuring physical quantities.

The instrument is provided with three inputs for probes with SICRAM module: the SICRAM module interface between the instrument and sensor connected and communicate the sensor parameters and calibration data to the instrument.

The instrument is equipped with three inputs for probes with SICRAM module: the probes have an electronic circuit that communicates with the instrument and stores the sensor calibration data. All SICRAM probes can be connected to any of the instrument's inputs, they are automatically recognized upon turning the Instrument on. The main features of the instrument are:

- . Logging: data acquisition and logging to the internal instrument memory. Storage capacity: 64 different logging sections, sample interval, user selectable.
- You can set the automatic logging start with auto-start function (Start/Stop time).
- The measurement unit of the temperature: °C, °F, °K.
- The display of **maximum, minimum, medium** statistic parameters.
- The data transfer via the RS232 or USB serial ports.

HD32.2 instrument can detect simultaneously the following quantities:

- Globe thermometer temperature Tg.
- · Wet bulb temperature with natural ventilation Tn.
- Environment temperature T.

Starting from the detected values, HD32.2 can calculate:

- WBGT(in) index (Wet Bulb Glob Temperature: wet bulb temperature and Globe thermometer) in absence of solar radiation.
- WBGT(out) index (Wet Bulb Glob Temperature wet bulb temperature and Globe thermometer) in presence of solar radiation.

#### **WBGT** index

**WBGT** (Wet Bulb Globe Temperature – Wet bulb temperature and globe thermometer) is one of the indexes used to determinate the occupational heat exposure.

It represents the value, related to the metabolic expenditure linked to a specific work activity, that causes a thermal stress when exceeded.

WBGT index combines the temperature measurement of wet bulb with natural ventilation  $\mathbf{t}_{nw}$  with the globe thermometer  $\mathbf{t}_n$  and, in some situations, with the air temperature  $t_a$ .

The calculation formula is the following:

• inside and outside a buildings in absence of solar radiation:

WBGT  $_{close\ environments} = 0.7\ t_{nw} + 0.3\ t_{g}$ 

outside a building in presence of solar radiation:

 $WBGT_{outside\ environments} = 0.7\ t_{nw} + 0.2\ t_g + 0.1\ t_a$ 

 $t_{nw}$  = natural wet bulb;

 $t_a$  = globe thermometer temperature;

 $\vec{t}_a$  = air temperature.

The measured data should be compared with the limit values prescribed by the requlations:

when exceeded you have to:

- reduce directly the thermal stress on the examined work place;
- proceed to a detailed analysis of the thermal stress.

In order to measure the WBGT index, the following probes should be connected:

- Natural wet bulb HP3201.2 (HP3201).
- TP3276.2 Globe thermometer probe (TP3276 or TP3275).
- TP3207.2 (TP3207) Dry bulb temperature, if the measurement is performed in presence of solar radiation.

In order to measure the WBGT index, you should refer to the following regulations:

- ISO 7726
- ISO 7243
- ISO 8996

## **Technical features**

Instrument **Dimensions** 

(Length x Width x Height)

Weight

Materials

Display

185x90x40 mm

470 g (batteries included)

ABS, rubber

back light, with dot-matrix

160x160 points, visible area 52x42mm



**Working conditions** 

Working temperature  $-5 \dots 50^{\circ}$ C Storage temperature  $-25 \dots 65^{\circ}$ C

Working relative humidity 0 ... 90% RH no condensation

Protection Degree

Instrument uncertainty ± 1 digit @ 20°C

Power supply (code SWD10) 12Vdc/1A

IP65

Batteries 4 batteries 1.5V type AA

Autonomy 200 hours with 1800mAh alkaline batteries

Power absorbed with instrument off  $< 45\mu A$ 

Safety of the stored data unlimited

TP3207.2 (TP3207) Temperature probe

Connection: 4 wires plus SICRAM module
Connector: 8 female poles DIN45326
Dimensions: Ø=14 mm L= 150 mm

Response time T<sub>95</sub>: 15 minutes



Example of immediate data print, obtained with **HD40.1** printer.

ISO 7243 WBGT Index

Model HD32.2 WBGT Index Firm.Ver.=01.00 Firm.Date=2008/12/05

SN=12345678 ID=00000000000000000

Probe ch.1 description

Type: Pt100 Data cal.:2008/10/01 Serial N.:08109450

Probe ch.2 description Type: Pt100 Tg 50

Data cal.:2008/10/01 Serial N.:08109452

Probe ch.3 description Type: Pt100 Tw Data cal.:2008/10/01 Serial N.:08109454

Date=2008/11/21 15:00:00
Tnw 21.2 °C
Tg 24.9 °C
Ta 31.3 °C
WBGT (i) 22.3 °C
WBGT (o) 23.0 °C

Notes:

NOTES

Reference standard

Instrument Model Instrument firmware version Instrument firmware date Instrument Serial Number Identification Code

Description of the probe connected to input  $\ensuremath{\mathsf{1}}$ 

Description of the probe connected to input 2

Description of the probe connected to input 3

Date and time
Natural wet bulb
Globe thermometer ventilation
Dry bulb temperature
WBGT in absence of direct solar radiation
WBGT in presence of direct solar radiation





TP3276.2 Globe thermometer probe Ø=50 mm (Ø=150mm TP3275)

Sensor type: Pt100

 $\begin{array}{lll} \text{Connection:} & \text{4 wires plus SICRAM module} \\ \text{Connector:} & \text{8 female poles DIN45326} \\ \text{Stem dimensions:} & \emptyset = 8 \text{ mm} \quad L = 170 \text{ mm} \\ \end{array}$ 

Response time T<sub>95</sub>: 15 minutes

HP3201.2 (HP3201) Natural ventilation wet bulb

Tank capacity: 15 cc.

Tank autonomy: 96 hours with RH=50%,  $t = 23^{\circ}C$ 

Response time T<sub>95</sub>: 15 minutes

**Connections** Input for probes with SICRAM module 3

Connectors 8 male poles DIN 45326

**USB** Interface

Type USB 1.1 or 2.0 not isolated

Connection Mini-USB Baud rate 460800

RS232 Serial Interface:

Pin: M12-8 poles.

Type: RS232C (EIA/TIA574) not insulated

Baud rate: from 1200 to 38400 baud.

Data bit: 8
Parity: None
Stop bit: 1

Flow control: Xon-Xoff Cable length: max 15m

**Memory** divided in 64 blocks.


**Storage capacity** 67600 memorizations for each of the 3 inputs.

**Logging interval** selectable among: 15, 30 seconds, 1, 2, 5, 10, 15, 20, 30 minutes and 1 hour.



HP3201.2 TP3276.2 TP3207.2

Storage capacity
Approx. 11 days and 17 hours
Approx. 23 days and 11 hours
Approx. 46 days and 22 hours
Approx. 93 days and 21 hours
Approx. 234 days and 17 hours
Approx. 1 year and 104 days
Approx. 1 year and 339 days
Approx. 2 years and 208 days
Approx. 3 years and 313 days
Approx. 7 years and 261 days



- A USB connection to PC using type A USB M12 cable, code HD2110USB. **USB drivers** are required.
- B RS232C connection to PC. It allows you to connect the RS232C serial port of a PC or the printer HD40.1 with the cable HD2110RS.

#### **ORDERING CODES**

HD32.2 consisting of:

H032.2 WBGT Index instrument, 4 alkaline batteries 1.5V AA type, instruction manual, case. DeltaLog10 Software Warm environments: WBGT analysis downloadable from Delta OHM website. Probes and cables have to be ordered separately.

Required probes for the measurement of WBGT:

- TP3207.2 Probe of dry bulb temperature.
- TP3276.2 Globe thermometer probe.
- HP3201.2 Natural ventilation wet bulb

### HD32.2A consisting of:

HD32.2 WBGT Index instrument, 4 alkaline batteries 1.5V AA type, instruction manual, case. DeltaLog10 Software Warm environments: WBGT analysis downloadable from Delta OHM website. Probes and cables have to be ordered separately.

Required probes for the measurement of WBGT version A:


- TP3207 Dry bulb temperature.
- TP3275 Globe thermometer probe.
- HP3201 Natural ventilation wet bulb.

### Probes for HD32.2 WBGT Index (without cable):

**TP3207.2:** Temperature probe with Pt100 sensor. Probe stem Ø 14mm, length 150 mm. Equipped with SICRAM module.

**TP3276.2:** Globe thermometer probe with Pt100 sensor, globe Ø 50 mm. Stem Ø 8 mm, length 170 mm. Equipped with SICRAM module.

HP3201.2: Natural wet bulb. Pt100 sensor. Probe stem Ø 14 mm, length 170 mm. Equipped with SICRAM module, spare parts of the braid and case of 50cc. distilled water.



### Probes for HD32.2 version A (with cable):

**TP3207:** Temperature probe with Pt100 sensor. Probe stem Ø 14mm, length 140 mm. Cable length 2m. Equipped with SICRAM module.

TP3275: Globe thermometer probe with Pt100 sensor, globe Ø 150 mm. Stem Ø 14 mm, length 110 mm. Cable length 2m. Equipped with SICRAM module.

**HP3201:** Natural ventilation wet bulb. Pt100 sensor. Probe stem  $\emptyset$  14 mm, length 110 mm. Cable length 2m. Equipped with SICRAM module, spare braids and 50cc of distilled water.

**TP3204S:** Natural ventilation wet bulb probe for long-lasting measurements. Capacity: 500 cc of distilled water. Autonomy: 15 days @ 40 °C. Pt100 sensor. 2 m cable. Complete with SICRAM module, 500 cc bottle and 2 spare cotton wicks.



#### **Accessories:**

VTRAP30: Tripod to suit instrument with a maximum height of 280 mm

VTRAP32.2A.3A: Tripod with instrument holder for HD32.2A

HD32.2.7.1: Probe holder, to be fixed on standard tripod. For version HD32.2A.

HD2110 RS: Connection cable with M12 connector from the instrument side and with SubD female connector 9 poles for RS232C from PC side.

HD2110USB: Connection cable with M12 that attaches to instrument side and USB 2.0 on PC side.

SWD10: 100-240Vac/12Vdc-1A mains voltage stabilized power supply.

AQC: 200cc. of distilled water and n° 3 braids for HP3201 or HP3201.2 probes

HD40.1: 24-column portable printer (uses cable HD2110RS).

**BAT.40:** Spare battery pack for HD40.1 printer with built-in temperature sensor.

RCT: The kit includes 4 thermal paper rolls, wide 57mm, diameter 32mm.



