

MH60

Isolated current probe for oscilloscopes



View AC and DC currents in the field or in the lab!

- › Up to 100 A
- › 26 mm clamping diameter
- › 1 MHz bandwidth
- › Rechargeable battery
- › Power supply and recharging via standard 5 V μ USB



600 V
CAT II

300 V
CAT III

Measure up



MH60 Isolated AC and DC current probe for oscilloscopes

Without opening the circuit, simply clamp and measure!

The quick, practical MH60 probe can be used for wide-band AC and DC current measurements thanks to its dual Hall effect / transformer technology.

The MH60 probe can be powered either via its μ USB port connected to an oscilloscope, via a mains adapter or via its internal rechargeable battery combined with an automatic standby function which can be deactivated.

To make it simpler to use, the MH60 probe is equipped with:

- › an automatic "ZeroDC" system allowing you to compensate magnetic and electronic drift.
- › a built-in magnetometer to overcome the influence of the clamp's position in the presence of the earth field and other constant fields
- › a switchable low-pass filter



View and check

When installing or maintaining electrical or electrotechnical equipment, the MH60 can be used to view the currents in order to check, for example:

- › the command signals in power electronics (PWM)
- › the quality and efficiency of a DC / AC converter
- › activation / deactivation of the equipment in a vehicle



MH60 TECHNICAL SPECIFICATIONS

Measurement range*	10 mA to 100 A RMS or DC (140 A peak)	Power supply	Internal NiMH rechargeable battery (approx. 8-hour battery life) or 5 VDC external via female μ USB type B connection
Output signal	10 mV/A	Safety	IEC 61010-1, IEC 61010-2-032, 300 V CAT III / 600 V CAT II
Bandwidth	1 MHz	Dimensions	138 x 49 x 28 mm
Switchable low-pass filters	none / 30 kHz / 3 kHz	Weight	Approx. 200 g (with cable and rechargeable battery)
Rise time from 10 to 90%	350 ns		
Clamping diameter	1 cable with $\varnothing$ 26 mm		
Connections	Built-in cable 2 m long with moulded isolated male BNC plug		

*From 60 kHz, limitation of the current measurement range according to the frequency

TO ORDER

MH60 isolated AC and DC current probe for oscilloscopes delivered with a 100 V-240 V 50/60 Hz mains adapter, 1 USB / μ USB power cable, 5-language user manual

..... **P01120612**

Replacement parts

NiMH rechargeable battery **P01296049**

FRANCE
Chauvin Arnoux
190, rue Championnet
75876 PARIS Cedex 18
Tél : +33 1 44 85 44 85
Fax : +33 1 46 27 73 89
info@chauvin-arnoux.fr
www.chauvin-arnoux.fr

INTERNATIONAL
Chauvin Arnoux
Unit 1 Nelson Ct, Flagship Sq, Shaw Cross Business Pk
Dewsbury, West Yorkshire - WF12 7TH
Tel: +44 1924 460 494
Fax: +44 1924 455 328
info@chauvin-arnoux.co.uk
www.chauvin-arnoux.com

MIDDLE EAST
Chauvin Arnoux Middle East
P.O. BOX 60-154
1241 2020 JAL EL DIB - LEBANON
Tel: +961 1 890 425
Fax: +961 1 890 424
camie@chauvin-arnoux.com
www.chauvin-arnoux.com

 **CHAUVIN
ARNOUX**
GROUP